



PRODUCT NUMBER

10124323-4XX-XXLF




RoHS COMPATIBLE, SEE NOTE 5
TOTAL NB OF POSITION 01 TO 36
PACKAGING, SEE NOTE 3
PIN STYLE, SEE TABLE
PLATING :
-4 : 2µmMIN MATE TIN
OVER 1.27µm Ni MIN



PIN STYLE	OAL	STACK HEIGHT	DIM"B"
01	19.40	12.00	4.40
02	17.70	7.95	3.40

NOTES :

- HOUSING MATERIAL :
HIGH TEMP THERMOPLASTIC UL94-V-0, COLOR : BLACK
PIN MATERIAL : COPPER ALLOY
- 9N MIN RETENTION IN EITHER DIRECTION
- PACKAGING : BULK
- THIS PRODUCT IS INTENDED TO BE USED WITH 1.6mm PCB THICKNESS
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS :
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - MANUFACTURING PROCESS COMPATIBILITY :
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C
 - LABELLING :
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - LEGAL STATEMENT :
 - SEE GS-47-0004
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITION
EXAMPLE : 8 POS = N x 2.54 = 20.52mm
- PRODUCT SPECIFICATION AS PER BUS-12-117



SCALE 1:1

spec ref	dr	Aymeric Soudy	2014/02/14	projection	size	A3	scale	5:1
tolerance std	eng	Aymeric Soudy	2014/02/17	chr	Laurent Mulin	2014/02/17	ecn no	-
	appr	Ludovic Meyer	2014/02/17	product family	BSTIK	rel level	Released	
surface	linear	0.X	±	FCI	title	SINGLE ROW - DOUBLE BODY	dwg no	10124323
		0.XX	±	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 1 of 1
		0.XXX	±					
	angular	0°	±°					