



DUAL-IN-LINE SOCKETS


SERIES 115...001 • VERY LOW PROFILE • OPEN FRAME



- Low profile DIP socket, sits only .122" above the PCB
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 115 uses MM #0501 pins. See page 162 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



ORDERING INFORMATION

Total number of pins				Quantity per tube	ORDERING INFORMATION														
	A	B	C																
10	0.5	0.2	0.3	41	115-XX-210-41-001000 115-XX-304-41-001000 115-XX-306-41-001000 115-XX-308-41-001000 115-XX-310-41-001000 115-XX-314-41-001000 115-XX-316-41-001000 115-XX-318-41-001000 115-XX-320-41-001000 115-XX-322-41-001000 115-XX-324-41-001000 115-XX-328-41-001000 115-XX-420-41-001000 115-XX-422-41-001000 115-XX-424-41-001000 115-XX-428-41-001000 115-XX-432-41-001000 115-XX-624-41-001000 115-XX-628-41-001000 115-XX-632-41-001000 115-XX-636-41-001000 115-XX-640-41-001000 115-XX-642-41-001000 115-XX-648-41-001000 115-XX-650-41-001000 115-XX-652-41-001000 115-XX-950-41-001000 115-XX-952-41-001000 115-XX-964-41-001000														
4	0.2	0.3	0.4	102															
6	0.3	0.3	0.4	67															
8	0.4	0.3	0.4	50															
10	0.5	0.3	0.4	40															
14	0.7	0.3	0.4	28															
16	0.8	0.3	0.4	25															
18	0.9	0.3	0.4	22															
20	1.0	0.3	0.4	20															
22	1.1	0.3	0.4	18															
24	1.2	0.3	0.4	16															
28	1.4	0.3	0.4	14															
20	1.0	0.4	0.5	20															
22	1.1	0.4	0.5	18															
24	1.2	0.4	0.5	16															
28	1.4	0.4	0.5	14															
32	1.6	0.4	0.5	12															
24	1.2	0.6	0.7	16															
28	1.4	0.6	0.7	14															
32	1.6	0.6	0.7	12															
36	1.8	0.6	0.7	11															
40	2.0	0.6	0.7	10															
42	2.1	0.6	0.7	9															
48	2.4	0.6	0.7	8															
50	2.5	0.6	0.7	8															
52	2.6	0.6	0.7	7															
50	2.5	0.9	1.0	8															
52	2.6	0.9	1.0	7															
64	3.2	0.9	1.0	6															
SPECIFY PLATING CODE XX =														91	93		41	43	
Sleeve (Pin) 														200 μ" Sn/Pb	200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn	
Contact (Clip) 														10 μ" Au	30 μ" Au		10 μ" Au	30 μ" Au	

XX=Plating Code
See Below

RoHS-2
2011/65/EU



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com