

NOTES:


- MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):
BODY - BRASS, GOLD PLATING
CONTACT - BRASS, GOLD PLATING
INSULATOR - PTFE
- ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
- MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: - 65°C to +165°C
- FOR ASSEMBLY INSTRUCTIONS SEE AMPHENOL SPEC. 349-50521,SHEET 4

THIRD ANGLE PROJ.







REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A1	PART ASSEMBLY WAS CHANGED	25-Jul-03	--	--
B	SEE SHEET 1	01-Mar-05	--	SH
F	ADD NOTE 4/RD-DM08072901S1	08-Aug-08	47141	SH
G	SEE SHEET 1/RD-DM08090502K	11-Sep-08		SH



RECOMMENDED MOUNTING
HOLE DIMENSIONS
SCALE 5.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

FINISH

DRAWN
S.XIEENGINEER
S.HSIEHAPPROVED
S.HSIEH

CAD FILE

F:\DWG\CNPD\903\411J\51S1-GSZ

DATE
01-Mar-05DATE
01-Mar-05DATE
01-Mar-05

TITLE

50 OHM SMB JACK BULKHEAD
MOUNT(FOR RG-174/U,188A/U,
316/U CABLE)

SCALE: 4/1

DWG SIZE

B

SHEET

CODE ID

74868

2 OF 2

REV

G

Amphenol RF

Danbury CT USA, Tainan Taiwan, Shenzhen China
www.amphenolrf.com

DRAWING NO. 903-411J-51S1

ITEM NO. 903-411J-51S1

PART NO. 903-411J-51S1