


- Designed for Complementary Use with the TIP33 Series
- 80 W at 25°C Case Temperature
- 10 A Continuous Collector Current
- 15 A Peak Collector Current
- Customer-Specified Selections Available



Pin 2 is in electrical contact with the mounting base.

MDTRAAA

**absolute maximum ratings at 25°C case temperature (unless otherwise noted)**

| RATING                                                                             |        | SYMBOL              | VALUE       | UNIT |
|------------------------------------------------------------------------------------|--------|---------------------|-------------|------|
| Collector-base voltage ( $I_E = 0$ )                                               | TIP34  | $V_{CBO}$           | -80         | V    |
|                                                                                    | TIP34A |                     | -100        |      |
|                                                                                    | TIP34B |                     | -120        |      |
|                                                                                    | TIP34C |                     | -140        |      |
| Collector-emitter voltage ( $I_B = 0$ )                                            | TIP34  | $V_{CEO}$           | -40         | V    |
|                                                                                    | TIP34A |                     | -60         |      |
|                                                                                    | TIP34B |                     | -80         |      |
|                                                                                    | TIP34C |                     | -100        |      |
| Emitter-base voltage                                                               |        | $V_{EBO}$           | -5          | V    |
| Continuous collector current                                                       |        | $I_C$               | -10         | A    |
| Peak collector current (see Note 1)                                                |        | $I_{CM}$            | -15         | A    |
| Continuous base current                                                            |        | $I_B$               | -3          | A    |
| Continuous device dissipation at (or below) 25°C case temperature (see Note 2)     |        | $P_{tot}$           | 80          | W    |
| Continuous device dissipation at (or below) 25°C free air temperature (see Note 3) |        | $P_{tot}$           | 3.5         | W    |
| Unclamped inductive load energy (see Note 4)                                       |        | $\frac{1}{2}LI_C^2$ | 62.5        | mJ   |
| Operating junction temperature range                                               |        | $T_j$               | -65 to +150 | °C   |
| Storage temperature range                                                          |        | $T_{stg}$           | -65 to +150 | °C   |
| Lead temperature 3.2 mm from case for 10 seconds                                   |        | $T_L$               | 250         | °C   |

NOTES: 1. This value applies for  $t_p \leq 0.3$  ms, duty cycle  $\leq 10\%$ .  
2. Derate linearly to 150°C case temperature at the rate of 0.64 W/°C.  
3. Derate linearly to 150°C free air temperature at the rate of 28 mW/°C.  
4. This rating is based on the capability of the transistor to operate safely in a circuit of:  $L = 20$  mH,  $I_{B(on)} = -0.4$  A,  $R_{BE} = 100 \Omega$ ,  $V_{BE(off)} = 0$ ,  $R_S = 0.1 \Omega$ ,  $V_{CC} = -20$  V.

**PRODUCT INFORMATION**

**electrical characteristics at 25°C case temperature**

| PARAMETER                                              | TEST CONDITIONS                                                                                                 |                                                              |                                     | MIN                       | TYP | MAX                          | UNIT |
|--------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|-------------------------------------|---------------------------|-----|------------------------------|------|
| $V_{(BR)CEO}$ Collector-emitter breakdown voltage      | $I_C = -30 \text{ mA}$<br>(see Note 5)                                                                          | $I_B = 0$                                                    | TIP34<br>TIP34A<br>TIP34B<br>TIP34C | -40<br>-60<br>-80<br>-100 |     |                              | V    |
| $I_{CES}$ Collector-emitter cut-off current            | $V_{CE} = -80 \text{ V}$<br>$V_{CE} = -100 \text{ V}$<br>$V_{CE} = -120 \text{ V}$<br>$V_{CE} = -140 \text{ V}$ | $V_{BE} = 0$<br>$V_{BE} = 0$<br>$V_{BE} = 0$<br>$V_{BE} = 0$ | TIP34<br>TIP34A<br>TIP34B<br>TIP34C |                           |     | -0.4<br>-0.4<br>-0.4<br>-0.4 | mA   |
| $I_{CEO}$ Collector cut-off current                    | $V_{CE} = -30 \text{ V}$<br>$V_{CE} = -60 \text{ V}$                                                            | $I_B = 0$<br>$I_B = 0$                                       | TIP34/34A<br>TIP34B/34C             |                           |     | -0.7<br>-0.7                 | mA   |
| $I_{EBO}$ Emitter cut-off current                      | $V_{EB} = -5 \text{ V}$                                                                                         | $I_C = 0$                                                    |                                     |                           |     | -1                           | mA   |
| $h_{FE}$ Forward current transfer ratio                | $V_{CE} = -4 \text{ V}$<br>$V_{CE} = -4 \text{ V}$                                                              | $I_C = -1 \text{ A}$<br>$I_C = -3 \text{ A}$                 | (see Notes 5 and 6)                 | 40<br>20                  |     | 100                          |      |
| $V_{CE(sat)}$ Collector-emitter saturation voltage     | $I_B = -0.3 \text{ A}$<br>$I_B = -2.5 \text{ A}$                                                                | $I_C = -3 \text{ A}$<br>$I_C = -10 \text{ A}$                | (see Notes 5 and 6)                 |                           |     | -1<br>-4                     | V    |
| $V_{BE}$ Base-emitter voltage                          | $V_{CE} = -4 \text{ V}$<br>$V_{CE} = -4 \text{ V}$                                                              | $I_C = -3 \text{ A}$<br>$I_C = -10 \text{ A}$                | (see Notes 5 and 6)                 |                           |     | -1.6<br>-3                   | V    |
| $h_{fe}$ Small signal forward current transfer ratio   | $V_{CE} = -10 \text{ V}$                                                                                        | $I_C = -0.5 \text{ A}$                                       | $f = 1 \text{ kHz}$                 | 20                        |     |                              |      |
| $ h_{fe} $ Small signal forward current transfer ratio | $V_{CE} = -10 \text{ V}$                                                                                        | $I_C = -0.5 \text{ A}$                                       | $f = 1 \text{ MHz}$                 | 3                         |     |                              |      |

NOTES: 5. These parameters must be measured using pulse techniques,  $t_p = 300 \mu\text{s}$ , duty cycle  $\leq 2\%$ .

6. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

**thermal characteristics**

| PARAMETER                                               | MIN | TYP | MAX  | UNIT |
|---------------------------------------------------------|-----|-----|------|------|
| $R_{\theta JC}$ Junction to case thermal resistance     |     |     | 1.56 | °C/W |
| $R_{\theta JA}$ Junction to free air thermal resistance |     |     | 35.7 | °C/W |


**resistive-load-switching characteristics at 25°C case temperature**

| PARAMETER               | TEST CONDITIONS †           |                              |                                        | MIN | TYP | MAX | UNIT          |
|-------------------------|-----------------------------|------------------------------|----------------------------------------|-----|-----|-----|---------------|
| $t_{on}$ Turn-on time   | $I_C = -6 \text{ A}$        | $I_{B(on)} = -0.6 \text{ A}$ | $I_{B(off)} = 0.6 \text{ A}$           |     | 0.4 |     | $\mu\text{s}$ |
| $t_{off}$ Turn-off time | $V_{BE(off)} = 4 \text{ V}$ | $R_L = 5 \Omega$             | $t_p = 20 \mu\text{s}$ , $dc \leq 2\%$ |     | 0.7 |     | $\mu\text{s}$ |

† Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.


**TYPICAL CHARACTERISTICS**

**TYPICAL DC CURRENT GAIN  
vs  
COLLECTOR CURRENT**




**Figure 1.**

**COLLECTOR-EMITTER SATURATION VOLTAGE  
vs  
BASE CURRENT**



**Figure 2.**

**BASE-EMITTER VOLTAGE  
vs  
COLLECTOR CURRENT**



**Figure 3.**

**PRODUCT INFORMATION**

## MAXIMUM SAFE OPERATING REGIONS




Figure 4.

## THERMAL INFORMATION




Figure 5.

## PRODUCT INFORMATION

JULY 1968 - REVISED SEPTEMBER 2002  
Specifications are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[TIP34A-S](#) [TIP34B-S](#) [TIP34C-S](#) [TIP34-S](#)