

- Designed to meet UL1950 and IEC950 safety requirements
- Operating temperature range: -40° C to +85° C
- Meets IEC 695, 2-2 flammability requirements
- PWB Process Capability: standard printed wiring board assembly techniques, total-immersion cleaning
- Reliability testing: shock, vibration, temperature cycling, temperature - humidity - bias


ELECTRICAL SPECIFICATIONS AT 25° C

Part Number	Package	Turns Ratio ¹ ± 2%	Inductance ³ μH	Leakage Inductance ⁶ μH max ⁵	DCR Ω max				Dielectric Rating Vrms
		(1-5) : (10-6) ²	(10-6) ⁴	(10-6) ²	(1-4)	(2-5)	(9-6)	(10-7)	(1-5) & (10-6) ²
S560-6600-74	SMD	1 : 1.4	95 - 105	10	0.50	0.50	0.60	0.60	1500

- measured at 20 kHz, 1 Vrms
- connect terminals 2 to 4 & 7 to 9
- measured at 10 kHz, 0.1 Vrms
- connect terminals 7 to 9
- measured at 100 kHz, 0.1 Vrms
- short terminals 1, 2, 4, & 5


SCHEMATIC

S560-6600-74




MECHANICAL

S560-6600-74



SUGGESTED PCB PAD LAYOUT



©2000 Bel Fuse Inc. Specifications subject to change without notice. 10.00

CORPORATE

Bel Fuse Inc.
198 Van Vorst Street
Jersey City, NJ 07302
Tel 201-432-0463
Fax 201-432-9542
www.belfuse.com

T3-34

FAR EAST

Bel Fuse Ltd.
8F / 8 Luk Hop Street
San Po Kong
Kowloon, Hong Kong
Tel 852-2328-5515
Fax 852-2352-3706
www.belfuse.com

EUROPE

Bel Fuse Europe Ltd.
Preston Technology Management Centre
Marsh Lane, Suite G7, Preston
Lancashire, PR1 8UD, U.K.
Tel 44-1772-556601
Fax 44-1772-888366
www.belfuse.com