


Features

- Complementary Pair MOSFETs
- Low On-Resistance
 - N-Channel: 35mΩ @ 10V
61mΩ @ 4.5V
 - P-Channel: 65mΩ @ -10V
115mΩ @ -4.5V
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Lead Free By Design/RoHS Compliant (Note 2)**
- "Green" Device (Note 3)**
- Qualified to AEC-Q101 Standards for High Reliability**

Mechanical Data

- Case: SOP-8L
- Case Material: Molded Plastic, "Green" Molding Compound.
UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020D
- Terminals Connections: See Diagram
- Terminals: Finish - Matte Tin annealed over Copper lead frame. Solderable per MIL-STD-202, Method 208
- Marking Information: See Page 6
- Ordering Information: See Page 6
- Weight: 0.072g (approximate)



Maximum Ratings N-CHANNEL @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Drain Source Voltage	V _{DSS}	30	V
Gate-Source Voltage	V _{GSS}	±20	V
Drain Current (Note 1)	I _D	6.9 5.8	A
		T _A = 25°C T _A = 70°C	
Pulsed Drain Current (Note 4)	I _{DM}	30	A

Maximum Ratings P-CHANNEL @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Drain Source Voltage	V _{DSS}	-30	V
Gate-Source Voltage	V _{GSS}	±20	V
Drain Current (Note 1)	I _D	-5 -4.2	A
		T _A = 25°C T _A = 70°C	
Pulsed Drain Current (Note 4)	I _{DM}	-20	A

Thermal Characteristics @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 1)	P _D	2	W
Thermal Resistance, Junction to Ambient	R _{θJA}	62.5	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

- Notes:
- Device mounted on 2oz. copper pads on 2" x 2" FR4 PCB.
 - No purposefully added lead.
 - Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.
 - Repetitive rating, pulse width limited by junction temperature.

Electrical Characteristics N-CHANNEL @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 5)						
Drain-Source Breakdown Voltage	BV _{DSS}	30	—	—	V	V _{GS} = 0V, I _D = 250μA
Zero Gate Voltage Drain Current	I _{DSS}	—	—	1	μA	V _{DS} = 24V, V _{GS} = 0V
Gate-Source Leakage	I _{GSS}	—	—	± 100	nA	V _{GS} = ±20V, V _{DS} = 0V
ON CHARACTERISTICS (Note 5)						
Gate Threshold Voltage	V _{GS(th)}	1	—	2.1	V	V _{DS} = V _{GS} , I _D = 250μA
Static Drain-Source On-Resistance	R _{DS(ON)}	—	28 51	35 61	mΩ	V _{GS} = 10V, I _D = 6.9A V _{GS} = 4.5V, I _D = 5.0A
Forward Transfer Admittance	Y _{fs}	—	7.7	—	S	V _{DS} = 5V, I _D = 6.9A
Diode Forward Voltage (Note 5)	V _{SD}	0.5	—	1.2	V	V _{GS} = 0V, I _S = 1A
DYNAMIC CHARACTERISTICS						
Input Capacitance	C _{iss}	—	384	—	pF	V _{DS} = 15V, V _{GS} = 0V, f = 1.0MHz
Output Capacitance	C _{oss}	—	67	—	pF	
Reverse Transfer Capacitance	C _{rss}	—	48	—	pF	
Gate Resistance	R _G	—	1.3	—	Ω	V _{GS} = 0V, V _{DS} = 0V, f = 1MHz
SWITCHING CHARACTERISTICS						
Total Gate Charge	Q _g	—	4.3 8.6	—	nC	V _{DS} = 10V, V _{GS} = 4.5V, I _D = 10A V _{DS} = 10V, V _{GS} = 10V, I _D = 10A
Gate-Source Charge	Q _{gs}	—	1.2	—		V _{DS} = 10V, V _{GS} = 10V, I _D = 10A
Gate-Drain Charge	Q _{gd}	—	2.5	—		V _{DS} = 10V, V _{GS} = 10V, I _D = 10A







Electrical Characteristics P-CHANNEL @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 5)						
Drain-Source Breakdown Voltage	BV _{DSS}	-30	—	—	V	V _{GS} = 0V, I _D = -250μA
Zero Gate Voltage Drain Current	I _{DSS}	—	—	-1.0	μA	V _{DS} = -24V, V _{GS} = 0V
Gate-Source Leakage	I _{GSS}	—	—	± 100	nA	V _{GS} = ±20V, V _{DS} = 0V
ON CHARACTERISTICS (Note 5)						
Gate Threshold Voltage	V _{GS(th)}	-1	—	-2.1	V	V _{DS} = V _{GS} , I _D = -250μA
Static Drain-Source On-Resistance	R _{DS(ON)}	—	56 98	65 115	mΩ	V _{GS} = -10V, I _D = -5A V _{GS} = -4.5V, I _D = -4A
Forward Transfer Admittance	Y _{fs}	—	—	5.2	S	V _{DS} = -10V, I _D = -5A
Diode Forward Voltage (Note 5)	V _{SD}	-0.5	—	-1.2	V	V _{GS} = 0V, I _S = -2.6A
DYNAMIC CHARACTERISTICS						
Input Capacitance	C _{iss}	—	336	—	pF	V _{DS} = -25V, V _{GS} = 0V, f = 1.0MHz
Output Capacitance	C _{oss}	—	70	—	pF	
Reverse Transfer Capacitance	C _{rss}	—	49	—	pF	
Gate Resistance	R _G	—	4.6	—	Ω	V _{GS} = 0V, V _{DS} = 0V, f = 1MHz
SWITCHING CHARACTERISTICS						
Total Gate Charge	Q _g	—	4.0 7.8	—	nC	V _{DS} = 15V, V _{GS} = -4.5V, I _D = -5A V _{DS} = 15V, V _{GS} = -10V, I _D = -5A
Gate-Source Charge	Q _{gs}	—	1.0	—		V _{DS} = 15V, V _{GS} = -10V, I _D = -5A
Gate-Drain Charge	Q _{gd}	—	2.5	—		V _{DS} = 15V, V _{GS} = -10V, I _D = -5A

Notes: 5. Short duration pulse test used to minimize self-heating effect.

N-CHANNEL

NEW PRODUCT



N-CHANNEL (continued)




Fig. 7 Reverse Drain Current vs. Source-Drain Voltage




Fig. 8 Typical Total Capacitance










Fig. 9 Transient Thermal Resistance

P-CHANNEL

NEW PRODUCT




P-CHANNEL (continued)


Fig. 16 Gate Threshold Variation vs. Ambient Temperature




Fig. 17 Diode Forward Voltage vs. Current



Ordering Information (Note 6)

Part Number	Case	Packaging
DMC3035LSD-13	SOP-8L	2500/Tape & Reel

 Notes: 6. For packaging details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.


Marking Information

(Top View)


Package Outline Dimensions


SOP-8L		
Dim	Min	Max
A	-	1.75
A1	0.08	0.25
A2	1.30	1.50
A3	0.20	Typ
b	0.3	0.5
D	4.80	5.30
E	5.79	6.20
E1	3.70	4.10
e	1.27	Typ
h	-	0.35
L	0.38	1.27
θ	0°	8°
All Dimensions in mm		

Suggested Pad Layout



Dimensions	Value (in mm)
X	0.60
Y	1.55
C1	5.4
C2	1.27

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.