

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRELIMINARY ECO-09-012031 WR	28MAY09	LH	JH
	A	RLSD REV ECO-09-014128	16JUN09	LH	JS

- ENCLOSURE HAS 4 EMBOSSED MOUNTING HOLES ON BASE UNIT.
- PORON FOAM ON BOTH ENDS (4 PLACES)
- HOLDS TWO (2) FIBER OPTIC CASSETTE.
- MOUNTING HARDWARE INCLUDED:
(4) #8 X .50 LG/ TYPE AB PAN HEAD SCREWS
- FINISH: BLACK POWDER COAT, MEDIUM TEXTURE.
- TOOLHEAD RECESS KEY PROVIDED WITH -2 ASSEMBLY.

Exploded view diagram of the AMP Netconnect enclosure. The cover is shown at the top, secured by four quarter turn stud fasteners. The base unit is shown below, containing two fiber optic cassettes held in place by retainers. Poron urethane foam is used for cushioning at the ends. The AMP Netconnect logo is embossed on the cover. Labels include: QUARTER TURN STUD FASTENER, WEAR WASHER, EJECTOR SPRING 4 SUPPLIED; AMP NETCONNECT LOGO; COVER; RETAINER 4 SUPPLIED; PORON URETHANE FOAM; and BASE UNIT.

Assembled view diagram of the AMP Netconnect enclosure. The cover is mounted on the base unit. Dimensions are provided: 279.40 [11.00] REF for the length and 44.45 [1.75] REF for the height. Labels include: COVER, QUARTER TURN STUD FASTENER, WEAR WASHER, EJECTOR SPRING 4 SUPPLIED, AMP NETCONNECT, PORON URETHANE FOAM, and BASE UNIT.

6	TOOL	1777273-2
	PHILLIPS	1777273-1
	STUD HEAD SIZES	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	L. HALL	26MAY2009	Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: mm [INCHES]		CHK	J. SHIPE	27MAY2009	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J. SHIPE	27MAY2009	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	J. SHIPE	27MAY2009	
MATERIAL	FINISH	WEIGHT	NAME		
16 AWG ALUMINUM	BLACK POWDER COATED	-	DW-EAZ ENCLOSURE		
CUSTOMER DRAWING		SCALE	SHEET		RESTRICTED TO
		NTS	1 OF 1		-

AMP 1471-9 REV 31MAR2000

1777273

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity Divested:

[1-1906051-1](#) [381A302510CS5327](#) [2-6278028-2](#) [1-6754278-2](#) [3-1907394-2](#) [4-1906071-7](#) [1-1906996-7](#) [4-1906073-7](#) [TCP-5ERUVA-DB14F](#) [3-1375191-0](#) [1-6374497-4](#) [E658721](#)