















Axial Fans




D591T, 601T, 603T, 604T 12 VDC




D591T, 601T, 603T, 604T 24 VDC



D591Q, 601Q, 603Q, 604Q 12 VDC



D591Q, 601Q, 603Q, 604Q 24 VDC



D600

Technical data

The serie D600Q is equipped with an electro-nical motor, including Micronel Asic (3 leads)
– Long life
– voltage range 5-30 VDC
– tacho signal (speed indicator)
– current limitation
Option: 10 leads-version with further functions

Types -1 -3 -4		D591T/D601T/D603T/D604T		D591Q/D601Q/D603Q/D604Q	
		12	24	12	24
U	U _N V	9...15	18...30	5...15	9...30
U	U V				
I	I _N mA	557	231	635	315
I	I _{max} mA	668	277	794	394
I	I _{block} A	5.6	4.3	2.4	1.5
P	P _N W	6.68	5.54	7.62	7.56
rpm	n min ⁻¹	10650	10200	9550	9450
→	ṽ l/min; CFM	1192/42.1	1143/40.4	1100/38.9	1080/38.7
↑	p Pa	395	366	266	268
↻	LpA dB(A)	57	56	55	56
MTTF	MTTF hr	10000		++plus 40 000	
⌈	T °C/F	-20...+65 / -5...+150		-20...+65 / -5...+150	
⌈	m g/oz.	179/6.17		165/5.81	
⌈	L/M mm/inch	220/8.86		220/8.86	
⌈	PPO UL-94V-1	-		-	
⌈	Aluminium	o.k.		o.k.	
⌈		-		-	
⌈		o.k.		o.k.	
CLL		-		-	
⌈		-		o.k.	
⌈		o.k.		o.k.	
⌈		o.k.		o.k.	
Ex		-		i	

Additional Functions for 10 Lead Version

- PWM (variable speed)
- PLL (constant speed)
- Low noise function
- Brake function
- Direction
- NOS

D591	mm	inch	D600	mm	inch
D1			D1	60	2.362
D2	56.5	2.224	D2	56.5	2.224
L1	60	2.362	L1	60	2.362
L2			L2		
L3			L3	4	0.157
B	M3		B	M3	
Q1	62	2.441	Q1	64	2.520
Q2	50	1.968	Q2	50	1.968
R	0.3	0.012	R	4	0.157

Micronel U.S. 1280 Liberty Way Vista, Ca. 92083
Tel: 760-727-7400 / Fax: 760-727-4436
Email: mus@ix.netcom.com / Web: www.micronel.com



Price 1-4 pcs. _____
Price 5-24 pcs. _____
Delivery ARO _____