

SOURIAU

8LT Series

MIL-DTL-38999 Series I

Esterline
Connection Technologies

8LT Series
MIL-DTL-38999 Series I

Contents

Overview

- 8LT Series - Presentation 06
- 8LT Series - Applications 06
- A universal product platform 07
- Contact layouts 08
- Contact layouts (matrix) 12

Series

- 8LT Standard Version:
  - Technical features 16
  - Ordering information 17
  - Dimensions 19
- Backshells:
  - Ordering information 24
  - Dimensions 24
  - Thread information 27
  - Recommended installation torque 27
  - Band-it 27
- 8LT Rack & Panel:
  - Technical features 28
  - Ordering information 29
  - Dimensions 30
  - Panel cut-out 31
- 8LT Resin sealed:
  - Technical features 32
  - Ordering information 33

Contacts & Tooling

- Crimp contacts 36
- Straight PC tail contacts 38
- Coaxial contacts # 12 39
- Solder cup 39
- Crimp contacts: 1500 mating 39
- Wire wrap contacts 39
- Quadrax #8 contacts 39
- Thermocouple contacts 40
- Dummy contacts 40
- Filler plugs 40
- Wiring instructions 41
- Crimping tools 42
- Insertion & extraction tools 43

Common Section

- Protective caps 46
- Reductors 47
- Boots 48
- Orientations 48
- Panel gasket 49
- Dummy receptacles 49
- Cross reference list 50
- Coordinates information 52

Range Extension

- micro38999 62
- RoHS solution 62
- High density 63
- PCB contact without shoulder 63

© 2013 - SOURIAU

8LT Series

8LT Series

Overview

- 8LT Series - Presentation 06
- 8LT Series - Applications 06
- A universal product platform: MIL-DTL-38999 07
- A universal product platform: VG96912 & JN1003 07
- Contact layouts 08
- Contact layouts (matrix) 12

8LT Series
MIL-DTL-38999 Series I

8LT Series - Presentation

High contact density connectors with high reliability

38999 Series I: 8LT Series

This 8LT product family is qualified in accordance to the MIL-DTL-38999 Series I.

Originally designed to meet the high performance needs of the aerospace industries & military applications, it is also now used in varied applications needing extremely reliable interconnections with high density contact arrangements in a miniature circular shell.

- Weight and Space Saving
- Quick Mating - 3 point bayonet lock system
- Mismating, error proof positioning - keyway polarization (5 positions)
- High choice of Insert arrangements (customization possible, please consult us)
- Range extension available or on demand (Rack Panel, Potted, Hermetics, Low Profile, Filters, etc..), please consult us
- Versatility thanks to our inserts as for the series III (except for 8LT type 2) with full range of crimp contacts interchangeable
- Gold plated crimp or PC tail contacts are rear removable and retained in the insulator by a metal clip.
- RoHS version available (cadmium free)

8LT Series - Applications

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

A universal product platform: MIL-DTL-38999

38999 Series II: 8T Series

- Short version of MIL-DTL-38999 Series I
- Low profile = lightweight
- High density MIL-spec circular (1980's)
- Non-scoop proof, bayonet coupling
- Method of mounting: screws or jam nut
- Shell: Aluminum alloy
- Plating: cadmium, nickel, hard anodized
- QPL approved
- Numerous layouts

38999 Series III: 8D Series

- High density MIL-spec circular (1980's)
- Scoop proof, fast screw coupling
- Composite light-weight version available
- QPL approved
- Titanium version, light-weight, mechanical and environnemental performances
- Quadrax and Elio version
- Specific versions (clinch nuts, double flange, high power, hermetic, ...)

A universal product platform: VG96912 & JN1003

8ST Series

- High density - same layouts as 38999 Series I
- Lightweight version of Series I
- Scoop proof, bayonet coupling
- Method of mounting: screws or jam nut
- Shell: Aluminum alloy
- Plating: olive green cadmium or nickel
- VG 96912 German specification
- JN 1003 Typhoon specification

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Contact layouts

09

12 HD

12#26
Service R

35

6#22D
Service M

98

3#20
Service I

- Contact #26 & #22D
- Contact #20
- Contact #16
- Contact #12
- Contact #10
- Contact #8
- Contact #8 Power
- Contact #8 Quadrax
- Contact #4 Power

11

01

1#12
Service II

02

2#16
Service I

04

4#20
Service I

05

5#20
Service I

22*

4#22D
Service M

26 HD

26#26
Service R

35

13#22D
Service M

80

1#8 Triax
Service I

81

1#8 Quadrax

98

6#20
Service I

99

7#20
Service I

13

03

3#16
Service I

04

4#16
Service I

08

8#20
Service I

26

2#12
6#22D
Service M

35

22#22D
Service M

43 HD

43#26
Service R

98

10#20
Service I

Ethernet Quadrax HD High Density layout * Available on specific request. Please consult us.

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Contact layouts

15

05



5#16
Service II

15



1#16
14#20
Service I

18



18#20
Service I

19



19#20
Service I

35



37#22D
Service M

97



4#16
8#20
Service I

17

02



38#22D
1#8 Triax
Service M

06*



6#12
Service I

08



8#16
Service II

20*



4#12
16#22D
Service M

22



2#12
2#8 Triax
Service M

26



26#20
Service I

35



55#22D
Service M

75



2#8 Triax
Service M

80



2#12
2#8 Quadrax

81



38#22D
1#8 Quadrax

82



2#8 Quadrax

99



2#16
21#20
Service I

19

11



11#16
Service II

18



14#22D
4#8 Triax
Service M

28



26#20
2#16
Service I

32



32#20
Service I

35



66#22D
Service M

84



14#22D
4#8 Quadrax

Ethernet Quadrax * Available on specific request. Please consult us.

© 2013 - SOURIAU

Contact layouts

21

11



11#12
Service I

16



16#16
Service II

35



79#22D
Service M

39



2#16
37#20
Service I

41



41#20
Service I

42



2#4 Power
Service I

48



4#8 Power
Service I

72



2#4 Power
6#16
Service I

75



4#8 Triax
Service M

77



17#22D
2#8 Triax
Service M

78



17#22D
2#8 Quadrax

84



4#8 Quadrax

23

21



21#16
Service II

32



32#20
Service I

35



100#22D
Service M

53



53#20
Service I

54



4#12, 9#16
40#22D
Service M

55



55#20
Service I

Ethernet Quadrax

© 2013 - SOURIAU

Contact layouts

25

04



8#16
48#20
Service I

07



2#8 Triax
97#22D
Service M

08*



8#8 Triax
Service M

11*



2#20
9#10
Service N

19



19#12
Service I

24



12#16
12#12
Service I

29



29#16
Service I

35



128#22D
Service M

37



37#16
Service I

41

22#22D, 3#20
11#16, 2#12
3#8 Triax
Service M

43



23#20
20#16
Service I

44

4#4 Power
4#16
Service I

46

40#20, 4#16
2#8 Coax
Service I

61



61#20
Service I

81



22#22D
3#20, 11#16
2#12
3#8 Quadrax

82



97#22D
2#8 Quadrax

86

40#20
4#16
2#8 Quadrax

88



8#8 Quadrax

90

40#20, 4#16
2#8 Twinax
Service I

Ethernet Quadrax

* Available on specific request. Please consult us.

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Contact layouts (matrix)

Shell Size	Layout	Service	8LT	8LT2	MIL-DTL-38999 (QPL)		HE 308			Nber of Contacts	#26	#22D	#20	#16	#12	#10	# 8	#4 Power
					MS (1)	MS27505	Not Rack		Rack									
09	09-12	R								12	12							
	09-35	M			**Q**	**Q**	O	X		6		6						
	09-98	I			**Q**		O	X		3			3					
11	11-01	II							•	1					1			
	11-02	I			**Q**				•	2				2				
	11-04	I			**Q**				•	4			4					
	11-05	I			**Q**				•	5			5					
	11-22	M								4		4						
	11-26	R								26	26							
	11-35	M			**Q**	**Q**	O	X	•	13		13						
	11-80	I								1							1 Triax	
	11-81	-								1							1 Qdx	
	11-98	I			**Q**	**Q**	O	X	•	6			6					
	11-99	I			**Q**				•	7			7					
13	13-03	I								3				3				
	13-04	I			**Q**		O		•	4				4				
	13-08	I			**Q**				•	8			8					
	13-26	M								8		6			2			
	13-35	M			**Q**	**Q**	O	X	•	22		22						
	13-43	R								43	43							
	13-98	I			**Q**	**Q**	O	X	•	10			10					
15	15-05	II			**Q**		O	X	•	5				5				
	15-15	I							•	15			14	1				
	15-18	I			**Q**	**Q**	O		•	18			18					
	15-19	I			**Q**	**Q**	O	X	•	19			19					
	15-35	M			**Q**	**Q**	O	X	•	37		37						
	15-97	I			**Q**	**Q**	O	X	•	12			8	4				
17	17-02	M								39		38					1 Triax	
	17-06	I			**Q**	**Q**	O		•	6			6					
	17-08	II			**Q**		O	X	•	8				8				
	17-20	M								20		16			4			
	17-22	M								4					2		2 Triax	
	17-26	I			**Q**	**Q**	O	X	•	26			26					
	17-35	M			**Q**	**Q**	O	X	•	55		55						
	17-75	M							•	2							2 Triax	
	17-80	-								4					2		2 Qdx	
	17-81	-								39		38					1 Qdx	
	17-82	-								2							2 Qdx	
	17-99	I			**Q**	**Q**	O	X	•	23			21	2				
19	19-11	II			**Q**		O	X	•	11				11				
	19-18	M								18		14					4 Triax	
	19-28	I			**Q**				•	28			26	2				
	19-32	I			**Q**	**Q**	O	X	•	32			32					
	19-35	M			**Q**	**Q**	O	X	•	66		66						
	19-84	-								18		14					4 Qdx	

Souriau's layout

Q Qualified layout (QPL) MIL - DTL 38999

(1) Available MS27466 & MS27467 & MS27468 & MS27656

O Layout according to UTE C 93-422 norm

X Qualified Layout HE308 for «Ministère de la Défense» DGA DTAT

• Layout according to C5935X0005 norm

#8 **Qdx:** Quadrax

© 2013 - SOURIAU

Contact layouts (matrix)

Shell Size	Layout	Service	8LT	8LT2	MIL-DTL-38999 (QPL)		HE 308			Nber of Contacts	#26	#22D	#20	#16	#12	#10	# 8	#4 Power
					MS (1)	MS27505	Not Rack		Rack									
21	21-11	I			Q		O	X	•	11					11			
	21-16	II			Q	Q	O	X	•	16				16				
	21-35	M			Q	Q	O	X	•	79		79						
	21-39	I			Q	Q	O		•	39			37	2				
	21-41	I			Q	Q	O	X	•	41			41					
	21-42	I								2								2
	21-48	I								4							4 Pow	
	21-72	I								8				6				2
	21-75	-			Q				•	4							4 Triax	
	21-77	M								19		17					2 Triax	
	21-78	-								19		17					2 Qdx	
	21-84	-								4							4 Qdx	
23	23-21	II			Q		O		•	21				21				
	23-32	I			Q	Q				32			32					
	23-35	M			Q	Q	O	X	•	100		100						
	23-53	I			Q		O	X	•	53			53					
	23-54	M								53		40		9	4			
	23-55	I			Q				•	55			55					
25	25-04	I			Q	Q				56			48	8				
	25-07	M			Q					99		97					2 Triax	
	25-08	-								8							8 Triax	
	25-11	N								11			2			9		
	25-19	I			Q		O	X		19					19			
	25-24	II			Q					24				12	12			
	25-29	I			Q		O	X		29				29				
	25-35	M			Q	Q	O	X		128		128						
	25-37	I								37				37				
	25-41	N								41		22	3	11	2		3 Triax	
	25-43	I			Q					43			23	20				
	25-44	I								8				4				4
	25-46	I			Q					46			40	4			2 Coax	
	25-61	I			Q		O	X		61			61					
	25-81	N								41		22	3	11	2		3 Qdx	
	25-82	M								99		97					2 Qdx	
	25-86	I								46			40	4			2 Qdx	
	25-88	-								8							8 Qdx	
	25-90	I								46			40	4			2 Triax	

Souriau's layout

Q Qualified layout (QPL) MIL - DTL 38999

(1) Available MS27466 & MS27467 & MS27468 & MS27656

O Layout according to UTE C 93-422 norm

X Qualified Layout HE308 for «Ministère de la Défense» DGA DTAT

• Layout according to C5935X0005 norm

#8 **Pow:** Power; **Qdx:** Quadrax

© 2013 - SOURIAU

8LT Series

8LT Series

Series

- 8LT Standard Version 16
- Backshells 24
- 8LT Rack & Panel 28
- 8LT Resin Sealed 32

8LT Series
MIL-DTL-38999 Series I

Description

- High contact density
- Bayonet coupling
- Contact protection : 100% Scoop proof
- Shell size from 9 to 25
- Accessories available (protective caps, backshells, etc…)
- RFI - EMI shielding and shell to shell continuity
- Hermetic
- Aluminum alloy, protection by cadmium, nickel, green zinc cobalt or black zinc nickel plating

Applications

- Civil and Military Aerospace
- Marine Equipments
- Communications Equipements
- Medical Instrumentation
- Ballistic Missiles & Weapon Systems
- Armored Carriers & Tanks
- Test Equipments

Technical features

Mechanical

- Shell: aluminum alloy
- Plating: . black zinc nickel (Z)
  . olive green cadmium (B)
  . nickel (F)
  . green zinc cobalt (ZC)
- Insulator: thermoplastic or metallic version available for specification 284 & 384
- Grommet or seal: liquid silicone rubber or fluorocarbone elastomer for specification 022
- Contact: copper alloy
- Plating contact: gold over nickel
- Endurance:
  500 mating / unmating operations
- Shock: 300 g during 3 ms and as per MIL S 901 grade A
- Vibration: . Sine 10 to 2000 Hz - 30 g
  . Random 100 à 300 Hz - 5 g²/Hz
- Contact retention (min force in N):

Contacts size	22	20	16	12	8	4
Min force in N	44	67	111	111	111	200

Electrical

- Test voltage (Vrms)

Service	sea level	at 21000 m
R	400	N/A
M	1 300	800
N	1 000	600
I	1 800	1 000
II	2 300	1 000

- Insulation resistance:
  ≥ 5 000 MW (at 500 Vcc)
- Contact resistance:

Contacts size	26	22	20	16	12	8	4
Resistance mΩ	16	14.6	7.3	3.8	3.5	3	2

- Contact rating:

Contacts size	26	22	20	16	12	8	4
Rating (A)	3	5	7.5	13	23	45	80

- Shell continuity: . black zinc nickel: 2.5 mΩ
  . olive green plating: 2.5 mΩ
  . nickel plating: 1 mΩ
  . green zinc cobalt: 2.5 mΩ
- Shielding: 90 db at 100 MHz, 50 db at 10 000 MHz
- Electrical continuity between contact and shell for specification 284 & 384: 10 mΩ max

Climatic

- Temperature range:
  . black zinc nickel plating (Z)
  - 65°C +175°C
  . olive green cadmium plating (B)
  - 65°C +175°C
  . nickel plating (F)
  - 65°C +200°C
  . green zinc cobalt plating (ZC)
  - 65°C +200°C
- Sealing: mated connectors
  Differential pressure 2 bars:
  leakage ≤ 16 cm^3/h
- Salt spray as per:
  . MIL STD 1344 method 1001 :
  - 500 hours (plating B, ZC and Z)
  - 48 hours (plating F)
  . NFC 93422 :
  - 48 hours (plating F)
- Resistance to fluids
  . As per MIL DTL 38999, hydraulic fluids, solvents
  . Specification 022 for fuel immersion (please consult us)

© 2013 - SOURIAU

Ordering information

Basic series	8LT	0	-	13	B	35	P	N			L

Shell type
- **0:** Square flange receptacle
- **1:** In line receptacle
- **2:** Short square flange receptacle, not accepting backshell
- **3:** Square flange receptacle (rear mounting)
- **5:** Plug with RFI shielding
- **7:** Jam nut receptacle
- **15:** Plug with RFI shielding, not accepting backshell

Type
- **-:** Connector with standard crimp contacts
- **L:** Connector with long PC tail (male and female #22D)
- **M:** Connector with medium PC tail (please see page 38)
- **C:** Connector with short spill (male and female #22D, #20, #16, #12, #8 quadrax)
- **T:** Connector with male contact size 20 for wire wrap (2 wraps)
- **W:** Connector with male contact size 22D for wire wrap (3 wraps)
- **S:** Connector with specific PC Tail (male and female #22D only)
- **Q:** Connector with quadrax crimp contacts
- **P:** Connector with solder cup: . Pin: #22D & #16; Socket: #12
  . Socket: #22D & #16; Pin: #12 - Please consult us

Shell size
09; 11; 13; 15; 17; 19; 21; 23; 25

Plating
- **Z:** Black zinc nickel
- **F:** Nickel
- **B:** Olive green cadmium
- **ZC:** Green zinc cobalt

Contact layout
See tables pages 8 to 11

Contact type
- **P:** Male
- **A:** Connector supplied less pin contact or with specific contacts (Connector marking : A + orientation)
- **S:** Female
- **B:** Connector supplied less socket contact or with specific contacts (Connector marking : B + orientation)

Orientation (1)
N, A, B, C, D see table page 48

Specifications
- **None:** Supplied with contact
- **046:** PC Tail contact with tinned plating
- **251:** Connector provided with power contacts with layout contacts #8
- **022:** Fuel tank Please consult us
- 284: Quadrax grounded PC tail contact, type L, C & S only (100Ω) (2)(3)
- **308:** Quadrax not grounded PC tail contact, type L, C & S only (100Ω) (2)
- **620:** Quadrax grounded crimp contact, type Q only (100Ω) (2)(3)
- **621:** Quadrax not grounded crimp contact, type Q only (100Ω) (2)
- **384:** Quadrax grounded crimp contact, type Q only (150Ω) (2)(3)
- **408:** Quadrax not grounded crimp contact, type Q only (150Ω) (2)

Special custom
- **None:** Standard plastic cap
- **M:** Antistatic plastic cap

L: For P or S contact type only, connector delivered without contacts, connector marking P or S (without L)

(1) Orientations B & C not developped for shell size number 9.
(2) Type shell 0, 3 and 5 available only.
(3) Excepted mixed layouts with quadrax and signal contacts. Please consult us.

© 2013 - SOURIAU

MIL-DTL-38999 connector part numbers

Basic series	MS	27466	T	13	B	35	P			L

Shell type
- **27466:** Square flange receptacle (front mounting)
- **27656:** Square flange receptacle (rear mounting)
- **27468:** Jam nut receptacle
- **27467:** Plug with RFI shielding
- **27505:** Square flange receptacle, not accepting backshell

Class
- **E:** Without thread for back fitting, not accepting backshell for MS27505 and MS27467 only
- **T:** With thread for backfitting, supplied without backshell (excepted MS27505)

Shell size
- **09; 11; 13; 15; 17; 19; 21; 23; 25**

Plating
- **Z:** Black zinc nickel **F:** Nickel **B:** Olive green cadmium

Contact layout
- See tables pages 8 to 11

Contact type
- **P:** Male **A:** Connector supplied less pin contact or with specific contacts (Connector marking : A + orientation)
- **S:** Female **B:** Connector supplied less socket contact or with specific contacts (Connector marking : B + orientation)

Orientation (1)
- **None:** Normal (N)
- **A, B, C, D** see table page 48

Special custom
- **None:** Standard plastic cap
- **M:** Antistatic plastic cap

L: For P or S contact type only, connector delivered without contacts, connector marking P or S (without L)

HE 308 connector part numbers

Basic series	HE308	00	T	13	35	P	N	7	M		L

Shell type
- **00:** Square flange receptacle
- **07:** Jam nut receptacle
- **06:** Plug with RFI shielding
- **11:** Jam nut receptacle with PC Tail contacts

Class
- **T:** Sealed

Shell size
- **09; 11; 13; 15; 17; 19; 21; 23; 25**

Contact layout
- See tables pages 8 to 11

Contact type
- **P:** Male
- **S:** Female

Orientation (1)
- **N, A, B, C, D** see table page 48

Plating
- **6:** Nickel
- **7:** Olive green cadmium

Contractual spécification

Special custom
- **None:** Standard plastic cap
- **M:** Antistatic plastic cap

Specification
- **None:** Connector supplied with contact
- **L:** Connector supplied without contact

(1) Orientations B & C not developped for shell size number 9.

© 2013 - SOURIAU

Dimensions

Type 0 - Square flange receptacle



Shell size	A		B		ØC		D		E		F	ØG		ØH Min	J	K ±0.15
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max		Min	Max			
09	15.93	16.05	13.23	13.49	14.40	14.53	2.14	2.54	23.70	24.30	18.26	3.25	3.35	15.70	18.26	3.25
11					17.65	17.78			26.05	26.70	20.62			18.70	20.62	
13					21.40	21.59			28.50	29.05	23.01			21.80	23.01	
15					24.65	24.77			30.85	31.45	24.61			25.00	24.61	
17					27.82	27.94			33.20	33.80	26.97			28.30	26.97	
19					29.24	30.66			36.40	37.00	29.36			31.00	29.36	
21	15.17	15.29			33.70	33.83	2.90	3.30	39.55	40.15	31.75			34.20	31.75	
23					36.92	37.00			42.75	43.35	34.93	3.73	3.83	37.30	34.92	3.91
25					40.06	40.18			46.00	46.50	38.10			40.50	38.10	

Type 1 - Cable connecting receptacle



Shell size	A		B		ØC		D		E		ØF	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
9	15.93	16.05	13.23	13.49	14.40	14.53	2.14	2.54	18.35	18.92	21.80	22.35
11					17.65	17.78			21.65	22.22	25.10	25.65
13					21.40	21.59			25.05	25.62	28.50	29.05
15					24.65	24.77			27.25	27.82	30.70	31.25
17					27.82	27.94			30.78	31.35	34.10	34.65
19					29.24	30.66			34.05	34.62	37.50	38.05
21	15.17	15.29			33.70	33.83	2.90	3.30	37.45	38.02	40.90	41.45
23					36.92	37.00			41.45	42.02	44.90	45.45
25					40.06	40.18			45.93	46.50	49.40	49.95

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Type 3 - Square flange receptacle (rear mounting)



Shell size	A		B		ØC		D		E		F	ØG		ØH Min	J	K ±0.15
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max		Min	Max			
09	20.71	20.83	10.40	11.90	14.40	14.53	2.14	2.54	23.70	24.30	18.26	3.25	3.35	16.66	18.26	3.25
11					17.65	17.78			26.05	26.70	20.62			20.22	20.62	
13					21.40	21.59			28.50	29.05	23.01			23.42	23.01	
15					24.65	24.77			30.85	31.45	24.61			26.59	24.61	
17					27.82	27.94			33.20	33.8	26.97			30.96	26.97	
19					29.24	30.66			36.40	37.00	29.36			32.94	29.36	
21	19.96	20.08	11.15	12.70	33.70	33.83	2.90	3.30	39.55	40.15	31.75	3.73	3.83	36.12	31.75	3.91
23					36.92	37.00			42.75	43.35	34.93			39.29	34.92	
25					40.06	40.18			46.00	46.50	38.10			42.47	38.10	

Type 7 - Jam nut receptacle
Type 11 - HE 308



Shell size	F		E		ØC		ØG		A		B		D		ØH	J
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max		
09	26.60	27.35	21.95	22.35	14.40	14.53	29.90	30.58	23.12	23.36	8.18	8.32	2.60	3.00	17.78	17.02
11	31.40	32.10	25.15	25.55	17.65	17.78	34.60	35.30							20.96	19.59
13	34.60	35.31	29.80	30.30	21.40	21.59	37.75	38.50							25.65	24.26
15	37.80	38.49	33.05	33.45	24.65	24.77	41.00	41.65							28.83	27.56
17	40.90	41.63	36.25	36.65	27.82	27.94	44.11	44.85							32.00	30.73
19	45.63	46.37	39.40	39.80	29.24	30.66	48.90	49.60					3.35	3.79	35.18	33.91
21	48.84	49.58	42.60	43.00	33.70	33.83	52.00	52.75							38.35	37.08
23	52.02	52.76	45.75	46.15	36.92	37.00	55.30	55.94							41.53	40.26
25	55.19	55.93	50.65	50.95	40.06	40.18	58.40	59.10							44.70	43.45

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Type 2 - Short square flange receptacle (not accepting backshell)







Shell size	A		B		ØC		ØD		E		F	G		ØH		J	ØK	ØL
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max		Min	Max	Min	Max			
09	20.71	20.83	5.40	5.55	14.40	14.53	9.85	9.95	2.14	2.54	18.26	23.70	24.30	3.25	3.35	18.26	16.66	3.25
11					17.65	17.78	12.80	12.90			20.62	26.05	26.70			20.62	20.22	
13					21.40	21.59	16.00	16.10			23.01	28.50	29.05			23.01	23.42	
15					24.65	24.77	18.95	19.05			24.61	30.85	31.45			24.61	26.59	
17					27.82	27.94	22.10	22.20			26.97	33.20	33.80			26.97	30.96	
19					29.24	30.66	25.10	25.20			29.36	36.40	37.00			29.36	32.94	
21	19.96	20.08	6.15	6.35	33.70	33.83	28.25	28.35	2.90	3.30	31.75	39.55	40.15			31.75	36.12	
23					36.92	37.00	31.40	31.50			34.93	42.75	43.35	3.73	3.83	34.92	39.29	3.91
25					40.06	40.18	34.60	34.70			38.10	46.00	46.50			38.10	42.47	

Type 5 - Plug with RFI shielding
Type 15 - Plug with RFI shielding (not accepting backshell)



Type 5



Type 5 and 15



Type 15

Shell size		09	11	13	15	17	19	21	23	25
A	Max	21.80	25.00	29.30	32.50	35.70	38.50	41.70	43.85	48.00
B	Min	31.28	31.28	31.28	31.28	31.28	31.28	31.28	31.28	31.28
	Max	31.35	31.35	31.35	31.35	31.35	31.35	31.35	31.35	31.35

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Detail



Sealing bushing
used for triaxial
#8 protude

Shell Type	Type 0	Type 1	Type 3	Type 5	Type 7
L max	13.39	13.58	13.58	13.54	13.58

Mated connectors dimensions

Square flange receptacle (type 0) with plug (type 5)



Jam nut receptacle (type 7) with plug (type 5)



Shell Size	A Max	B Max	C Max	D Max
09	33.30	47.40	40.60	54.70
11				
13				
15				
17				
19				
21	32.50	46.70		
23				
25				

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Receptacle with PC Tail contact

Type 0
Square flange receptacle



Type 2
Short square flange receptacle



Type 3
Square flange receptacle (rear mounting)



Type 7
Jam nut receptacle



(1) M: Male Contact
F: Female Contact

(2) C: Short PC tail
M: Medium PC tail
L: Long PC tail
S: Specific PC tail

Shell Size					09	11	13	15	17	19	21	23	25
	Contact size	Contact type (1)	PC tail contact (2)										
ØA	#22D	M & F	C & L		0.70								
			S		0.50								
		M	M		0.50								
	#20	M & F	C		0.70								
	#16	M & F	C		1.15								
B	#22D	M & F	C		$4^{\ 0}_{0.20}$								
			S		$5^{\pm 0.1}$								
			L		$8.5^{\ 0}_{0.20}$								
		M	M		$6^{\pm 0.1}$								
	#20	M & F	C		$5^{\pm 0.1}$								
	#16	M & F	C		$5^{\pm 0.1}$								
C type 7	8LT #22D	M	C & L	Max	10.06								
				Min	9.07								
			M	Max	10.21								
				Min	9.23								
		F	C & L	Max	10.06								
				Min	8.74								
	8LT7S HE308 #22D	M	S	Max	10.23								
				Min	9.24								
		F	S	Max	10.23								
				Min	8.91								
	8LT/HE308 #20 & #16	M & F	C	Max	10.23								
				Min	9.24								
D type 0	#22D	M	C & L	Max	15.08								
				Min	13.91								
			M	Max	15.22								
				Min	14.05								
		F	C & L	Max	15.08								
				Min	13.58								
		M	S	Max	15.25	–							15.25
				Min	14.08	–							14.08
		F	S	Max	15.25	–							15.25
				Min	13.75	–							13.75
	#20 & #16	M & F	C	Max	15.25								
				Min	14.08								
E type 2 type 3	#22D	M	C & L	Max	12.47						13.22		
				Min	11.60						12.35		
		F	C & L	Max	12.47						13.22		
				Min	11.27						12.02		
		M	S	Max	12.64	–				12.64	13.39		
				Min	11.77	–				11.77	12.52		
		F	S	Max	12.64	–				12.64	13.39		
				Min	11.44	–				11.44	12.19		
	#20 & #16	M & F	C	Max	12.64						13.39		
				Min	11.77						12.52		

Type 7 receptacle with wire wrap contacts



Contact size	Contact type	A	B Max
#22D	W (3 wraps)	9.07 / 10.06	16.00
#20	T (2 wraps)	9.7 / 10.06	12.60

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Aluminum backshells

Ordering information

Basic Series	8T	AB	05	A	16	W	S	01	-

Accessories type

Type:
- **01:** Backnut
- **02:** Cable clamp
- **03:** Shrink boot
- **04:** Crimp ring
- **05:** Band lock
- **06:** Double cone

Angle:
- **A:** Straight
- **B:** 90° (Type 02 only)

Size code:
08, 10, 12, 14, 16, 18, 20, 22, 24

Size code	08	10	12	14	16	18	20	22	24
= Shell size 8LT	09	11	13	15	17	19	21	23	25

Finish:
- **Z:** Black zinc nickel
- **W:** Olive green cadmium
- **F:** Nickel
- **A:** Black anodized

Self locking option:
- **None**
- **S:** Self locking (available for Types 01 & 02 - mandatory for Type 05)

Cable entry (Type 05 only):
- **01, 02** (02 mandatory for shell size 08 & 10)

Drain hole option:
- **None**
- **D:** Drain hole (Type 03 only)

Dimensions

Aluminum backshell Type 01 - Backnut



Shell size	ØA Min	ØB Max
09	6.7	17.9
11	9.95	20.9
13	12.85	24.3
15	17.0	27.9
17	19.25	31.3
19	21.7	35.3
21	24.7	38.1
23	27.8	41.5
25	32.0	44.5

Thread: See page 27 for information.

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Aluminum backshell Type 02 - Cable clamp

A Angle - straight





B Angle - 90°





Thread: See page 27 for information.

Shell size	ØA		ØB Max	C Max	D Max	E Max	F Max
	Min	Max					
09	2.49	5.94	17.9	21.5	23.1	29.5	20
11	3.89	5.94	20.9	21.5	23.1	29.5	21.5
13	4.83	8.33	24.3	24.5	25.6	31.5	23.5
15	6.60	11.61	27.9	27.5	26.9	35.8	25.5
17	7.19	15.6	31.3	31.5	29.4	40.1	27.5
19	8.26	16.1	35.3	35.5	35.8	40.6	30.5
21	8.71	17.73	38.1	37	38.3	42.7	31.5
23	9.68	20.9	41.5	40.5	42.1	46.2	34.5
25	10.62	21.67	44.5	45	44.7	49	36.5

Aluminum backshell Type 03 - Shrink boot



Shell size	ØA Min	ØB Max	C Max
09	6.7	19.0	11.3
11	9.95	21.5	14.9
13	12.85	25.3	17.8
15	16.05	29.1	21.27
17	19.2	31.7	24.3
19	21.5	35.5	26.4
21	24.7	39.3	30.8
23	27.8	41.8	34.1
25	31	46.9	36.6

Thread: See page 27 for information.

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Aluminum backshell Type 04 - Crimp ring



Shell size	ØA Min	ØB Max
09	6	17.9
11	8.2	20.9
13	10.5	24.3
15	13.6	27.9
17	16.9	31.3
19	20	34.3
21	23.2	38.1
23	26.1	41.5
25	28.1	44.4

Thread: See page 27 for information.

Aluminum backshell Type 05 - Band lock



Shell size	ØA Max - Entry size		ØB Max
	01	02	
09	-	6.6	17.9
11	-	8	24.9
13	8	11.2	29.3
15	11.2	14.4	32.4
17	12.8	16	35.6
19	16	19.1	38.4
21	16	20.7	41.6
23	17.6	23.9	44.8
25	19.1	25.5	47.9

Thread: See page 27 for information.

Aluminum backshell Type 06 - Double cone

HE 308 standard - Screen termination and heat shrink boot



Shell size	ØA$^{\pm 0.07}$	ØB$^{\pm 0.12}$	ØC$^{\pm 0.12}$	D$^{\pm 0.07}$
09	7.1	15.55	19.35	16.7
11	10.25	18.45	23.35	20.7
13	13.05	21.85	25.35	22.7
15	15.25	25.05	28.35	25.7
17	18.45	28.05	31.35	28.7
19	20.65	31.05	34.35	31.7
21	23.85	34.45	38.35	35.7
23	26.95	37.45	41.35	38.7
25	30.15	40.75	44.35	41.7

Thread: See page 27 for information.

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Thread information

Shell size	UNEF Thread
09	7/16-28 2B
11	9/16-24 2B
13	11/16-24 2B
15	13/16-20 2B
17	15/16-20 2B
19	1 1/16 -18 2B
21	1 3/16 -18 2B
23	1 5/16 -18 2B
25	1 7/16 -18 2B

Recommended installation torque

Shell Size	Installation Torque (Inch-Pounds)
09	40
11	40
13	40
15	40
17	40
19	40
21	80
23	80
25	80

Note: Torque values are based on 80% of the coupling thread strength specified in SAE-AS85049 standard.

Band-it

Designation	Flat stainless steel standard band	Pre-coiled stainless steel standard band	Hand banding tool
Part number	8599-9344	8599-9345	8599-9346





MIL specification

For aluminum bachshells MIL specification, please consult us.

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Rack and Panel

- Signal and Power connector
- Easy and fast connection without any coupling/uncoupling between a float-mounting unit and a fixed unit.
- 100% scoop proof
- Plug misalignment allowed
- Rear accessories available
- 8 shell sizes available: from 11 to 23 with DTAT-C5935-X0005 layout - including power contact cavities
- Sealing as per HE 308
- EMI performances as per DTAT-C5935-X0005

Shell Size	Mated Force (daN)	Unmatted Force (daN)
11	20	12
13	30	13
15	35	15
17	50	16
19	55	18
21	65	22
23	80	27
25	-	-

Blind mateable connector



Just push to connect... and release to disconnect

Superior misalignment allowances



Axial ±1mm



Angular ±1mm



Longitudinal 0/-0.5mm

© 2013 - SOURIAU

Rack and Panel - Ordering information

Souriau Rack and Panel connectors part numbers

Basic series	8LT	27	-	15	B	35	P	N			L

Shell type
27: Receptacle for rack, for male contacts, with possibility to mount rear accessory
23: Square flange receptacle (consult us)
26: Floating plug for rack, for crimp female contacts, with possibility to mount rear accessory

Type
-: Connector with standard crimp contacts
Q: Connector with quadrax crimp contacts
C: Connector with short PC tail (male and female #20, #16, #12, #8 quadrax)
S: Connector with specific PC tail (male and female #22D only)
L: Connector with long PC tail (male and female #22D)

Shell size: 11, 13, 15, 17, 19, 21, 23, 25

Plating
F: Nickel **B:** Olive green cadmium

Contact layout: See tables pages 8 to 11

Contact type
P: Male **S:** Female

Orientation: N

Specification
None: Supplied with contacts
251: Connector provided with power contacts (for layout with cavities #8)
***284:** Quadrax grounded (cts 100Ω)
308: Quadrax not grounded (cts 100Ω)
***384:** Quadrax grounded (cts 150Ω)
408: Quadrax not grounded (cts 150Ω)

Special custom
None: Standard plastic cap **M:** Antistatic plastic cap

L: Connector supplied without contacts

*Excepted mixted layouts with quadrax and signal contacts. Please consult us.

HE 308 Rack and Panel connectors part numbers

Basic series	HE308	26	T	23	01	P	N	7	M	

Shell type
26: Floating plug for rack, for crimp female contacts, with possibility to mount rear accessory
27: Receptacle for rack, for male contacts, with possibility to mount rear accessory
21: Receptacle for rack with PC Tail contacts

Class
T: Sealed

Shell size: 11, 13, 15, 17, 19, 21, 23

Contact layout: See tables pages 8 to 11

Contact type
P: Male **S:** Female

Orientation: N

Plating
7: Olive green cadmium

Contractual specifications
M: DAT quality insurance

Special custom
None: Standard plastic cap **M:** Antistatic plastic cap

Specifications
None: Connector supplied with contact **L:** Connector supplied without contact

© 2013 - SOURIAU

Rack and Panel - Dimensions

Equipment receptacle (type 27)



Shells	11	13	15	17	19	21	23	25
A Max	15.33	16.92	18.51	20.1	22.67	24.26	25.84	27.43
B Max	32.16	35.34	38.51	41.69	46.43	49.64	52.78	56
C	25.55	30.3	33.45	36.65	39.8	43	46.15	50.95

Square flange receptacle (type 23)



Shells	09	11	13	15	17	19	21	23	25
A Min	23.7	26.05	28.5	30.85	33.2	36.4	39.55	42.75	46
A Max	24.3	26.7	29.05	31.45	33.8	37	40.15	43.35	46.5
B	18.26	20.62	23.01	24.61	26.97	29.36	31.75	34.93	38.1
ØC Min	3.25							3.73	
ØC Max	3.35							3.83	

Rack plug (type 26)



Shells	11	13	15	17	19	21	23	25
A Max	32.1	35.25	38.4	41.6	46.3	49.6	52.7	55.9
B Max	16.92	18.51	20.1	22.67	24.26	25.84	27.43	29.03
C Max	32.16	35.34	38.51	41.69	46.43	49.64	52.78	55.96

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Mated connectors

Plug type 26 & Receptacle type 23



Plug type 26 & Receptacle type 27



*Included longitudinal alignment

Panel cut out





Shell size	Plug			
	A	ØB ±0.1	C Min	ØA
11	12.81	25.58	32.57	2 0 -0.05
13	13.94	28.80	36	
15	15.06	31.98	39.60	
17	16.88	35.15	43.30	
19	18	38.28	47	
21	19.12	41.50	50.60	
23	20.24	44.68	54.20	
25	21.38	47.85	57.45	

Shell size	Receptacle			
	A	ØB ±0.1 0	C Min	ØA
09	10	17.70	27.80	2 0 -0.05
11	11.69	20.86	32.57	
13	12.81	25.58	36	
15	13.94	28.80	39.60	
17	15.06	31.98	43.30	
19	16.88	35.15	47	
21	18	38.28	50.60	
23	19.12	41.50	54.20	
25	20.24	44.68	59.70	

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Cost effective & light hermetics Resin sealed

- Potted receptacle with male or female straight PC tail contacts
- 100% scoop proof: no interference when mating the connector, contacts never touch each other
- Weight saving compared to hermetic version
- Reinforced sealing for harsh environment ($10E^{-7}$ atm.cm³/s)
- Good shock resistance - better than hermetic glass seal
- Female contacts available for the receptacle
- PC Tail from #22D to #16 (for all other contacts please consult us)

Ordering information

Basic Series	8LTR	0	C	09	B	35	P	N
Shell style **0:** Square flange receptacle **1:** In line receptacle **2:** Short square flange receptacle not accepting backshell **3:** Square flange receptacle (rear mounting) **5:** Plug with RFI shielding **7:** Jam nut receptacle **15 :** Plug with RFI shielding not accepting backshell								
Type **C:** Receptacle with short PC tail (male and female #22D, #20, #16) **L:** Connector with long PC tail (male and female #22D) **S:** Connector with specific PC Tail (male and female #22D) **M:** Connector with medium PC tail (male #22D) **P:** Connector with solder cup: . Pin: #22D & #16; Socket: #12 . Socket: #22D & #16; Pin: #12 - Please consult us								
Shell size: 09 - 11 - 13 - 15 - 17 - 19 - 21 - 23 - 25								
Plating **B:** Olive green cadmium **F:** Nickel **ZC:** Green zinc cobalt **Z:** Black zinc nickel								
Contact layouts: see tables pages 8 to 11								
Contact type **P:** Male **S:** Female								
Orientation (1) **N - A - B - C - D** see table page 48								

(1) Orientation B & C not developed for shell size number 9

© 2013 - SOURIAU

8LT Series

8LT Series

Contacts & Tooling

Contacts:

- Crimp contacts 36
- Straight PC tail contacts 38
- Coaxial contacts #12 39
- Solder cup 39
- Crimp contacts: 1500 mating 39
- Wire wrap contacts 39
- Quadrax #8 contacts 39
- Thermocouple contacts 40
- Dummy contacts 40
- Filler plugs 40

Wiring instructions 41

Tooling:

- Crimping tools 42
- Insertion & extraction tools 43
- Backshell tightening tools 43
- Tightening support 43
- Slackening tools 43
- Tightening of fixing nuts, receptacle type 7 43

Crimp contacts

Contact size	Contact type	Souriau Part number (without color code)	MIL-DTL-38999 contacts	
			Part number	Profile and color code
#26	Pin	8599-0297	-	
	Socket	8599-0298	-	
#22D	Pin	8599-0702 JJ	M39029/58 360	Black / Blue / Orange
	Socket	8599-0706 900	M39029/56 348	Grey / Yellow / Orange
#20	Pin	8599-0703 SA	M39029/58 363	 Orange / Blue / Orange
	Socket	8599-0707 900	M39029/56 351	 Brown / Green / Orange
#16	Pin	8599-0704 MJ	M39029/58 364	Yellow / Blue / Orange
	Socket	8599-0708 900	M39029/56 352	Red / Green / Orange
#16 Coaxial	Pin	-	M39029/76 424	Yellow / Red / Yellow
	Socket	-	M39029/77 428	Grey / Red / Yellow
#12	Pin	8599-0705 MJ	M39029/58 365	 Green / Blue / Orange
	Socket	8599-0709 900	M39029/56 353	 Orange / Green / Orange
#12 Coaxial	Pin	-	M39029/102 558	
	Socket	-	M39029/103 559	
	Pin	-	M39029/28 211	
	Socket	-	M39029/75 416	
#10 Power	Pin	-	M39029/58 528	
	Socket	-	M39029/56 527	
#8 Power	Pin	8599-7544 *	-	
	Socket	8599-7541 *	-	
	Pin	8599-7580	-	
	Socket	8599-7581	-	
	Boot	8599-4542	-	For wire #8
		8599-4547	-	For wire #10
	Reductor	8599-7645	-	
#8 Coaxial	Pin	-	M39029/60 367	
	Socket	-	M39029/59 366	
	Boot	8590-4571	-	
#8 Twinax	Pin	-	M39029/90 529	
	Socket	-	M39029/91 530	
	Boot	8590-4571	-	
#4 Power	Pin	8599-7598 900 **	-	For wire 25 mm²
	Socket	8599-7599 900 **	-	
	Pin	8599-7534	-	For wire 21.15 mm²
	Socket	8599-7535	-	
	Boot for cable 16 mm²	8599-4594	-	
	Boot for cable 10 mm²	8599-4593	-	
	Reductor cable 10 mm²	8400-2351A	-	
#4 Power with reduced barrel	Pin	8599-7528 900	-	Mating part #4 / Barrel #6
	Socket	8599-7529 900	-	
	Boot	8599-4593	-	

* JVS only. ** Not included in connector Part number. Must be ordered separately.

© 2013 - SOURIAU

Crimp contacts

Contact size	Contact type	Contact Ø	Conductor section AWG		Conductor section mm²		External Ø over insulator	
			Min	Max	Min	Max	Min	Max
#26	Pin	0.50	30	24	0.055	0.215	0.60	0.83
	Socket							
#22D	Pin	0.76	26	22	0.012	0.34	0.76	1.37
	Socket							
#20	Pin	1.00	24	20	0.21	0.60	1.02	2.11
	Socket							
#16	Pin	1.60	20	16	0.60	1.34	1.65	2.77
	Socket							
#16 Coaxial	Pin		RG 174 RG 179 RG 316				1.65	2.60
	Socket							
#12	Pin	2.40	14	12	1.91	3.18	2.46	3.61
	Socket							
#12 Coaxial	Pin		RG 174 RG 179 RG 316				2.40	2.60
	Socket							
	Pin							
	Socket							
#10 Power	Pin	3.20	Please consult us				-	2.95
	Socket							
#8 Power	Pin	3.64	-	8	-	8.98	-	-
	Socket							
	Boot		-	-	-	-	4.50	6.50
			-	-	-	-	2.50	4
	Reductor		-	-	-	-	-	-
#8 Coaxial	Pin		RG 180 A/U				-	2.80
	Socket							
	Boot							
#8 Twinax	Pin	5.50	0,76MIL-C 17/176 00002 FILECA F.2703/14 RAYCHEM CHEMINAX 10612 FILOTEX M 17/176 00002				3.15	3.40
	Socket							
	Boot							
#4 Power	Pin	5.74	-	3	-	25	-	-
	Socket							
	Pin		5	4	16	21.15	-	-
	Socket							
	Boot (Available for 8599-7534 and 7535 contacts)		-	-	-	-	6.35	7.50
			-	-	-	-	4	5.80
	Reductor cable 10 mm²		-	-	-	-	-	-
#4 Power with reduced barrel	Pin		6		13.3		-	-
	Socket							
	Boot		-	-	-	-	4	5.80

© 2013 - SOURIAU

Straight PC tail contacts

Contact size	Contact type	PC tail type	Part number	Profile
#22D	Pin	L	8599-0720 900	
	Pin	M	8599-8028 900	-
	Pin	C	8599-0730 900	
	Pin	S	8599-0796 900	
	Socket	L	8599-0721 900	
	Socket	C	8599-0731 900	
	Socket	S	8599-0797 900	
#20	Pin	M	8599-0658 JJ	-
	Socket	M	8599-0759 900	-
	Pin	C	8599-0724 900	
	Socket	C	8599-0725 900	
	Pin	L	8599-0771 900	-
	Socket	L	8599-0772 900	-
#16	Pin	C	8599-0726 900	
	Socket	C	8599-0727 900	
Coaxial #16	Pin	C	8599-1000 900	
#12	Pin	C	8599-7929 900	-
	Socket	C	8599-7932 900	-

S: Specific PC tail
L: Long PC tail
M: Medium PC tail
C: Short PC tail

© 2013 - SOURIAU

Coaxial contacts #12

Designation	Part number
Coax socket solder contact #12	THA1-0151A
Coax pin solder contact #12	THA1-0152A
Coax pin crimp contact #12	THA1-0155A
Coax socket crimp contact #12	THA1-0156A

Solder cup

Contact size	Contact type	Part number
#22D	Pin	8599-0750 900
#20	Pin	8599-0077A 900
#16	Pin	8599-7482A 900
#12	Socket	8599-7485A 900

For other contacts type please consult us.

Crimp contacts: 1500 mating

Contact size	MIL-DTL-38999 contacts		
	Contact type	Part number	Color code
#22D	Pin (H)	M39029/107 620	Blue / Red / Black
	Socket (J)	M39029/106 614	Blue / Brown / Yellow
#20	Pin (H)	M39029/107 621	Blue / Red / Brown
	Socket (J)	M39029/106 615	Blue / Brown / Green
#16	Pin (H)	M39029/107 622	Blue / Red / Red
	Socket (J)	M39029/106 616	Blue / Brown / Blue
#12	Pin (H)	M39029/107 623	Blue / Red / Orange
	Socket (J)	M39029/106 617	Blue / Brown / Gray

Wire wrap contacts

Contact size	Contact type	Part number	Contact Ø (mm)	Profile	(mm)
#22D	Pin	8599-0790 JJ	0.76		0.86
#20	Pin	8599-0791 900	1		0.86

Quadrax #8 contacts

Contact type	Version	Souriau Part Number	Cross Norm	T°	Impedance	Sealing	Release
Pin	PCB mount	ETH1-1237A	-	125°C	100Ω	Sealed	Rear
		ETH1-1501A	-		150Ω		
	Crimp	ETH1-1345A	EN3155-074	200°C	100Ω		
		ETH1-1503A	-		150Ω		
Socket	PCB mount	ETH1-1238A	-	125°C	100Ω		
		ETH1-1502A	-		150Ω		
	Crimp	ETH1-1346A	EN3155-075	200°C	100Ω		
		ETH1-1504A	-		150Ω		

© 2013 - SOURIAU

Thermocouple contacts

Contact size	Contact type	Souriau part numbers (without color code)	MIL-DTL-38999 contacts		Ø Contact (mm)	Wire section				Ø Over insulation (mm)	
			Part numbers	Profile and color code		Awg		mm²			
						min	max	min	max	min	max
#22D Chromel	Pin	-	M39029/87-472	 Red / Violet / Yellow	0.75	28	22	0.095	0.34	0.76	1.37
	Socket	-	M39029/88-484	Yellow / Grey / Yellow							
#22D Alumel	Pin	-	M39029/87-471	 Brown / Violet / Yellow							
	Socket	-	M39029/88-483	Orange / Grey / Yellow							
#20 Chromel	Pin	8599-0749 900	8599-0949 900	 Blue / Violet / Yellow	1	24	20	0.21	0.6	1.02	2.11
	Socket	8599-0753 900	8599-0953 900	Grey / Grey / Yellow							
#20 Alumel	Pin	8599-0761 900	8599-0961 900	 Green / Violet / Yellow							
	Socket	8599-0765 900	8599-0965 900	Violet / Grey / Yellow							

Dummy contacts

Size	Part number
#16	8599-6A016001A
#8	8599-0308
#4	8599-0310



8599-0308

Filler plugs

Contact size	Filler plugs		
	MS Part number (Rev. N)	Souriau Part number	Color
#22D	MS27488-22-2	8660-212	Black
#20	MS27488-20-2	8522-389A	Red
#16	MS27488-16-2	8522-390A	Green
#12	MS27488-12-2	8522-391A	Orange



Direction of introduction in grommet

These filler plugs are installed at the rear of unwired contact to maintain connector sealing.

© 2013 - SOURIAU

Wiring instruction

Cable preparation and wire stripping

Contact size	#26	#22D	#20	#16	#12	#8	#4
L	4		6			12	



L = length of wire stripping

Insertion of wire in contact barrel



When inserting the stripped wire into the contact barrel check that no strands are left outside and that the wire is visible through the wire inspection hole in the barrel.

Important:
- Slide any accessories over wire strands before carrying out the following operations.
- Contacts are inserted and extracted from the rear of the connector.

Insertion of the contacts

1 - Engage the crimp cable / contact asembly into the longitudinal slot of the plastic tool (coloured tip).
Slide the tool down the cable until the tip of the tool abuts the contact retention shoulder.



2 - Introduce the contact into the required contact cavity in the insulator, pushing tool axialy, until the contact snaps into position in clip.



3 - Withdraw the tool (from rear). Check that contact is firmly locked by pulling wire gently.
When connector is fully loaded, check the position of contact tips. They should all be in the same plane.
Nota: For larger sizes of cable which are stiff enough manual insertion without tool is preferable.

Extraction of the contacts

1 - Engage the appropriate cable into the longitudinal slot of the tool with the white tip towards connector.

2 - Slide the tool down towards the contact. Insert the tool in the insulator until it abuts the contact shoulder.



3 - Holding the tool-contact and cable assembly together, remove them simultaneously.



© 2013 - SOURIAU

Tooling

Crimping tools

Contact size	Contact type	Plier M22520/1-01		Plier M22520/2-01 (Souriau 8476-01)		Plier M300BT	Plier * M22520/23-01	
		Turret Part number		Locator Part number		Locator Part number	Turret Part number	Locator Part number
		Norm	Souriau	Norm	Souriau			
#26	Pin	-	-	-	8599-0397	-	-	-
	Socket	-	-	-	8599-0398	-	-	-
#22D	Pin	-	-	M22520/2-09	8476-09	-	-	-
	Socket	-	-	M22520/2-07	8476-07	-	-	-
#20	Pin	M22520/1-04	8365-04	M22520/2-10	8476-10	-	-	-
	Socket					-	-	-
#16	Pin	M22520/1-04	8365-04	-	-	-	-	-
	Socket			-	-	-	-	-
#12	Pin	M22520/1-04	8365-04	-	-	-	-	-
	Socket			-	-	-	-	-
#8 Power	Pin	-	-	-	-	SP 593	M22520/23-02	8599-9601
	Socket	-	-	-	-			
#4 Power	pin	-	-	-	-	-	M22520/23-04	M22520/23-11
	Socket	-	-	-	-	-		

Contact size	Contact type	Plier M22520/2-01 (Souriau 8476-01)	Plier M22520/31-01	Plier M22520/4-01	Plier M22520/5-01
		Locator Part Number	Locator Part number	Locator Part Number	Die set Part Number
#12 Coaxial M39029/102-558 M39029/103-559	Inner	-	-	-	M22520/5-03
	Outer	-	-	-	
#12 Coaxial M39029/28-211 M39029/75-416	Inner	M22520/2-34	-		
	Outer	-	M22520/31-02	-	-
#16 Coaxial	Inner	M22520/2-35	-	-	-
	Outer	-	-	M22520/4-02	-
#8 Coaxial	Inner	M22520/2-31	-	-	-
	Outer	-	-	-	M22520/5-05 closure B
#8 Triaxial	Inner	K709	-	-	-
	Middle	-	-	-	y631 closure B
	Ferrule	-	-	-	y631 closure A

* Pneumatic plier
Note: for the #10 contact's plier and locator, please consult us.

© 2013 - SOURIAU

Insertion & extraction tools

Contact size	Material	Part number		Color	
		MIL standard	Souriau	Insertion	Extraction
#26	Plastic	-	8599-0399 900	Black	White
#22D	Plastic	M81969/14-01	-	Green	White
#20	Plastic	M81969/14-10	-	Red	Orange
#16	Plastic	M81969/14-03	-	Blue	White
#12	Plastic	M81969/14-04	-	Yellow	White
#10	Plastic	M81969/14-05	-	Grey	-
#8	Plastic	M81969/14-12	-	-	Green
	Metalic	-	8660-197	-	-
#4	Plastic	M81969/14-07	-	-	Blue
	Metalic	-	8533-8175	-	-

Backshell tightening tools

8498-03



Backshell tightening pliers,
part number: **8498-03**
Square jaws (order 2 jaws),
part number: **8500-1015**

Tightening of rear accessories:

Shell size	9	11	13	15	17	19	21	23	25
Max torque in m/daN	0.62						1.24		

Tightening support

8599-0801



Part number: **8599-0801**
This tool is made up of dummy receptacles housings of all 9 sizes for all key polarisation, and secures free connectors during wiring and fitting of rear accessories.

Slackening tools

8498-04

Strap clamp,
part number: **8498-04**
Spare strap,
part number: **8498-103**

Tightening of fixing nuts, receptacle type 7

Shell size	09	11	13	15	17	19	21	23	25
Nut dimension across flats	22.35	25.55	30.30	33.45	36.65	39.80	43.00	46.10	50.95
Max tightening torque on nut (mN)	6	8	10	13	20	23	25	26	28

© 2013 - SOURIAU

8LT Series

8LT Series

Common Section

- Protective caps 46
- Reductors 47
- Boots 48
- Orientations 48
- Panel gasket 49
- Dummy receptacles 49
- Cross reference list 50
- Coordinates information 52

Protective caps

Metalic protective caps - Dimensions

Metalic protective cap for receptacles



Metalic protective cap for plugs



Shell size	ØA Max	B Max	ØC Max	D Max	ØE Min	ØF Min	G	H±5	J±5	K±5
09	21.80	28.00	20.80	29.50	3.20	17.80	76	105	200	160
11	24.90		23.80			21.30				
13	29.40		27.70			25.70	89			
15	32.50		30.20			29.00				
17	35.80		33.50			32.00				
19	38.60		36.50			35.30				
21	41.90		39.80			38.40	102			
23	44.90		42.90			41.70				
25	48.00		46.20			44.70				

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Protective caps

Metalic protective caps - Ordering

Basic series	8LT	E	01	B	13

Cap type
- **E:** Cap for receptacle
- **F:** Cap for plug

Fixing type

Cap for receptacle	Cap for plug
01: Plastic sleeved metal cord with eyelet	**01:** Plastic sleeved metal cord with eyelet
02: Plastic sleeved metal cord with ring	**03:** Nylon cord without fastener
04: Nylon cord with eyelet	**05:** Nylon cord with eyelet
06: Nylon cord with ring	**07:** Nylon cord with strap
10: Black nylon cord with eyelet	

Plating
- **B:** Olive green cadmium
- **F:** Nickel

Shell size:
09 - 11 - 13 - 15 - 17 - 19 - 21 - 23 - 25

Plastic protective caps

Shell size	Part numbers for standard cap		Part numbers for antistatic cap	
	Caps for receptacle	Caps for plug	Caps for receptacle	Caps for plug
09	8500-5594	70609	MS90376-10RF	MS90376-14RF
11	MS90376-12R	MS90376-16Y	MS90376-12RF	MS90376-16RF
13	8500-5588A	8500-5600	8500-5588N	8500-5600N
15	8500-5589A	8500-5601	MS90376-18YF	8500-5601N
17	MS90376-20YF	8500-5602	MS90376-20YF	8500-5602N
19	8500-5601	8500-5592A	8500-5601N	8500-5592N
21	8500-5602	8500-5593A	8500-5602N	8500-5593N
23	MS90376-24R	MS90376-24R	MS90376-24RF	-
25	8500-5593A	J599ABC6009A00	8500-5593N	-

Reductors

Reductor Size	Part number	For cable	For pin contacts	For socket contacts
#8 Power	8599-7645	#10	8599-7580	8599-7581
#4 Power	8400-2352A	10 mm^2	8599-7534A	8599-7535A

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

Boots

Boot Size	Part number	Admissible wire section mm²		For cable
#8 Power	8599-4542	5	6.5	8.48 à 10 mm²
	8599-4547	2.5	4	#10
#4 Power	8599-4594	6.35	7.5	#4 - #5
	8599-4593	4	5.8	#6 - #8

Orientations

Polarization is determined by the master keyway position.
The secondary keyway positions remain fixed.

View from front face of receptacle

View from front face of plug



Shell size	Angles (degrees)				
	N	A	B	C	D
09	95	77	-	-	113
11	95	81	67	123	109
13	95	75	63	127	115
15	95	74	61	129	116
17	95	77	65	125	113
19	95	77	65	125	113
21	95	77	65	125	113
23	95	80	69	121	110
25	95	80	69	121	110

© 2013 - SOURIAU

Panel gasket

Shell size	Part numbers	
	Gasket for receptacle type 0, 2, 3 (to be ordered separately)	O ring for receptacle type 7 (shipped with connector)
09	8599-5541	AS3582-019
11	8599-5542	AS3582-022
13	8599-5543	AS3582-024
15	8599-5544	AS3582-026
17	8599-5545	AS3582-028
19	8599-5546	AS3582-128
21	8599-5547	AS3582-130
23	8599-5548	AS3582-132
25	8599-5549	AS3582-134

Dummy receptacles



Shell size	Part numbers*	A Max	B Max	ØC Max	D Max	E	ØF
09	8LT0-09GUR	16.05	2.54	14.53	24.25	18.26	3.25
	8LT0-09FUR						
11	8LT0-11GUR	16.05	2.54	17.78	26.60	20.62	3.25
	8LT0-11FUR						
13	8LT0-13GUR	16.05	2.54	21.59	29.00	23.01	3.25
	8LT0-13FUR						
15	8LT0-15GUR	16.05	2.54	24.77	31.35	24.61	3.25
	8LT0-15FUR						
17	8LT0-17GUR	16.05	2.54	27.94	33.75	26.97	3.25
	8LT0-17FUR						
19	8LT0-19GUR	16.05	2.54	30.66	36.90	29.36	3.25
	8LT0-19FUR						
21	8LT0-21GUR	15.29	3.30	33.83	40.10	31.75	3.25
	8LT0-21FUR						
23	8LT0-23GUR	15.29	3.30	37.00	43.25	34.93	3.73
	8LT0-23FUR						
25	8LT0-25GUR	15.29	3.30	40.18	46.50	38.10	3.73
	8LT0-25FUR						

** F or G = Plating.*

Note: All dimensions are in millimeters (mm)

© 2013 - SOURIAU

Cross reference list :
Part Numbers Souriau and Specifications : NFC 93422 / MIL DTL 38999

Connectors

SOURIAU	NFC 93422 HE 308	MIL DTL 38999 Serie I	Designation
8LT0●●B●●P/SN 8LT0●●F●●P/SN	HE30800T●●●●P/SN7 M HE30800T●●●●P/SN6 M	MS27466T●●B●●P/S●* MS27466T●●F●●P/S●*	Square flange receptacle
8LT1●●B●●P/SN 8LT1●●F●●P/SN	- -	- -	Cable connecting receptacle
8LT2●●B●●P/SN 8LT2●●F●●P/SN	- -	MS27505E●●B●●P/S●* MS27505E●●F●●P/S●*	Square flange receptacle not accepting backshell
8LT3●●B●●P/SN 8LT3●●F●●P/SN	- -	MS27656T●●B●●P/S●* MS27656T●●F●●P/S●*	Square flange receptacle (rear mounting)
8LT5●●B●●P/SN 8LT5●●F●●P/SN	HE30806T●●●●P/SN7 M HE30806T●●●●P/SN6 M	MS27467T●●B●●P/S●* MS27467T●●F●●P/S●*	Plug with RFI shielding
8LT15●●B●●P/SN 8LT15●●F●●P/SN	- -	MS27467E●●B●●P/S●* MS27467E●●F●●P/S●*	Plug with RFI shielding not accepting backshell
8LT7●●B●●P/SN 8LT7●●F●●P/SN	HE30807T●●●●P/SN7 M HE30807T●●●●P/SN6 M	MS27468T●●B●●P/S●* MS27468T●●F●●P/S●*	Jam nut receptacle
8LT7S●●B●●P/SN (#22D) 8LT7S●●F●●P/SN (#22D)	HE30811T●●●●P/SN7 M HE30811T●●●●P/SN6 M	- -	Jam nut receptacle with PC Tail contacts
8LT7C●●B●●P/SN (#20, #16, #12) 8LT7C●●F●●P/SN (#20, #16, #12)	HE30811T●●●●P/SN7 M HE30811T●●●●P/SN6 M	- -	Jam nut receptacle with PC Tail contacts
8LT26●●B●●P/SN 8LT26●●F●●P/SN	HE30826T●●●●P/SN7 M -	- -	Floating plug for rack HE308
8LT27●●B●●P/SN 8LT27●●F●●P/SN	HE30827T●●●●P/SN7 M -	- -	Receptacle for rack HE308 with possibility to mount rear accessories
8LT27S●●B●●P/SN (#22D) 8LT27C●●B●●P/SN (#20, #16, #12)	HE30821T●●●●P/SN7 M HE30821T●●●●P/SN7 M	- -	Receptacle for rack HE308 with PC Tail contacts
8LT23●●B●●P/SN	-	-	Square flange receptacle

* Standard P/S : . None = N position,
. Use A,B,C,D for other orientations

Backshells

SOURIAU	NFC 93422 HE 308	MIL DTL 38999 Serie I	Designation
8LST●●●B01 8LST●●●F01	- -	M8504927●●W M8504927●●N	Backnut
8LST●●●B02 8LST●●●F02 8LST●●●G02	- HE308-11●●26 HE308-11●●27	- - -	Straight cable clamp
8LST●●●B03 8LST●●●F03 8LST●●●G03	- HE308-12●●26 HE308-12●●27	- - -	Elbow cable clamp
8LST●●●B071 8LST●●●F071	HE308-13●●17 HE308-13●●16	- -	Backshell for screen termination and heatshrink sleeving

© 2013 - SOURIAU

Caps

SOURIAU	NFC 93422 / HE 308	MIL-DTL-38999 Series I	Designation
8LTE04B●● 8LTE04F●●	HE308-B00●●7 HE308-B00●●6	- -	Cap for square flange receptacle
8LTE06B●● 8LTE06F●●	HE308-B07●●7 HE308-B07●●6	- -	Cap for jam nut receptacle
8LTF05B●● 8LTF05F●●	HE308-B16●●7 HE308-B16●●6	- -	Cap for plug
8LTF07B●● 8LTF07F●●	HE308-B06●●7 HE308-B06●●6	- -	Cap for plug
8LTE01B●● 8LTE01F●●	- -	MS27502B●●C MS27502F●●C	Cap for receptacle
8LTE02B●● 8LTE02F●●	- -	MS27502B●●N MS27502F●●N	Cap for receptacle
8LTF01B●● 8LTF01F●●	- -	MS27501B●●C MS27501F●●C	Cap for plug

Contacts

See page 35

© 2013 - SOURIAU

Coordinates for straight PC tail terminations

Viewed from front face of male insulator

Hole sizes: 1mm min. (#22 and #20 contacts) and 1.3mm min. (#16 contact) coordinates in mm.

09 / A

12



Ctc	x	y
1	+0.92	+2.54
2	+2.34	+1.35
3	+2.66	-0.47
4	+1.74	-2.07
5	0.00	-2.70
6	-1.74	-2.07

Ctc	x	y
7	-2.66	-0.47
8	-2.34	+1.35
9	-0.92	+2.54
10	0.00	+1.03
11	+0.89	-0.51
12	-0.89	-0.51

35



Ctc	x	y
1	+1.14	+1.98
2	+1.98	-1.14
3	0.00	-2.29
4	+1.98	-1.14
5	+1.14	+1.98
6	0.00	0.00

98



Ctc	x	y
A	+1.65	+0.97
B	0.00	-1.90
C	-1.65	+0.97

11 / B

02



Ctc	x	y
A	0.00	+2.41
B	0.00	-2.41

04



Ctc	x	y
A	+1.65	+1.65
B	+1.65	-1.65
C	-1.65	-1.65
D	-1.65	+1.65

05



Ctc	x	y
A	+1.65	+1.42
B	+2.86	-1.65
C	0.00	-3.30
D	-2.86	-1.65
E	-1.65	+1.42

26



Ctc	x	y
1	+1.69	+3.79
2	+3.09	+2.77
3	+3.95	+1.28
4	+4.13	-0.44
5	+3.58	-2.10
6	+2.40	-3.37
7	0.00	-4.13
8	-2.40	-3.37
9	-3.58	-2.10
10	-4.13	-0.44
11	-3.95	+1.28
12	-3.09	+2.77
13	-1.69	+3.79

Ctc	x	y
14	0.00	+3.50
15	+1.70	+1.76
16	+2.55	+0.29
17	+1.70	-1.18
18	+0.85	-2.65
19	-0.85	-2.65
20	-1.70	-1.18
21	-2.55	+0.29
22	-1.70	+1.76
23	0.00	+1.76
24	+0.85	+0.29
25	0.00	-1.18
26	-0.85	+0.29

35



Ctc	x	y
1	0.00	+3.71
2	+2.16	+3.00
3	+3.51	+1.14
4	+3.51	-1.14
5	+2.16	-3.00

Ctc	x	y
6	0.00	-3.71
7	-2.16	-3.00
8	-3.51	-1.14
9	-3.51	+1.14

Ctc	x	y
10	-2.16	+3.00
11	0	+1.42
12	+1.24	-0.89
13	-1.24	-0.89

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

11 / B

98



Ctc	x	y
A	0.00	+3.30
B	+3.30	0.00
C	+1.65	-2.87
D	-1.65	-2.87
E	-3.30	0.00
F	0.00	0.00

99



Ctc	x	y
A	+1.65	+2.85
B	+3.30	0.00
C	+1.65	-2.87
D	-1.65	-2.87
E	-3.30	0.00
F	-1.65	+2.87
G	0.00	0.00

13 / C

04



Ctc	x	y
A	0.00	+3.81
B	+3.71	+0.89
C	0.00	-2.11
D	-3.71	+0.89

08



Ctc	x	y
A	+1.65	+3.99
B	+4.32	0.00
C	+3.05	-3.05
D	0.00	-4.32
E	-3.05	-3.05
F	-4.32	0.00
G	-1.65	+3.99
H	0.00	+1.12

35



Ctc	x	y
1	+1.14	+5.00
2	+3.20	+4.01
3	+4.62	+2.24
4	+5.16	0.00
5	+4.62	-2.24
6	+3.20	-4.01
7	+1.14	-5.00
8	-1.14	-5.00
9	-3.20	-4.01
10	-4.62	-2.24
11	-5.16	0.00

Ctc	x	y
12	-4.62	+2.24
13	-3.20	+4.01
14	-1.14	+5.00
15	+1.14	+2.72
16	+2.97	+0.66
17	+2.36	-1.91
18	0.00	-3.05
19	-2.36	-1.91
20	-2.97	+0.66
21	-1.14	+2.72
22	0.00	-0.76

43



Ctc	x	y
1	+1.80	+5.54
2	-1.80	+5.54
3	+3.42	+4.71
4	+4.71	+3.42
5	+5.54	+1.80
6	+5.82	0.00
7	+5.54	-1.80
8	+4.71	-3.42
9	+3.42	-4.71
10	+1.80	-5.54
11	0.00	-5.82
12	-1.80	-5.54
13	-3.42	-4.71
14	-4.71	-3.42
15	-5.54	-1.80
16	-5.82	0.00
17	-5.54	+1.80
18	-4.71	+3.42
19	-3.42	+4.71
20	0.00	+4.12
21	+1.68	+3.76
22	+2.54	+2.28

Ctc	x	y
23	+3.92	+1.27
24	+4.10	-0.43
25	+3.57	-2.06
26	+1.99	-2.74
27	+0.86	-4.03
28	-0.86	-4.03
29	-1.99	-2.74
30	-3.57	-2.06
31	-4.10	-0.43
32	-3.92	+1.27
33	-2.54	+2.28
34	-1.68	+3.76
35	0.00	+2.42
36	+1.21	+1.21
37	+2.42	0.00
38	+1.21	-1.21
39	0.00	-2.42
40	-1.21	-1.21
41	-2.42	0.00
42	-1.21	+1.21
43	0.00	0.00

98



Ctc	x	y
A	0.00	+4.95
B	+3.18	+3.81
C	+4.90	+0.76
D	+4.17	-2.67
E	0.00	-3.43

Ctc	x	y
F	-4.17	-2.67
G	-4.90	+0.76
H	-3.18	+3.81
J	+1.65	-0.38
K	-1.65	-0.38

© 2013 - SOURIAU

15 / D

05



Ctc	X	y
A	0	+2.54
B	+4.42	+0.61
C	+2.39	+3.76
D	-2.39	-3.76
E	-4.42	+0.61

18



Ctc	X	y
A	+1.65	+6.40
B	+4.95	+2.87
C	+6.60	0.00
D	+4.95	-2.87
E	+3.30	-5.72
F	0.00	-5.72
G	-3.30	-5.72
H	-4.95	-2.87
J	-6.60	0.00

Ctc	X	y
K	-4.95	+2.87
L	-1.65	+6.40
M	-1.65	+2.87
N	+1.65	+2.87
P	+3.30	0.00
R	+1.65	-2.87
S	-1.65	-2.87
T	-3.30	0.00
U	0.00	0.00

19



Ctc	X	y
A	0.00	+5.72
B	+3.30	+5.72
C	+4.95	+2.87
D	+6.60	0.00
E	+4.95	-2.87
F	+3.30	-5.72
G	0.00	-5.72
H	-3.30	-5.72
J	-4.95	-2.87
K	-6.60	0.00

Ctc	X	y
L	-4.95	+2.87
M	-3.30	+5.72
N	-1.65	+2.87
P	+1.65	+2.87
R	+3.30	0.00
S	+1.65	-2.87
T	-1.65	-2.87
U	-3.30	0.00
V	0.00	0.00

97



Ctc	X	y
A	+1.65	+5.94
B	+4.52	+4.52
C	+5.84	-0.58
D	+4.52	-4.52
E	+1.65	-5.94
F	-2.26	-5.97
G	-5.26	-2.41
H	-5.94	+1.65
J	-4.52	+4.52
K	-1.65	+5.94
L	-1.19	+2.06
M	+1.19	-2.06

35



Ctc	X	y
1	+1.14	+6.65
2	+3.12	+5.51
3	+5.36	+4.06
4	+6.45	+2.03
5	+6.75	-0.25
6	+6.27	-2.49
7	+5.08	-4.45
8	+3.30	-5.89
9	+1.14	-6.65
10	-1.14	-6.65
11	-3.30	-5.89
12	-5.08	-4.45
13	-6.27	-2.49
14	-6.76	-0.25
15	-6.45	+2.03
16	-5.36	+4.06
17	-3.12	+5.51
18	-1.14	+6.65
19	+1.14	+4.37

Ctc	X	y
20	+3.12	+3.02
21	+4.32	+1.02
22	+4.32	-1.27
23	+3.12	-3.23
24	+1.14	-4.37
25	-1.14	-4.37
26	-3.12	-3.23
27	-4.32	-1.27
28	-4.32	+1.02
29	-3.12	+3.02
30	-1.14	+4.37
31	+1.14	+1.88
32	+2.29	-0.10
33	+1.14	-2.08
34	-1.14	-2.08
35	-2.29	-0.10
36	-1.14	+1.88
37	0.00	-0.10

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

17 / E

06



Ctc	x	y
A	+3.07	+5.31
B	+6.12	0.00
C	0.00	-6.12
D	-6.12	0.00
E	-3.07	+5.31
F	0.00	0.00

08



Ctc	x	y
A	0.00	+5.99
B	+3.25	+2.18
C	+5.84	-1.98
D	+2.39	-5.49
E	-2.39	-5.49
F	-5.84	-1.98
G	-3.25	+2.18
H	0.00	-1.32

26



Ctc	x	y
A	0.00	+8.15
B	+3.33	+7.44
C	+6.07	+5.44
D	+7.75	+2.51
E	+8.10	-0.86
F	+7.06	-4.09
G	+4.80	-6.60
H	+1.70	-7.98

Ctc	x	y
J	-1.70	-7.98
K	-4.80	-6.60
L	-7.06	-4.09
M	-8.10	-0.86
N	-7.75	+2.51
P	-6.07	+5.44
R	-3.33	+7.44
S	-1.78	+4.50
T	+1.78	+4.50
U	+4.45	+2.39
V	+4.53	-0.91
W	+3.02	-3.84
X	0.00	-5.16
y	-3.02	-3.84
Z	-4.53	-0.91
a	-4.45	+2.39
b	0.00	+1.65
c	0.00	-1.65

35



Ctc	x	y
1	-7.92	+2.18
2	-7.92	-0.10
3	-7.92	-2.39
4	-6.15	+5.61
5	-5.94	+3.33
6	-5.94	+1.04
7	-5.94	-1.24
8	-5.94	-3.53
9	-5.94	-5.82
10	-4.37	+7.09
11	-3.96	+4.47
12	-3.96	+2.18

Ctc	x	y
13	-3.96	-0.10
14	-3.96	-2.39
15	-3.96	-4.67
16	-3.96	-6.96
17	-2.26	+8.03
18	-1.98	+5.61
19	-1.98	+3.33
20	-1.98	+1.04
21	-1.98	-1.24
22	-1.98	-3.53
23	-1.98	-5.82
24	-1.98	-8.10

Ctc	x	y
25	0.00	+8.36
26	0.00	+4.47
27	0.00	+2.18
28	0.00	-0.10
29	0.00	-2.39
30	0.00	+4.67
31	0.00	-6.96
32	+2.26	+8.03
33	+1.98	+5.61
34	+1.98	+3.33
35	+1.98	+1.04
36	+1.98	-1.24
37	+1.98	-3.53
38	+1.98	-5.82
39	+1.98	-8.10
40	+4.37	+7.09

Ctc	x	y
41	+3.96	+4.47
42	+3.96	+2.18
43	+3.96	-0.10
44	+3.96	-2.39
45	+3.96	-4.67
46	+3.96	-6.96
47	+6.15	+5.61
48	+5.94	+3.33
49	+5.94	+1.04
50	+5.94	-1.24
51	+5.94	-3.53
52	+5.94	-5.82
53	+7.92	+2.18
54	+7.92	-0.10
55	+7.92	2-.39

99



Ctc	x	y
A	0.00	+8.15
B	+3.33	+7.44
C	+6.07	+5.44
D	+7.75	+2.51
E	+8.10	-0.86
F	+7.06	-4.09
G	+4.80	-6.60
H	+1.70	-7.98
J	-1.70	-7.98
K	-4.80	-6.60
L	-7.06	-4.09
M	-8.10	-0.86

Ctc	x	y
N	-7.75	+2.51
P	-6.07	+5.44
R	-3.33	+7.44
S	-1.78	+4.50
T	+1.78	+4.50
U	+4.45	+2.39
V	+3.81	-1.91
W	0.00	-4.09
X	-3.81	-1.91
y	-4.45	+2.39
Z	0.00	+0.64

© 2013 - SOURIAU

19 / F

11



Ctc	x	y
A	+2.67	+6.60
B	+6.35	+3.35
C	+6.99	-1.35
D	+4.55	-5.46
E	0.00	-7.14
F	-4.55	-5.46
G	-6.99	-1.35
H	-6.35	+3.35
J	-2.67	+6.60
K	0.00	+2.67
L	0.00	-2.34

32



Ctc	x	y
A	+1.68	+8.97
B	+4.80	+7.75
C	+7.26	+5.51
D	+8.76	+2.49
E	+9.07	-0.84
F	+8.15	-4.06
G	+6.15	-6.73
H	+3.30	-8.51
J	0.00	-9.12
K	-3.30	-8.51
L	-6.15	-6.73
M	-8.15	-4.06
N	-9.07	-0.84
P	-8.76	+2.49
R	-7.26	+5.51
S	-4.80	+7.75

Ctc	x	y
T	-1.68	+8.97
U	0.00	+5.84
V	+3.15	+4.90
W	+5.31	+2.41
X	+5.79	-0.84
y	+4.42	-3.84
Z	+1.65	-5.61
a	-1.65	-5.61
b	-4.42	-3.84
c	-5.79	-0.84
d	-5.31	+2.41
e	-3.15	+4.90
f	0.00	+2.44
g	+2.44	0.00
h	0.00	-2.44
j	-2.44	0.00

35



Ctc	x	y
1	-9.07	+2.29
2	-9.07	+0.08
3	-9.07	-2.29
4	-7.09	+5.72
5	-7.09	+3.43
6	-7.09	+1.14
7	-7.09	-1.14
8	-7.09	-3.43
9	-7.09	-5.72
10	-5.11	+6.86
11	-5.11	+4.57
12	-5.11	+2.29
13	-5.11	0.00
14	-5.11	-2.29

Ctc	x	y
15	-5.11	-4.57
16	-5.11	-6.86
17	-3.12	+8.00
18	+3.12	+5.72
19	-3.12	+3.43
20	-3.12	+1.14
21	-3.12	-1.14
22	-3.12	-3.43
23	-3.12	-5.72
24	-3.12	-8.00
25	-1.14	+9.14
26	-1.14	+6.86
27	-1.14	+4.57

Ctc	x	y
28	-1.14	+2.29
29	-1.14	0.00
30	-1.14	-2.29
31	-1.14	-4.57
32	-1.14	-6.86
33	-1.14	-9.14
34	+1.14	+9.14
35	+1.14	+6.86
36	+1.14	+4.57
37	+1.14	+2.29
38	+1.14	0.00
39	+1.14	-2.29
40	+1.14	-4.57

Ctc	x	y
41	+1.14	-6.86
42	+1.14	-9.14
43	+3.12	+8.00
44	+3.12	+5.72
45	+3.12	+3.43
46	+3.12	+1.14
47	+3.12	-1.14
48	+3.12	-3.43
49	+3.12	-5.72
50	+3.12	-8.00
51	+5.11	+6.86
52	+5.11	+4.57
53	+5.11	+2.29

Ctc	x	y
54	+5.11	0.00
55	+5.11	-2.29
56	+5.11	-4.57
57	+5.11	-6.86
58	+7.09	+5.72
59	+7.09	+3.43
60	+7.09	+1.14
61	+7.09	-1.14
62	+7.09	-3.43
63	+7.09	-5.72
64	+9.07	+2.29
65	+9.07	0.00
66	+9.07	-2.29

© 2013 - SOURIAU

21 / G

16



Ctc	X	y
A	+3.00	+8.18
B	+6.88	+5.36
C	+8.66	+0.91
D	+7.82	-3.81
E	+4.62	-7.37
F	0.00	-8.71
G	-4.62	-7.37
H	-7.82	-3.81

Ctc	X	y
J	-8.66	+0.91
K	-6.88	+5.36
L	-3.00	+8.18
M	0.00	+4.45
N	+3.91	+1.57
P	+2.39	-3.10
R	-2.39	-3.10
S	-3.91	+1.57

35



Ctc	X	y
1	+1.35	+10.82
2	+3.71	+10.26
3	+5.89	+9.19
4	+7.77	+7.67
5	+9.27	+5.77
6	+10.31	+3.58
7	+10.85	+1.22
8	+10.85	-1.22
9	+10.31	-3.58
10	+9.27	-5.77
11	+7.77	-7.67
12	+5.89	-9.19
13	+3.71	-10.26

Ctc	X	y
14	+1.35	-10.82
15	-1.35	-10.82
16	-3.71	-10.26
17	-5.89	-9.19
18	-7.77	-7.67
19	-9.27	-5.77
20	-10.31	-3.58
21	-10.85	-1.22
22	-10.85	+1.22
23	-10.31	+3.58
24	-9.27	+5.77
25	-7.77	+7.67
26	-5.89	+9.19
27	-3.71	+10.26
28	-1.35	+10.82
29	0.00	+8.20
30	+2.49	+8.18
31	+4.67	+7.11
32	+6.55	+5.59
33	+7.90	+3.58
34	+8.43	+1.22
35	+8.43	-1.22

Ctc	X	y
36	+7.90	-3.58
37	+6.55	-5.59
38	+4.67	-7.11
39	+2.49	-8.18
40	0.00	-8.81
41	-2.49	-8.18
42	-4.67	-7.11
43	-6.55	-5.59
44	-7.90	-3.58
45	-8.43	-1.22
46	-8.43	+1.22
47	-7.90	+3.58
48	-6.55	+5.59
49	-4.67	+7.11
50	-2.49	+8.18
51	-1.22	+6.12
52	+1.22	+6.12
53	+3.40	+5.05
54	+5.28	+3.53
55	+6.02	+1.22
56	+6.02	-1.22
57	+5.28	-3.53

Ctc	X	y
58	+3.40	-5.05
59	+1.22	-6.12
60	-1.22	-6.12
61	-3.40	-5.05
62	-5.28	-3.53
63	-6.02	-1.22
64	-6.02	+1.22
65	-5.28	+3.53
66	-3.40	+5.05
67	-1.22	+3.71
68	+1.22	+3.71
69	+3.18	+2.29
70	+3.94	0.00
71	+3.18	-2.29
72	+1.22	-3.71
73	-1.22	-3.71
74	-3.18	-2.29
75	-3.94	0.00
76	-3.18	+2.29
77	0.00	+1.35
78	+1.22	-0.74
79	-1.22	-0.74

39



Ctc	X	y
A	+1.65	+10.44
B	+4.80	+9.42
C	+7.47	+7.47
D	+9.42	+4.80
E	+10.44	+1.65
F	+10.44	-1.65
G	+9.42	-4.80
H	+7.47	-7.47
J	+4.80	-9.42
K	+1.65	-10.44
L	-1.65	-10.44
M	-4.80	-9.42
N	-7.47	-7.47

Ctc	X	y
P	-9.42	-4.80
R	-10.44	-1.65
S	-10.44	+1.65
T	-9.42	+4.80
U	-7.47	+7.47
V	-4.80	+9.42
W	-1.65	+10.44
X	0.00	+7.49
y	+3.20	+6.50
Z	+5.89	+4.55
a	+7.11	+1.45
b	+7.11	-1.88
c	+5.51	-4.80

Ctc	X	y
d	+2.84	-6.73
e	-2.84	-6.73
f	-5.51	-4.80
g	-7.11	-1.88
h	-7.11	+1.45
i	-5.89	+4.55
j	-3.20	+6.50
k	0.00	+4.17
m	+2.90	+1.22
n	+2.69	-2.72
p	0.00	-4.80
q	-2.69	-2.72
r	-2.90	+1.22

41



Ctc	X	y
A	0.00	+10.60
B	+3.28	+10.09
C	+6.23	+8.58
D	+8.58	+6.23
E	+10.09	+3.28
F	+10.60	0.00
G	+10.09	-3.28
H	+8.58	-6.23
J	+6.23	-8.58
K	+3.28	-10.09
L	0.00	-10.60

Ctc	X	y
M	-3.26	-10.09
N	-6.23	-8.58
P	-8.58	-6.23
R	-10.09	-3.28
S	-10.60	0.00
T	-10.09	+3.28
U	-8.58	+6.23
V	-6.23	+8.58
W	-3.28	+10.09
X	0.00	+7.20
y	+3.35	+6.38

Ctc	X	y
Z	+5.92	+4.09
a	+7.15	+0.87
b	+6.73	-2.55
c	+4.78	-5.39
d	+1.73	-6.99
e	-1.73	-6.99
f	-4.78	-5.39
g	-6.73	-2.55
h	-7.15	+0.87
i	-5.92	+4.09
j	-3.35	+6.38
k	0.00	+3.81
m	+2.98	+2.38
n	+3.71	-0.85
p	-1.66	-3.43
q	+1.66	-3.43
r	-3.71	-0.85
s	-2.98	+2.38
t	0.00	0.00

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

23 / H

21



Ctc	x	y
A	+3.25	+9.78
B	+7.34	+7.24
C	+9.80	+3.12
D	+10.16	-1.65
E	+8.33	-6.07
F	+4.65	-9.19
G	0.00	-10.31
H	-4.65	-9.19
J	-8.33	-6.07
K	-10.16	-1.65
L	-9.80	+3.12
M	-7.34	+7.24
N	-3.25	+9.78
P	0.00	+6.22
R	+4.06	+3.71
S	+5.44	-0.89
T	+2.39	-4.93
U	-2.39	-4.93
V	-5.44	-0.89
W	-4.06	+3.71
X	0.00	0.00

53



Ctc	x	y
A	+2.84	+11.56
B	+5.72	+9.91
C	+8.53	+8.26
D	+11.43	+3.30
E	+11.43	0.00
F	+11.43	-3.30

Ctc	x	y
G	+8.53	-8.26
H	+5.72	-10.41
J	-5.72	-10.41
K	-8.53	-8.26
L	-11.43	-3.30
M	-11.43	0.00

Ctc	x	y
N	-11.43	+3.30
P	-8.53	+8.26
R	-5.72	+9.91
S	-2.84	+11.56
T	0.00	+9.91
U	+2.84	+8.26
V	+5.72	+6.60
W	+8.53	+4.95
X	+8.53	+1.65
y	+8.53	-1.65
Z	+8.53	-4.95
a	+5.72	-6.60
b	+2.84	-8.26
c	0.00	-9.91
d	-2.84	-8.26
e	-5.72	-6.60
f	-8.53	-4.95
g	-8.53	-1.65
h	-8.53	+1.65
k	-8.53	+4.95

Ctc	x	y
m	-5.72	+6.60
n	-2.84	+8.26
p	0.00	+6.60
q	+2.84	+4.95
r	+5.72	+3.30
s	+5.72	0.00
t	+5.72	-3.30
u	+2.84	-4.95
v	0.00	-6.60
w	-2.84	-4.95
x	-5.72	-3.30
y	-5.72	0.00
z	-5.72	+3.30
AA	-2.84	+4.95
BB	0.00	+3.30
CC	+2.84	+1.65
DD	+2.84	-1.65
EE	0.00	-3.30
FF	-2.84	-1.65
GG	-2.84	+1.65
HH	0.00	0.00

25 / J

04



Ctc	x	y
A	+1.75	+13.49
B	+5.16	+12.57
C	+8.23	+10.80
D	+10.77	+8.28
E	+12.52	+5.21
F	+13.49	+1.75
G	+13.49	-1.75

Ctc	x	y
H	+12.52	-5.21
J	+10.77	-8.28
K	+8.23	-10.80
L	+5.16	-12.57
M	+1.75	-13.49
N	-1.75	-13.49
P	-5.16	-12.57

Ctc	x	y
R	-8.23	-10.80
S	-10.77	-8.28
T	-12.52	-5.21
U	-13.49	-1.75
V	-13.49	+1.75
W	-12.52	+5.21
X	-10.77	+8.28
y	-8.23	+10.80
Z	-5.16	+12.57
a	-1.75	+13.49
b	+2.18	+10.08
c	+5.38	+8.78
d	+7.90	+6.38
e	+9.58	+3.35
f	+10.46	0.00
g	+9.58	-3.35
h	+7.90	-6.38
k	+5.38	-8.78
m	+2.18	-10.08
n	-2.18	-10.08
p	-5.38	-8.78

Ctc	x	y
q	-7.90	-6.38
r	-9.58	-3.35
s	-10.46	0.00
t	-9.58	+3.35
u	-7.90	+6.38
v	-5.38	+8.78
w	-2.18	+10.08
x	+1.75	+6.66
y	+4.37	+3.78
z	+6.55	0.00
AA	+4.37	-3.78
BB	+1.75	-6.66
CC	-1.75	-6.66
DD	-4.37	-3.78
EE	-6.55	0.00
FF	-4.37	-3.78
GG	-1.75	-6.66
HH	0.00	+3.35
JJ	+2.18	0.00
KK	0.00	-3.35
LL	-2.18	0.00

29



Ctc	x	y
A	0.00	+12.22
B	+6.55	+10.31
C	+10.03	+7.04
D	+11.91	+2.77
E	+11.91	-2.77
F	+10.03	-7.04
G	+6.68	-10.31
H	+2.31	-11.99

Ctc	x	y
J	-2.31	-11.99
K	-6.68	-10.31
L	-10.03	-7.04
M	-11.91	-2.77
N	-11.91	+2.77
P	-10.03	+7.04
R	-6.55	+10.31
S	-2.31	+8.15
T	+2.31	+8.15
U	+5.79	+4.93
V	+8.10	0.00
W	+6.10	-4.60
X	+2.31	-7.37
y	-2.31	-7.37
Z	-6.10	-4.60
a	-8.10	0.00
b	-5.79	+4.93
c	0.00	+4.09
d	+3.40	0.00
e	0.00	-3.30
f	-3.40	0.00

© 2013 - SOURIAU

8LT Series
MIL-DTL-38999 Series I

25 / J

35



Ctc	x	y
1	-12.17	+7.09
2	-13.21	+4.83
3	-13.87	+2.41
4	-14.10	0.00
5	-13.87	-2.41
6	-13.21	-4.83
7	-12.17	-7.09
8	-10.77	+9.07
9	-10.54	+4.83
10	-10.54	+2.41
11	-10.54	0.00
12	-10.54	-2.41
13	-10.54	-4.83
14	-10.77	-9.07
15	-8.43	+11.28
16	-8.43	+8.43
17	-8.43	+6.02
18	-8.43	+3.61
19	-8.43	+1.19
20	-8.43	-1.19
21	-8.43	-3.61
22	-8.43	-6.02
23	-8.43	-8.43
24	-8.43	-10.85
25	-6.32	+12.60
26	-6.32	+9.65
27	-6.32	+7.24
28	-6.32	+4.83
29	-6.32	+2.41
30	-6.32	0.00
31	-6.32	-2.41
32	-6.32	-4.83
33	-6.32	-7.24
34	-6.32	-9.65
35	-6.32	-12.07
36	-4.06	+13.49
37	-4.22	+10.85
38	-4.22	+8.43
39	-4.22	+6.02
40	-4.22	+3.61
41	-4.22	+1.19
42	-4.22	-1.19
43	-4.22	-3.61
44	-4.22	-6.02
45	-4.22	-8.43
46	-4.22	-10.85
47	-4.22	-13.26
48	-2.11	+12.07
49	-2.11	+9.65
50	-2.11	+7.24
51	-2.11	+4.83
52	-2.11	+2.41
53	-2.11	0.00
54	-2.11	-2.41
55	-2.11	-4.83
56	-2.11	-7.24
57	-2.11	-9.65
58	-2.11	-12.07
59	0.00	+13.26
60	0.00	+10.85
61	0.00	+8.43
62	0.00	+6.02
63	0.00	+3.61
64	0.00	+1.19
65	0.00	-1.19
66	0.00	-3.61
67	0.00	-6.02
68	0.00	-8.43
69	0.00	-10.85
70	0.00	-14.10
71	+2.11	+12.07
72	+2.11	+9.65
73	+2.11	+7.34
74	+2.11	+4.83
75	+2.11	+2.41
76	+2.11	0.00
77	+2.11	-2.41
78	+2.11	-4.83
79	+2.11	-7.24
80	+2.11	-9.65
81	+2.11	-12.07
82	+4.06	+13.49
83	+4.22	+10.85
84	+4.22	+8.43
85	+4.22	+6.02
86	+4.22	+3.61
87	+4.22	+1.19
88	+4.22	-1.19
89	+4.22	-3.61
90	+4.22	-6.02
91	+4.22	-8.43
92	+4.22	-10.85
93	+4.22	-13.26
94	+6.32	+12.60
95	+6.32	+9.65
96	+6.32	+7.24
97	+6.32	+4.83
98	+6.32	+2.41
99	+6.32	0.00
100	+6.32	-2.41
101	+6.32	-4.83
102	+6.32	-7.24
103	+6.32	-9.65
104	+6.32	-12.07
105	+8.43	+11.28
106	+8.43	+8.43
107	+8.43	+6.02
108	+8.43	+3.61
109	+8.43	+1.19
110	+8.43	-1.19
111	+8.43	-3.61
112	+8.43	-6.02
113	+8.43	-8.43
114	+8.43	-10.85
115	+10.77	+9.07
116	+10.54	+4.83
117	+10.54	+2.41
118	+10.54	0.00
119	+10.54	-2.41
120	+10.54	-4.83
121	+10.77	-9.07
122	+12.17	+7.09
123	+13.21	+4.83
124	+13.87	+2.41
125	+14.10	0.00
126	+13.87	-2.41
127	+13.21	-4.83
128	+12.17	-7.09

43



Ctc	x	y
A	+1.75	+13.49
B	+5.16	+12.57
C	+8.23	+10.80
D	+10.77	+8.28
E	+12.52	+5.21
F	+13.49	+1.75
G	+13.49	-1.75
H	+12.52	-5.21
J	+10.77	-8.28
K	+8.23	-10.80
L	+5.16	-12.57
M	0.00	-13.49
N	-5.16	-12.57
P	-8.23	-10.80
R	-10.77	-8.28
S	-12.52	-5.21
T	-13.49	-1.75
U	-13.49	+1.75
V	-12.52	+5.21
W	-10.77	+8.28
X	-8.23	+10.80
y	-5.16	+12.57
Z	-1.75	+13.4
a	+4.37	+8.74
b	+6.55	+4.37
c	+8.74	0.00
d	+8.74	-4.37
e	+4.37	-8.74
f	0.00	-8.74
g	-4.37	-8.74
h	-8.74	-4.37
k	-8.74	0.00
m	-6.55	+4.37
n	-4.37	+8.74
p	0.00	+8.74
q	+2.18	+4.37
r	+4.37	0.00
s	+4.37	-4.37
t	0.00	-4.37
u	-4.37	-4.37
v	-4.37	0.00
w	-2.18	+4.37
x	0.00	0.00

61



Ctc	x	y
A	+4.98	+12.70
B	+7.98	+11.05
C	+10.49	+8.71
D	+12.32	+5.84
E	+13.39	+2.57
F	+13.61	-0.76
G	+12.98	-4.17
H	+11.53	-7.29
J	+9.35	-9.93
K	+6.58	-11.94
L	+3.40	-13.18
M	0.00	-13.64
N	-3.40	-13.18
P	-6.58	-11.94
R	-9.35	-9.93
S	-11.53	-7.29
T	-12.98	-4.17
U	-13.61	-0.76
V	-13.39	+2.57
W	-12.32	+5.84
X	-10.49	+8.71
y	-7.98	-11.05
Z	-4.98	+12.10
a	-1.73	+11.53
b	+1.73	+11.53
c	+4.39	+9.22
d	+7.24	+7.19
e	+9.19	+4.45
f	+10.13	+1.17
g	+9.96	-2.24
h	+8.66	-5.41
i	+6.38	-7.98
j	+3.38	-9.63
k	0.00	-10.21
m	-3.38	-9.63
n	-6.38	-7.98
p	-8.66	-5.41
q	-9.96	-2.24
r	-10.13	+1.17
s	-9.19	+4.45
t	-7.24	+7.19
u	-4.39	+9.22
v	0.00	+8.59
w	+3.73	+5.66
x	+6.02	+3.10
y	+6.78	-0.25
z	+5.79	-3.53
AA	+3.33	-5.92
BB	0.00	-6.78
CC	-3.33	-5.92
DD	-5.79	-3.53
EE	-6.78	-0.25
FF	-6.02	+3.10
GG	-3.73	+5.66
HH	0.00	+5.08
JJ	+2.67	+2.39
KK	+3.43	-1.04
LL	0.00	-3.35
MM	-3.43	-1.04
NN	-2.67	+2.39
PP	0.00	0.00

© 2013 - SOURIAU

8LT Series

8LT Series

Range Extension

- micro38999 62
- RoHS solution 62
- High density 63
- PCB contact without shoulder 63

Product range extension

micro38999

A complete miniature range: threaded (8DA), break away (8BA) & bayonet (8LTA). Space saving with scoop proof connector for harsh applications.

A compact solution:
. Diameter up to 45% smaller than size 9 (D38999).
. Up to 50% shorter.
. Integrated backshell: Cost and space saving.

A high density solution:
. With #26 contacts (according to 39029).
. 5 layouts (size 3, 5 and 7 with #22 & #26).

Excellent features:
. Designed for D38999 requirements.
. IP67 sealing when mated.
. Stainless steel shell (1500 matings) & aluminum shell (500 matings).

RoHS and Cadmium free:
. Available in zinc nickel (RoHS) plating, as well as nickel and olive drab cadmium.

See «micro38999, A Complete Miniature Range» catalog on www.souriau.com

RoHS Solution

The RoHS alternative to cadmium !
SOURIAU Zinc Nickel: the best in terms of price and performance for aerospace & defense equipment.

SOURIAU Black Zinc Nickel:
. A unique alternative plating process to cadmium.

RoHS compliant:
. A unique SOURIAU plating process compliant with RoHS regulations for cadmium and Cr6+.

The first QPL qualified:
. SOURIAU Zn Ni is the first product which has been qualified by US Defense standards organization (DLA Land and Maritime).

High corrosion resistance:
. 500 hours salt spray.

Available in mass production:
. Available for 38999 Series I, II and III aluminum range.

See «RoHS by SOURIAU, The Cadmium Free Solution» catalog on www.souriau.com

© 2013 - SOURIAU

Product range extension

High Density

SOURIAU offers a robust & reliable High Density solution derived from 38999 Series I, Series III & VG96912.

3 shell sizes available:
. Provides flexibility according to your application.

A reliable & robust solution:
. Same well proven design as standard 38999 & VG96912.

Significant space saving:
. Twice the number of contacts compared to size 13-35 with 22 contacts.
. Two shell sizes smaller than a partially populated size 17-35 with 55 cavities.

See «High Density Connectors» product news on www.souriau.com

PCB Contact without Shoulder

Pin & socket PCB contacts without shoulder #22D & #20 as per MIL-DTL-38999 Series I, II & III. Contacts without shoulder allows a more flexible mounting on variable PCB thicknesses or depths.

Ruggedized contacts:
. Material: copper alloy
. Finish: gold per MIL-G-45204 type I class 1 over nickel plate
. Sleeve: stainless steel

Flexible mounting:
. Various PCB thicknesses.
. Multiple PCB positioning.



See «PCB contacts without shoulder» product news on www.souriau.com

© 2013 - SOURIAU

SOURIAU

www.souriau.com

contactmilaero@souriau.com

Esterline

Connection Technologies

© Copyright SOURIAU July 2013 - All information in this document presents only general particulars and shall not form part of any contract. All rights reserved to SOURIAU for changes without prior notification or public announcement. Any duplication is prohibited, unless approved in writing.