




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1891	A	RELEASED	EO	06/27/06	SA	7/25/06	HO	7/25/06



Telephone Flat Cable
Bare Copper Stranded
Polypropylene Insulated
Flame Retardant PVC Jacket



SPECIFICATION:

1. Insulation:

Conductor	Insulation		Color Code		
AWG	Material	O.D.	1. BLACK	2. RED	3. GREEN
24 (11/0.16)	PP	0.95±0.05mm	4. YELLOW		

2. Jacket:

Material	O.D.	Color
FR-PVC	2.4X5.0±0.1mm	SILVER SATIN

3. Electrical & Physical Properties:

- Temperature & Voltage Rating: 60°C – 150 V
- Conductor Resistance: 93 Ohm/1000 meters Max. at 20°C
- Insulation Resistance: 100 Megohm/1000 meters Min. at 20°C
- Dielectric Strength: 500 VAC for one minute

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
Unless Otherwise
Specified
.X ±0.2 [0.008]
.XX ±0.12 [0.005]

DRAWN BY:
EKLAS ODISH
DATE:
06/27/06
CHECKED BY:
DATE:
7/25/06
APPROVED BY:
DATE:
7/25/06
HISHAM ODISH

DRAWING TITLE:
Flat Telephone Cable, 24 AWG, 4 Stranded Conductors
SIZE DWG. NO.
A SPC19812
ELECTRONIC FILE REV
84K8574.DWG A
SCALE: NTS U.O.M.: mm [INCHES] SHEET: 1 OF 1