



Home: Terminal Blocks >

Part Number: 39522-4117

5.00mm Pitch Eurostyle™ Horizontal PCB Header, with Standard Imprinting, Surface Mount Compatible, 17 Circuits



Series image - Reference only

Status:
Replacement:**OBsolete**

Contact Molex

Series:
Category:

39522

Terminal Blocks

Go to [Part Detail](#) ▾ [CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#) [Email this page](#)**Mates With Part(s):**[39520](#) Horizontal Plug, [39523](#) Vertical Plug, Most 5.00mm Pitch Industry Standard Plugs**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active [EU RoHS Certificate of Compliance \(PDF\)](#) [Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****General**

Status	Obsolete
Category	Terminal Blocks
Series	39522
Application	N/A
Comments	with Standard Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block
UPC	822350445573

Physical

Circuits (Loaded)	17
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Horizontal
PC Tail Length	3.90mm
PCB Thickness - Recommended	3.20mm
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +140°C
Wire Size AWG	N/A

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Solder Process Data**Solderability Shelf Life Statement**

Lead-free Process Capability	N/A
------------------------------	-----

Products**Quick Links****Resources****Stay Connected**

Antennas

Company Information

Supply Chain Transparency

Application Tooling

Contact Molex

Business Continuity

Cable Assemblies

Cross-Reference

Compliance

Connected Lighting

Koch Industries

ecocare

Connectors

Industries

Feedback | Help

Copper Flex

Investor Relations

Jobs

Electrical Products

Literature

Legal | Trademarks

Industrial Automation

Molex Racing

Mobile Site

Membrane Switches

Press Room / Press Releases

Supplier Portal

Optical Solutions

Product Index

Privacy Policy

Printed Electronic Solutions

Sitemap

Tradeshows

Terms & Conditions