



**Materials and Finish**

Housing Material:
thermoplastic,
UL 94V-0 rated,
Color: black

Contact Material:
phosphor bronze

Contact Plating Options:
Standard: 0.0001" nickel
underplating, selectively plated
0.000015" gold on contact
area, tin-lead on solderails
50 Option: 0.0001" nickel
underplating, selectively plated
0.000050" gold on contact
area, tin-lead on solderails

Shield: 0.25 thick copper alloy,
tin-lead plated

Electrical Characteristics

Insulation Resistance:
500 Megohms min.

Voltage Rating: 150V AC

Contact Resistance:
20 milliohms max.

Current Rating:
1.5 amps

Operating Temperature:
-40°C to +85°C

Durability Rating:
500 mating cycles min.

LED Schematics

	Pin No.	Single Color (G, R, or Y)	Pin No.	Pin No.	Bi-Color (GR)	Pin No.	Pin No.	Bi-Color (GY)	Pin No.
LED 1	12	+	11	-	12	Green	11	Green	11
						Red		Yellow	
LED 2	10	+	9	-	10	Green	9	Green	9
						Red		Yellow	

LED Characteristics

LED Color	Forward DC Current (units: mA)	Forward Voltage (units: V)	Reverse Voltage (units: V)	Power Dissipation (units: mW)
green	25	2.2 Typ. (2.5 Max.)	5	105
red	30	2.0 Typ. (2.5 Max.)	5	105
yellow	30	2.1 Typ. (2.5 Max.)	5	105

Recommended PCB Layout (top view)


Part Number / Ordering Information

Complete P/N Example:	GWL	G	-	S1	-	4	8	8	GR	/	Y	50
P/N Breakdown:	Series	Type	dash	Shield Type	dash	No. of Ports	No. of Positions per Port	No. of Contacts per Port	LED 1 Color	slash	LED 2 Color	Contact Area Plating
Available Options:	GWL = right angle modular jack w/integrated LED's	G = ganged	dash	S1 = fully shielded w/top & side spring shield grounding tabs	dash	4 = 4 ports	8 = 8 contact positions per port	8 = 8 contacts per port	G = green R = red Y = yellow GR = bi-color green/red GY = bi-color green/yellow	slash	G = green R = red Y = yellow GR = bi-color green/red GY = bi-color green/yellow	blank = standard 50 = 50u" option



Tolerances
X.X ± 0.30
X.XX ± 0.20
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A0	1/8/03	New Drawing	C. Leiva	T. Gokcek	C. Leiva	1/8/03
A1	5/29/03	Release Drawing	T. Gokcek	C. Leiva		
A2	6/20/03	ECO #03-027	C. Leiva	T. Gokcek		
A3	2/24/04	ECO #04-020	C. Leiva	H. MA		



GWLG-S1-488-x/x
x = LED color

Right Angle Thru-Hole Ganged Modular Jack w/ LEDs
4 port, fully shielded w/ grounding tabs



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GWLG-S1-488-G/Y](#) [GWLG-S1-488-Y/G](#)