

14XE24

CATALOG LISTING

PAGE 1 OF 1

REPLACES

RELEASE NO. PR-18274

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK




NOTES

- ① MOUNTING HOLES WILL ACCEPT Ø.087 MAX PINS OR SCREWS ON .188±.002 CENTERS
- ② ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ③ WEIGHT OF SWITCH ONLY IS .16 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS .32 OZ MAX
- 4 - FOR USE IN TEMPERATURE RANGE FROM -65°F TO +300°F
- ⑤ WIRE LEAD MARKED PER MIL-W-5088 AS FOLLOWS: COMMON -22
- ⑥ WIRE LEAD MARKED PER MIL-W-5088 AS FOLLOWS: OPEN -22
- 7 - FLAT SPRING SX CONSTRUCTION

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — — 10 OZ MAX
RELEASE FORCE — — — — 2 OZ MIN
RELEASE TRAVEL — — — — .004 MIN
DIFFERENTIAL TRAVEL — — — .001 — .005
OVERTRAVEL — — — — .004 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

28 VOLTS DC RATING

INDUCTIVE — — — SEA LEVEL-3 AMP
50,000 FT-2 AMP
RESISTIVE — — — SEA LEVEL-5 AMP
50,000 FT-4 AMP

SCALE 2 : 1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT ③

DDM/CAD

DRAWN

SAV

18 MAY 91

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[14XE24](#)