



LOC	DIST			REVISIONS				
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
					J	REV / 0G10-0026-99	12FEB99	MLE SU



AMP WIRE RANGE	UL E13288 Listed
16-14 AWG STRANDED	16-14 AWG STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

1 STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		DR 2-4-93 TA BRINKMAN		30695		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE		MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 2-4-93 DA PATTERSON		PART NO		
FOR APPLICATION TOOLING INFORMATION			WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS STRANDED		FINISH TIN PLATE 0.00254[0.000100] MIN THK PER ASTM B-545		APPD 2-4-93 DE MILLER		NAME		
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				APPD 2-4-93 JL MECKLEY		TERMINAL, RING TONGUE, BUDGET		
PRODUCT INFORMATION CENTER 1-800-522-6752							PRODUCT SPEC -		SIZE	CAGE CODE	DRAWING NO
TOOLING ASSISTANCE CENTER 1-800-722-1111							APPLICATION SPEC -		C	00779	G-30695
1-800-526-5142							WEIGHT -		SCALE	8:1	SHEET 1 OF 1