



Features

- Diffused Junction
- Low Leakage
- Low Cost
- High Surge Current Capability
- Typical I_R less than $5.0\mu A$

Mechanical Data

- Case: 13mm Motorola Type Press-Fit
- Terminals: Contact Areas Readily Solderable
- Polarity: Cathode to Case (Reverse Units Are Available Upon Request and Are Designated By A "R" Suffix, i.e. MD2502R or MD2504R)
- Polarity: Red Color Equals Standard, Black Color Equals Reverse Polarity
- Mounting Position: Any
- **Lead Free: For RoHS / Lead Free Version, Add "-LF" Suffix to Part Number, See Page 2**



13mm Motorola		
Dim	Min	Max
A	12.80	13.20
B	7.70	8.10
C	1.25	1.31
D	25.00	—
E	11.10	11.50
All Dimensions in mm		

Maximum Ratings and Electrical Characteristics @ $T_A=25^\circ C$ unless otherwise specified

Single Phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

Characteristic	Symbol	MD2500	MD2501	MD2502	MD2503	MD2504	MD2505	MD2506	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V_{RRM} V_{RWM} V_R	50	100	200	300	400	500	600	V
RMS Reverse Voltage	$V_R(RMS)$	35	70	140	210	280	350	420	V
Average Rectified Output Current @ $T_C = 150^\circ C$	I_O	25							A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	300							A
Forward Voltage @ $I_F = 25A$	V_{FM}	1.0							V
Peak Reverse Current @ $T_A = 25^\circ C$ At Rated DC Blocking Voltage @ $T_A = 100^\circ C$	I_{RM}	5.0 500							μA
Typical Junction Capacitance (Note 1)	C_j	300							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JC}$	1.2							$^\circ C/W$
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +175							$^\circ C$

Note: 1. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.
2. Thermal Resistance: Junction to case, single side cooled.

ORDERING INFORMATION

Product No.	Package Type	Shipping Quantity
MD2500	13mm Motorola Press-Fit	100 Units/Box
MD2501	13mm Motorola Press-Fit	100 Units/Box
MD2502	13mm Motorola Press-Fit	100 Units/Box
MD2503	13mm Motorola Press-Fit	100 Units/Box
MD2504	13mm Motorola Press-Fit	100 Units/Box
MD2505	13mm Motorola Press-Fit	100 Units/Box
MD2506	13mm Motorola Press-Fit	100 Units/Box

1. Shipping quantity given is for minimum packing quantity only. For minimum order quantity, please consult the Sales Department.
2. **To order Lead Free version (with Lead Free finish), add "-LF" suffix to part number above. For example, MD2500-LF.**

Won-Top Electronics Co., Ltd (WTE) has checked all information carefully and believes it to be correct and accurate. However, WTE cannot assume any responsibility for inaccuracies. Furthermore, this information does not give the purchaser of semiconductor devices any license under patent rights to manufacturer. WTE reserves the right to change any or all information herein without further notice.

WARNING: DO NOT USE IN LIFE SUPPORT EQUIPMENT. WTE power semiconductor products are not authorized for use as critical components in life support devices or systems without the express written approval.

Won-Top Electronics Co., Ltd.

No. 44 Yu Kang North 3rd Road, Chine Chen Dist., Kaohsiung, Taiwan

Phone: 886-7-822-5408 or 886-7-822-5410

Fax: 886-7-822-5417

Email: sales@wontop.com

Internet: <http://www.wontop.com>

We power your everyday.