







PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-.01 [7.56]
1.25-2.0 [0.049-.079]	19.4-.01 [7.64]
2.0-3.0 [0.079-.118]	19.8-.01 [7.80]



CIRCUIT: DPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25


4. MATERIAL:
6A @250VAC; 9A @125VAC (UL, CSA, VDE)
4(1)A @250VAC

4. MATERIAL:

INTACT SURFACE: Coin Silver, Silver Plate

CRIMINAL: Copper Alloy W/ Silver Plate.

5. CONTACT RESISTANCE: 20MILLIOHMS TYP. INITIAL
6. INSULATION RESISTANCE: 1000MEGOHMS
7. DIELECTRIC STRENGTH:
 >1500V RMS min. @SEA LEVEL
 >3000V RMS @SEA LEVEL
8. MECHANICAL LIFE: 50,000 CYCLES.
9. ELECTRICAL LIFE: 10,000 CYCLES.



					TITLE				
					R1973B BLK REID FFO				
A	11330	RELEASED FOR PRODUCTION	10/01/01	CJB	SCALE	DATE	DR	DWG	REV
REV.	ECN No.	DESCRIPTION	DATE	CHKD	1.5/1	10/01/01	CB	M400024	A
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED									