





PRODUCT NUMBER
SEE TABLE



DETAIL "D"

mat'l. code				surface		tolerance		projection		product family			
				ISO 1302 ✓		ISO 406 ISO 1101				CLINCHER			
ltr		ecn nodr		date		tolerances unless otherwise specified:							
M		ELX-N-010494		ZK		06/03/12		angles		linear		title	
												CLINCHER™ RECEPTACLE ASSEMBLY-LATCHING	
G		V50244		HTB		2/14/95		0°±2°					
H		V51638		HTB		12/29/95		dr		M. FETROW		dwg no	
J		M05-0087		MHT		6/17/05		engr		T. HANNA		sheet 1 of 6	
K		M06-0233		AGS		06/12/06		chr		T. BREWBAKER		size	
L		M07-0170		MHT		3/30/07		appd		T. HANNA		A3	
												type	
												Product Customer Drawing	
sheet		revision		M		M		M		M			
index		sheet		1		2		3		4		5	

1

2

3

4

5

6

PLATING AVAILABLE





PLATING CODE	TERMINAL	SPRING
1	100u"/2.54u MIN. THICK PURE TIN	10u"/.25u MIN. THICK PURE TIN
2	30u"/.76u MIN. GOLD OR GXT STRIPE IN BOX AREA NOTE 12	3u"/.08u MIN. GOLD OVER 50u"/1.27u MIN. NICKEL

PRODUCT NUMBER

67516-XXXLF

LEAD FREE OPTION
NOTE 9,10NO OF POSITIONS
AND PLATING

BASE PART NUMBER

DETAIL Z
SCALE 5:1

NOTES:

- HOUSING MATERIAL: THERMOPLASTIC, FLAME RETARDANT PER UL 94V-0. COLOR: BLUE.
- TERMINAL MATERIAL: 1/2 HARD Cu NI ALLOY, UNS-C72500.
- TERMINAL PLATING: SEE TABLE.
- SEE TA-372 FOR CRIMP HEIGHT.
- FOR CABLE & CIRCUITRY INFORMATION SEE TA-264 AND TA-371.
- LATCH SNAPS CLOSED AFTER TERMINATION MAINTAINING A MAX OVER ALL HEIGHT OF .100/2.54.
- NO CENTER HINGE 2 THRU 8 POSITIONS. SINGLE CENTER HINGE 9 THRU 15 POSITIONS. TWO CENTER HINGES FOR 16 POSITION PARTS.
- KNURL MARK INDICATES FOR USE WITH INK TERMINATION. CONSULT WITH BERG ELECTRONICS TECHNICAL REPRESENTATIVE FOR SPECIFIC APPLICATIONS.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS
- PLATING OPTION MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code	surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family CLINCHER
l'tecn nodr date	tolerances unless otherwise specified	angles linea	scale 3:1	title CLINCHER™ RECEPTACLE ASSEMBLY-LATCHING
M		0°±2'		dwg no 67516
	dr M. FETROW 9/15/94	engr T. HANNA 9/15/94		sheet 2 of 6 size A3
	chr T. BREWBAKER 9/15/94	appd T. HANNA 9/15/94		type Product Customer Drawing
sheet index	revision sheet			

PDS: Rev :M

STATUS: Released

Printed: Mar 07, 2012

1

2

3

4

5

6

PRODUCT NUMBER	NO. OF	DIM. A	DIM. A	DIM. B	DIM. B	DIM. C	DIM. C	PLATING	TERMINATION
NOTE 9	POS.	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	CODE	NOTE 8
67516-201		U N A	S S I G	N E D					
67516-202	2	0.100	2.54	0.390	9.91	0.315	8.00	2	CONVENTIONAL
67516-203	3	0.200	5.08	0.490	12.45	0.415	10.54	2	CONVENTIONAL
67516-204	4	0.300	7.62	0.590	14.99	0.515	13.08	2	CONVENTIONAL
67516-205	5	0.400	10.16	0.690	17.53	0.615	15.62	2	CONVENTIONAL
67516-206	6	0.500	12.70	0.790	20.07	0.715	18.16	2	CONVENTIONAL
67516-207	7	0.600	15.24	0.890	22.61	0.815	20.70	2	CONVENTIONAL
67516-208	8	0.700	17.78	0.990	25.15	0.915	23.24	2	CONVENTIONAL
67516-209	9	0.800	20.32	1.090	27.69	1.015	25.78	2	CONVENTIONAL
67516-210	10	0.900	22.86	1.190	30.23	1.115	28.32	2	CONVENTIONAL
67516-211	11	1.000	25.40	1.290	32.77	1.215	30.86	2	CONVENTIONAL
67516-212	12	1.100	27.94	1.390	35.31	1.315	33.40	2	CONVENTIONAL
67516-213	13	1.200	30.48	1.490	37.85	1.415	35.94	2	CONVENTIONAL
67516-214	14	1.300	33.02	1.590	40.39	1.515	38.48	2	CONVENTIONAL
67516-215	15	1.400	35.56	1.690	42.93	1.615	41.02	2	CONVENTIONAL
67516-216	16	1.500	38.10	1.790	45.47	1.715	43.56	2	CONVENTIONAL

FCI

FCIconnect.com

Copyright FCI

mat'l. code

surface
ISO 1302 ✓

tolerance
ISO 406
ISO 1101

projection


product family
CLINCHER

title
CLINCHER™ RECEPTACLE
ASSEMBLY-LATCHING

dwg no
67516

sheet 4 of 6

size
A3

type
Product Customer Drawing

tolerances unless otherwise specified

angles
linea
0°±2°

XX±.01/0XX±0.3
XXX±.005/0XX±0.13
XXXX±.0020/0XXX±0.051

INCH/MM

scale 3:1

FCI

dr
M. FETROW
9/15/94

engr
T. HANNA
9/15/94

chr
T.BREWBAKER
9/15/94

appd
T.HANNA
9/15/94

sheet
index

revision
sheet

1

2

3

4

5

6

Form: A3

1

2

3

4

5

6

PDS: Rev :M

STATUS: Released

Printed: Mar 07, 2012



FCIconnect.com

Copyright FCI

1		2		3		4		5		6	
PRODUCT NUMBER	NO. OF	DIM. A	DIM. A	DIM. B	DIM. B	DIM. C	DIM. C	PLATING	TERMINATION		
NOTE 9	POS.	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	CODE	NOTE 8		
67516-501		U N A	S S I G	N E D							
67516-502	2	0.100	2.54	0.390	9.91	0.315	8.00	1	INK		
67516-503	3	0.200	5.08	0.490	12.45	0.415	10.54	1	INK		
67516-504	4	0.300	7.62	0.590	14.99	0.515	13.08	1	INK		
67516-505	5	0.400	10.16	0.690	17.53	0.615	15.62	1	INK		
67516-506	6	0.500	12.70	0.790	20.07	0.715	18.16	1	INK		
67516-507	7	0.600	15.24	0.890	22.61	0.815	20.70	1	INK		
67516-508	8	0.700	17.78	0.990	25.15	0.915	23.24	1	INK		
67516-509	9	0.800	20.32	1.090	27.69	1.015	25.78	1	INK		
67516-510	10	0.900	22.86	1.190	30.23	1.115	28.32	1	INK		
67516-511	11	1.000	25.40	1.290	32.77	1.215	30.86	1	INK		
67516-512	12	1.100	27.94	1.390	35.31	1.315	33.40	1	INK		
67516-513	13	1.200	30.48	1.490	37.85	1.415	35.94	1	INK		
67516-514	14	1.300	33.02	1.590	40.39	1.515	38.48	1	INK		
67516-515	15	1.400	35.56	1.690	42.93	1.615	41.02	1	INK		
67516-516	16	1.500	38.10	1.790	45.47	1.715	43.56	1	INK		

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family CLINCHER	
ltr ecn nodr date		tolerances unless otherwise specified		angles linea		INCH/MM scale 1:3		title CLINCHER™ RECEPTACLE ASSEMBLY-LATCHING	
M				XX±.01/0XX±0.3 XXX±.005/0XXX±0.13 XXXX±.0020/0XXXX±0.051				dwg no 67516	
		dr M. FETROW		9/15/94				sheet 5 of 6 size A3	
		engr T. HANNA		9/15/94					
		chr T. BREWBAKER		9/15/94					
		appd T. HANNA		9/15/94				type Product Customer Drawing	
sheet index		revision sheet							

