


KEMET Part Number: PME264NE6100MR30
(P264EL104M660A)

PME264/P264, Film, Metallized Paper, Safety, 0.1 uF, 20%, 1500 VDC, 660 VAC (X2), 85C, Lead Spacing = 25.4mm



General Information	
Supplier:	KEMET
Series:	PME264/P264
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
Construction:	Molded

Dimensions	
L	30.5mm MAX
H	22mm MAX
T	15.3mm MAX
S	25.4mm +/-0.5mm
LL	30mm +5mm
F	1mm NOM

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	75

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	20%
Voltage DC:	1500 VDC
Voltage AC:	660 VAC (X2)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	600 V/us
Safety Class:	X2