







STRIP




LOOSE-PIECE



COLOR CODE: YELLOW




SECTION A-A



SECTION B-B

WIRE RANGE : 0,20-0,50 mm? (24-20 AWG)
INSUL. RANGE : 1,1 -1,8 mm (.045-.070)

1-163085-4	1	A	1-163086-1	BRASS	EL.TIN	31	20
1-163085-3		A	1-163086-3	BRASS	BR. TIN		30
5-163085-3	5	C		BRASS	ECON.GOLD	21	
5-163085-2	1,5	C		BRASS	SEL.GOLD	22	
5-163085-1	1,5	C		BRASS	EL.TIN	20	
1-163085-2		B		BRASS	GOLD	23	
1-163085-1		A		BRASS	ECON.GOLD	21	
1-163085-0		B	1-163086-0	BRASS	ECON.GOLD	21	
163085-9		A		BRASS	EL.TIN	20	
163085-8		A		BRASS	SEL.GOLD	22	
163085-2	1	B	163086-2	BRASS	SEL.GOLD	22	
163085-1	1	B	163086-1	BRASS	EL.TIN	20	

PARTNUMBER				DIRECTION OF REEL	LOOSE-PIECE	MATERIAL	PLATING
RS		MG	13/12/04	CUSTOMER DRAWING			FOR REFERENCE ONLY WILL NOT BE UPDATED
JMS		FWK	02/08/04	© COPYRIGHT 19 - BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.			
PB		SS	3 OCT 02	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION - - ,19 - -			
D.K.		R.V.	06 OCT 95	 AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.			
JvL		MvD	03-05-94				
MvD		RD	06-02-92				
MvD		RD	09-10-91				
DR.		CHK.	DATE	NAME			
				TYPE_III_PIN_CONTACT SIZE_16			
APP.:		-		DWG.No.		REV.LTR.	SHEET
DATE:		-		163085		AC	1 OF 1
							A3

NOTES :

- U.L.RECONIZED UNDER FILE E28476 VOL.VI SEC.I
- FOR CRIMPDETAILS SEE AMP-SPEC. 114-19.000
- MEETS PRODUCTSPECIFICATION 108-10042.
- 0,40 MAX. GAP BETWEEN SPRING-NOSE AND CONTACT BODY.
- SPECIAL REEL WITH 200 PCS FOR REEL-FED HAND-TOOL

NOTES	MATERIAL	THICKNESS	AREA
20	TIN	2,0 μ m	ALL OVER
21	NICKEL	0,8 μ m	ALL OVER
22	GOLD	0,8 μ m	CONTACT AREA
23	TIN	0,8 μ m	BARREL
24	NICKEL	0,8 μ m	ALL OVER
25	GOLD	0,8 μ m	CONTACT AREA
26	TIN	0,8 μ m	BARREL
27	NICKEL	1,2 μ m	ALL OVER
28	GOLD	1,2 μ m	CONTACT AREA
29	TIN	1,2 μ m	BARREL
30	NICKEL	2,5 μ m	ALL OVER
31	SILVER	2,5 μ m	CONTACT AREA
32	TIN	2,5 μ m	BARREL
33	SILVER	1,27 μ m	ALL OVER
34	NICKEL	1,27 μ m	CONTACT AREA
35	BRIGHT TIN	1,27 μ m	BARREL
36	LUBRICATED		