




**Catalog Number: THT-47-478-10**  
**Thermal Transfer Printable Labels**



**Application(s):** Circuit Board & Component ID, SMT - Top/Bottom, Static Dissipative, Through Hole - Bottom, Through Hole - Top

**Agency Approval(s)/Compliance:** ESD-approved for IEC 61340-5-1 and EN 100015-1, UL Recognized

**Size:** 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)

**Printable Area:** 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)

**Web Width:** 0.850" (21.59 mm)

**Label Type/Style:** Label

**Vertical Repeat:** 0.300" (7.62 mm)

**Color:** White

**Finish:** Gloss

**Qty Per Row:** 1

**Material Type:** Polyimide

**Material Description:** Static Dissipative Polyimide

**Recommended Ribbon Series:** 6000

**Suggested Ribbon Part#:** R6011

**After Process:** Yes, this material will work with this application

**Printer Compatibility:** BBP81, Brady 200MVP Plus, Brady 300MVP Plus, Brady 300X-Plus II, Brady 360X-Plus II, Brady 600X-Plus II, Brady IP, Thermal Transfer Printers

**Surface Mount Technology:** Yes, this material will work with this application

**Through Hole Technology:** Top: Yes, Bottom: Yes

**Special Properties:** Low profile, Static dissipative adhesive & liner

**RoHS Compatibility:** Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**QTY/UOM:** 10,000/Roll