

SJ Series

Printed Circuit Surface Mount Jumper

Specifications

Materials:

Contact Material: #C110 Copper Flat Wire

Finish: .0001 minimum thick matte tin over .0001 nickel

Electrical:

Maximum Current: 2 amperes

[Home](#)

[>>Products](#)

[Through Hole](#)

[>>Surface Mount](#)

[Custom Wireform](#)

[News](#)

[About Us](#)

[Distributor &
Representative
Search](#)



[Check Stock](#)

[Compliance](#)

[Site Map](#)

[Contact Us](#)

SJ Series Contacts




SJ Series Dimensions

Part Number	Dimension A	Dimension B	Dimension C
SJ-0805-01-T	.080	.050	.050
SJ-1206-01-T	.120	.062	.050

Ordering Information

Example:



Series Designation:
SJ

Jumper Style:
SJ-0805
SJ-1206

Quantity Per Reel:
01 = 1,000 pieces

Finish:
Matte Tin

Product Description

The SJ-Series is the first true surface mount technology jumper, developed specifically for SMT applications. A low-cost solution that eliminates the need for zero ohm resistors or other even less acceptable substitutions, the SJ-Series is a flat wireform that offers stability, strength, and reliability when mounted. Manufactured using proprietary Components Corporation methods, this jumper is tin/lead plated for highest possible performance.

The SJ-Series features an ultra low profile, yet offers sufficient clearance for circuit board paths, requiring no expensive or time-consuming insulation. Compatible with automated placement and soldering equipment, the SJ-Series is delivered on 7" (1000 piece) tape and reel.



[Open this page as a PDF document](#)

Components Corporation

6 Kinsey Place Denville, NJ 07834 USA

voice: 866.4.COMPCO **fax:** 973.361.5801 **email:** sales@componentscorp.com

©2003 Components Corporation. All Rights Reserved. [Legal Statement](#). [Privacy Notice](#).