

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	HOLE DIA. TOLERANCES	09JUN2006	JJD	YP
	C	ECR 07-025006	25OCT2007	JT	GR

COUPE C-C

3.2MAX

1.2MAX

BODY 0.80±0.03 TONGUE
THICKNESS

Ø 9.92±0.13
FOR 3/8 STUD

Ø 4.15 MAX
FOR INSULATION
Ø 1.14-2.03

SERRATIONS
INSULATION

STAMP : AMP 20

SLEEVE


0.79 MIN

10.90 MIN

22.27 MAX

28.30 MAX

11.91±0.15



SCALE 3:1

WIRE
TERMINAL

1577629-1

BODY : COPPER ANNEALED
FINISH : NICKEL PLATED

SLEEVE : COPPER ANNEALED
FINISH : NICKEL PLATED

INSULATION : PEEK
COLOR : GREY

DESCRIPTION

PART NUMBER

MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN 02NOV2005

JJ. DESPRETZ

CHK 02NOV2005

G. ROBERT

APVD 02NOV2005

Y. PETRONIN

PRODUCT SPEC

108-15356

APPLICATION SPEC

114-15102

WEIGHT

0,84 gr

TYCO ELECTRONICS France SAS

BP 30039, 95301 CERGY-PONTOISE Cedex

NAME
TERMINAL, PEEK PIDG STRATO,
20 AWG


SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-1577629 -

CUSTOMER DRAWING SCALE 5:1 SHEET 1 OF 1 REV C

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.3
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±5

MATERIAL SEE TABLE

FINISH SEE TABLE