







TWIN PLASTIC PEG TYPE


mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ± 0.30	projection	title	www.fciconnect.com	
M	T05-0071	M	W 04/06/05		.XX ± 0.20		PCI EXPRESS		
N	T05-0105	M	W 05/11/05		.XXX ± 0.10		CARD EDGE ASSY		
P	T05-0124	M	W 06/07/05	angles	0° ± 2°				
R	T05-0129	M	W 06/13/05	dr	MAGGIE WU 07/30/02	MM	product family	EDGE CARD	code
S	T05-0153	M	W 07/12/05	enr	R Y LIU 07/30/02		size	dwg no	TWN
T	T05-0208	M	W 09/15/05	chr	R Y LIU 07/30/02	scale	10018783		sheet
U	T10-0007	J	H 1/20/10	appd	JENN TSAO 07/30/02	2:1			1 of 7
sheet index	revision	U	R	T	R	R	U		
	sheet	1	2	3	4	5	6		




SECTION P-P




SINGLE PLASTIC PEG TYPE





mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ± 0.30		projection		www.fciconnect.com	
R					.XX ± 0.20				PCI EXPRESS CARD EDGE ASSY	
				angles	.XXX ± 0.10					
					0° ±2°					
		dr	MAGGIE WU	07/30/02						
		engr	R Y LIU	07/30/02						
		chr	R Y LIU	07/30/02						
		appd	JENN TSAO	07/30/02						
sheet index	revision sheet						scale	2:1	product family	EDGE CARD
									size	dwg no
									A4	10018783
									code	TWN
									sheet	2 of





RECOMMENDED FOOTPRINT

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ±				projection 	title PCI EXPRESS CARD EDGE ASS'Y	
R					.XX ±						
					.XXX ±						
				angles	0° ±2°						
				dr	MAGGIE WU	07/30/02	MM ←→	product family		EDGE CARD	code TWN
				engr	R Y LIU	07/30/02		size	dwg no		
				chr	R Y LIU	07/30/02		scale	A4		
				appd	JENN TSAO	07/30/02	2:1	10018783		sheet 4 of	
sheet index	revision sheet										



NOTES:

1.MATERIAL:

HOUSING: HIGH TEMPERATURE NYLON, GLASS FILLED UL94V-0 RATED.
TERMINAL: COPPER ALLOY.

PLATING: 50u" NICKEL UNDERPLATE ALL OVER
CONTACT AREA PLATING - SEE PRODUCT NUMBER CODE
SOLDER TAIL: TIN OR TIN /LEAD(90/10)- SEE PRODUCT
NUMBER CODE 100u" MIN. OVER 50u" NICKEL.

METAL BOARD LOCKS: COPPER ALLOY.
FINISH: 100u" TIN OR TIN/LEAD(90/10) OVER 50u" NICKEL
UNDERPLATE SEE PRODUCT NUMBER CODE.

2.PRODUCT SPECIFICATION: GS-12-233.

③THE HORIZONTAL AXIS FOR THE HOLE PATTERN IS ESTABLISHED BY

A LINE THROUGH THE CENTER OF THE TWO Ø2.35 HOLES.

THE VERTICAL AXIS IS 90° TO THE HORIZONTAL AXIS, THROUGH THE CENTER
OF DATUM Z.

④NO TIE BAR PERMITTED FROM CARD EDGE TO LEADING EDGE OF PAD FOR PINS A1 AND PIN NUMBERS "F".

⑤CHAMFER EDGES MUST BE FREE OF CUTTING BURRS.

⑥FREQUENCY & LOCATION AT SUPPLIER DISCRETION. RIDGE MAY BE CONTINUOUS WITH NO BREAKS.

7.RoHS COMPATIBLE PRODUCT SPECIFICATIONS:

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2um MINIMUM MATTE TIN OVER 1.27um
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY:

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C±5°C TEMPERATURE FOR
10 SECONDS IN RE-FLOW APPLICATION, REFER TO GS-14-858 FOR OPERATING.

PRODUCT NUMBER CODE

10018783 -X X X X X X □ □

LEAD FREE OPTION

HOUSING COLOR OPTIONS

0-NATURAL

1-BLACK

PEGS OPTIONS

0-PLASTIC PEGS

1-METAL BOARD LOCKS

2-SINGLE PLASTIC PEGS

TERMINAL PLATING OPTIONS

0-50u" Ni UNDERPLATE

30u" Au CONTACT AREA

100u" TIN TAIL AREA ----- COMPATIBLE RoHS

1-50u" Ni UNDERPLATE

15u" Au CONTACT AREA

100u" TIN TAIL AREA ----- COMPATIBLE RoHS

2-50u" Ni UNDERPLATE

GOLD FLASH CONTACT AREA

100u" TIN TAIL AREA ----- COMPATIBLE RoHS

3-50u" Ni UNDERPLATE

30u" Au CONTACT AREA

100u" TIN/LEAD TAIL AREA ----- INCOMPLIANT RoHS

4-50u" Ni UNDERPLATE

15u" Au CONTACT AREA

100u" TIN/LEAD TAIL AREA ----- INCOMPLIANT RoHS

5-50u" Ni UNDERPLATE

GOLD FLASH CONTACT AREA

100u" TIN/LEAD TAIL AREA ----- INCOMPLIANT RoHS

LEAVE BLANK FOR TERMINAL PLATING 3,4,5
"LF" FOR TERMINAL PLATING OPTION 0,1,2

POS OPTIONS

0-36

1-64

2-98

3-164

PACKAGING OPTIONS

T-SOFT TRAY PACKAGING

M-SOFT TRAY PACKAGING & MYLAR TAPE. SEE FIGURE 1

Y-HARD TRAY PACKAGING (FOR 164P ONLY)

Z-HARD TRAY PACKAGING WITH MYLAR (FOR 164P ONLY)

CONNECTOR	# POS REF.	N	DIM "A"	DIM "B"	DIM "C"	"E"
1 PORT	36	6	7.65	25.00	9.15	6.00
4 PORT	64	20	21.65	39.00	23.15	20.00
8 PORT	98	37	38.65	56.00	40.15	37.00
16 PORT	164	70	71.65	89.00	73.15	70.00

TAIL LENGTH OPTIONS

	DIM "D"	PCB THICKNESS	BOARD LOCKS DIM "G"
0	2.30 ± 0.25 -0.13	1.56±0.10	1.70±0.15
1	3.10 ± 0.25 -0.13	2.36±0.10	2.50±0.15
2	2.54±0.25	1.56±0.10	1.70±0.15
3	1.90±0.25	1.56±0.10	1.70±0.15

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ±			projection	title		
U					.XX ±				PCI EXPRESS		
					.XXX ±				CARD EDGE ASS'Y		
				angles	0° ±2'			MM	product family		
				dr	MAGGIE WU	07/30/02	scale		EDGE CARD		
				engr	R Y LIU	07/30/02			code		
				chr	R Y LIU	07/30/02		size			
				appd	JENN TSAO	07/30/02	1:1	A4			
sheet index	revision										
	sheet										

cage code
22526

ACAD

PDM: Rev:U

STATUS: Released

Printed: Jun 28, 2010






FIGURE 1

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI		
ltr	ecn no	dr	date	linear	.X ± 0.25	.XX ± 0.13		www.fciconnect.com		
U				angles	.XXX ± 0.05	0° ± 2°	projection	PCI EXPRESS CARD EDGE ASS'Y		
				dr	MAGGIE WU	06/07/05	MM	product family EDGE CARD		
				enr	R Y LIU	06/07/05	scale	size dwg no		
				chr	R Y LIU	06/07/05	1.5:1	A4 10018783		
				appd	JENN TSAO	06/07/05		code TWN		
sheet index	revision sheet							sheet 7 of		