

4

3

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

6-APRIL-2001

©

COPYRIGHT 2001

ALL RIGHTS RESERVED.

SUGGESTED MATING TAB

9 MIN.

8 MIN.

4^{+0.5}₀

0.25 MAX. CUT-OFF

6.3±0.1

Ø 1.65^{+0.2}₀

1±0.3

45°

8

4

0.64±0.04

0.4±0.2

1. MATERIAL:- #2 HARD BRASS OR NICKEL PLATED STEEL.

2. NO BURRS PERMISSIBLE AT HOLE.

3. TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 85C.

4

 MUST BE FLAT WITHIN 0.076 OVER THIS LENGTH.

5. HOLE MUST BE SYMMETRICAL ABOUT TAB WITHIN 0.076.

2

1

LOC

DIST

IR

-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	EBA0-0049-04	25AUG2004	MJG	BB
	BI	NOMINAL DIM. CORRECTED AND TOLERANCE ADDED	09JAN2012	PKS	RRP

1. CONTINUOUS STRIP ON REELS.

2. WIRE SIZE IS 20-16 AWG.

3. INSULATION RANGE IS 2.29-3.30 DIA.

4

 DIM 5.41mm IN PARALLEL STATE, MAX 6.1mm IN FREE STATE

22.57^{+0.2}/_{-0.1}

BI

22.25±0.25

BI

0.25 MAX CUT-OFF

23.565

8

4.57

3.63

1.65

5.41

4

A

B

A

B

SECTION D-D

3.68

3.30

+

SECTION A-A

SCALE 10:1

5.46

5.08

+

SECTION B-B

SCALE 10:1

0.54

0.44

0.45

0.4

0.54

0.44

0.45

0.4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

D.R.TERRY

06APR2001

CHK

E.SCOTT

09APR2001

APVD

M.WHELAN

09APR2001

PRODUCT SPEC

108-3444

APPLICATION SPEC

114-5029

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm

0-PLC

±0.5

1-PLC

±0.1

2-PLC

±0.05

3-PLC

±

4-PLC

±

ANGLES

±0.5

FINISH

TIN

TE Connectivity

MKI POSITIVE LOCK RECEPTACLE

6.35 (.250) SERIES

SIZE

A260779

CAGE CODE

C-1337968

DRAWING NO

1337968-1

RESTRICTED TO

-

SCALE

5:1

SHEET

1

OF

1

REV

BI

1471-9 (3/11)

Pro/ENGINEER DRAWING