



LED Inspection Handlamp

Description

This battery operated Inspection Handlamp uses LED technology and is supplied complete with a charger and extra battery.

Features

- 4 x 1W LEDs
- 230lm light output
- Polycarbonate housing with aluminium protective frame
- Rubber grip
- Supplied with 2 Lithium rechargeable batteries and docking station for charging
- Charge time is 4 – 5 hours
- Active light time from fully charged is 3 – 4 hours
- 1 year guarantee

Range

LED 4W Inspection Handlamp	19B101
----------------------------	--------

Technical Specification

Input Voltage	100V – 230V ~
	50Hz
Lumen Output	230lm
Light colour temperature	10000k
IP Rating	IP54
Adaptor output	12V DC

Dimensions

Length (incl. hook)	485mm
Diameter	50mm
Weight	0.48kg (lamp only)
	0.78kg (all parts)

Standards

- BS EN 61558-2-6: 1997
- BS EN 61558-1: 1997+A1: 1998+A11: 2003