


Si photodiode S1337 series

For UV to IR, precision photometry



Features

- High UV sensitivity: QE 75 % ($\lambda=200$ nm)
- Low capacitance

Applications

- Analytical equipment
- Optical measurement equipment

■ General ratings / Absolute maximum ratings


Type No.	Dimensional outline/ Window material *	Package (mm)	Active area size (mm)	Effective active area (mm ²)	Absolute maximum ratings		
					Reverse voltage V _R Max. (V)	Operating temperature T _{opr} (°C)	Storage temperature T _{stg} (°C)
S1337-16BQ	①/Q	2.7 × 15	1.1 × 5.9	5.9	5	-20 to +60	-20 to +80
S1337-16BR	②/R						
S1337-33BQ	③/Q	6 × 7.6	2.4 × 2.4	5.7			
S1337-33BR	④/R						
S1337-66BQ	⑤/Q	8.9 × 10.1	5.8 × 5.8	33			
S1337-66BR	⑥/R						
S1337-1010BQ	⑦/Q	15 × 16.5	10 × 10	100			
S1337-1010BR	⑧/R						

■ Electrical and optical characteristics (Typ. T_a=25 °C, unless otherwise noted)

Type No.	Spectral response range λ (nm)	Peak sensitivity wavelength λ_p (nm)	Photo sensitivity S (A/W)					Short circuit current I _{sc} 100 lx		Dark current I _D V _R =10 mV Max. (pA)	Temp. coefficient of I _D T _{CID} (times/°C)	Rise time t _r V _R =0 V R _L =1 k Ω (μs)	Terminal capacitance C _t V _R =0 V f=10 kHz (pF)	Shunt resistance R _{sh} V _R =10 mV		NEP (W/Hz ^{1/2})
			λ_p	200 nm		He-Ne laser 633 nm	GaAs LED 930 nm	Min. (μA)	Typ. (μA)							
				Min.	Typ.											
														Min. (G Ω)	Typ. (G Ω)	
S1337-16BQ	190 to 1100	960	0.5	0.10	0.12	0.33	0.5	4.0	5.3	30	1.15	0.2	65	0.3	1	8.1 × 10 ⁻¹⁵
S1337-16BR	320 to 1100		0.62	-	-	0.4	0.6	4.4	6.2							6.5 × 10 ⁻¹⁵
S1337-33BQ	190 to 1100		0.5	0.10	0.12	0.33	0.5	4.0	5.0							8.1 × 10 ⁻¹⁵
S1337-33BR	320 to 1100		0.62	-	-	0.4	0.6	4.4	6.2							6.5 × 10 ⁻¹⁵
S1337-66BQ	190 to 1100		0.5	0.10	0.12	0.33	0.5	20	27	100		1	380	0.1	0.4	1.3 × 10 ⁻¹⁴
S1337-66BR	320 to 1100		0.62	-	-	0.4	0.6	22	33							1.0 × 10 ⁻¹⁴
S1337-1010BQ	190 to 1100		0.5	0.10	0.12	0.33	0.5	65	78	200		3	1100	0.05	0.2	1.8 × 10 ⁻¹⁴
S1337-1010BR	320 to 1100		0.62	-	-	0.4	0.6	70	95							1.5 × 10 ⁻¹⁴


* Window material Q: quartz glass, R: resin coating

Spectral response




KSPDB0102EA

Photo sensitivity temperature characteristic




KSPDB00053EB

Rise time vs. load resistance




KSPDB0103EA

Dark current vs. reverse voltage




KSPDB0104EA

Shunt resistance vs. ambient temperature



KSPDB0105EA


Photo sensitivity linearity (S1337-1010BQ / BR)



KSPDB00026EB


■ Dimensional outlines (unit: mm)

① S1337-16BQ




KSPDA0105EA

② S1337-16BR




KSPDA0106EA

③ S1337-33BQ




KSPDA0107EA

④ S1337-33BR




KSPDA0108EA

⑤ S1337-66BQ



KSPDA0109EA


⑥ S1337-66BR



KSPDA0110EA


Resin coating may extend a maximum of 0.1 mm above the upper surface of the package.

⑦ S1337-1010BQ



KSPDA0111EA

⑧ S1337-1010BR



KSPDA0112EA

Resin coating may extend a maximum of 0.1 mm above the upper surface of the package.

HAMAMATSU

HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Hamamatsu City, 435-8558 Japan, Telephone: (81) 053-434-3311, Fax: (81) 053-434-5184, <http://www.hamamatsu.com>

U.S.A.: Hamamatsu Corporation, 360 Foothill Road, P.O. Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1) 908-231-0960, Fax: (1) 908-231-1218

Germany: Hamamatsu Photonics Deutschland GmbH, Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49) 08152-3750, Fax: (49) 08152-2658

France: Hamamatsu Photonics France S.A.R.L.: 8, Rue du Saule Trappu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: 33-(1) 69 53 71 00, Fax: 33-(1) 69 53 71 10

United Kingdom: Hamamatsu Photonics UK Limited, 2 Howard Court, 10 Tewin Road, Welwyn Garden City, Hertfordshire AL7 1BW, United Kingdom, Telephone: (44) 1707-294888, Fax: (44) 1707-325777

North Europe: Hamamatsu Photonics Norden AB, Smidesvägen 12, SE-171 41 Solna, Sweden, Telephone: (46) 8-509-031-00, Fax: (46) 8-509-031-01

Italy: Hamamatsu Photonics Italia S.R.L.: Strada della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39) 02-935-81-733, Fax: (39) 02-935-81-741

Information furnished by HAMAMATSU is believed to be reliable. However, no responsibility is assumed for possible inaccuracies or omissions. Specifications are subject to change without notice. No patent rights are granted to any of the circuits described herein. ©2001 Hamamatsu Photonics K.K.