

Coaxial

Precision Fixed Attenuator

50Ω 1W 15dB DC to 2000 MHz

HAT-15+
HAT-15



Maximum Ratings

Operating Temperature	-45°C to 100°C
Storage Temperature	-55°C to 100°C

Features

- excellent VSWR, 1.05:1 typ.
- excellent flatness, 0.20 dB typ. to 2000 MHz
- usable to 4000 MHz

CASE STYLE: FF747

Connectors	Model	Price	Qty.
BNC Male-BNC Female	HAT-15(+)	9.95 ea.	(1-9)


Applications

- PCS
- instrumentation
- cellular

**+ RoHS compliant in accordance
with EU Directive (2002/95/EC)**

The +Suffix identifies RoHS Compliance. See our web site
for RoHS Compliance methodologies and qualifications.

Outline Drawing



Outline Dimensions (inch/mm)

B	D	wt
.62	1.94	grams
15.75	49.28	30.0



Electrical Specifications

FREQ. RANGE (MHz)	ATTENUATION (dB) Flatness*					VSWR (:1)			MAX. INPUT POWER (W)
	DC-0.5 GHz		DC-1 GHz	DC-2 GHz	Total Band Max.	DC-0.5 GHz	DC-1 GHz	DC-2 GHz	
	Nom.	Typ.	Typ.	Typ.		Typ.	Typ.	Typ.	
DC-2000	15±0.2	0.05	0.10	0.20	0.30	1.05	1.10	1.15	1.0

* Flatness = variation over band divided by 2.

Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	15.00	1.00
50.00	15.00	1.00
100.00	15.01	1.00
250.00	15.02	1.01
500.00	15.04	1.02
750.00	15.07	1.02
1000.00	15.08	1.04
1500.00	15.14	1.09
1750.00	15.20	1.14
2000.00	15.25	1.19



designers kit available

Kit No.	No. of Units in Kit	Description	Price \$ per Kit
K1-HAT	5	1 of ea. HAT-3(+), 6(+), 10(+), 20(+), 30(+)	48.95
K2-HAT	10	1 of ea. HAT-1(+), 2(+), 3(+), 4(+), 5(+), 6(+), 7(+), 8(+), 9(+), 10(+)	98.95

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. E
M98898
EDR-5087/1-15
HAT-15
RVN/LC/CP/AM
060817
Page 1 of 1