



Important notes about Classic Panel Mount Indicator Catalog Pages

SCROLL DOWN TO VIEW CATALOG PAGE

This catalog page is out-of-print and is used with the understanding that the information shown could be out-of-date. In many cases, part numbers shown on this page are discontinued. Most notably, many "Complete Assembly" parts, which consist of a cap and a base, can no longer be ordered by the 14-digit ordering code. To obtain these parts, please order the cap and base part numbers separately. This process provides the components contained with the original "Complete Assembly" part number.

All Dialight Classic Panel Mount Indicators need a leading 3-digit numerical series. In some cases, this catalog will show a 2-digit series. In this case, please add a leading zero. For example, 81-0211-300 becomes 081-0211-300.

Part numbers listed on Dialight catalog pages designate parts with Red lenses. For ordering lens colors other than red, consult the chart below. In most cases, the color is dictated by the 7th digit. For example, 095-0932-003 for a green cap.

Lens Colors	
1 - Red	5 - White
2 - Green	6 - Light Yellow
3 - Yellow	7 - Clear
4 - Blue	

[Click here for a cross reference guide to assembly part numbers.](#)

[Click here to view Frequently Asked Questions concerning Panel Mount Indicators.](#)

SCROLL DOWN TO VIEW CATALOG PAGE

A diagram of a crane. It features a vertical support structure with a pulley at the top. A rope is attached to a fixed point on the support, passes under a pulley on the crane's frame, and then up to the top pulley. The crane's frame is shown as a trapezoidal shape with a horizontal beam at the top where the pulley is located.

**T-1 3/4
MIDGET
FLANGE BASE**
See lamp ratings
on page J.

WATER-TIGHT, OIL-TIGHT, DUST-TIGHT ON THE FACE OF THE PANEL


Conform to MIL-L-3661B

367-8430-0931-503
LH89/1: LC35RN2

368-8430-0111-203
LH89/1: LC36RD2

- **Anti-rotation (locked) construction:** Provides for secure locking of the socket terminal assembly in the mounting bushing and of the center terminal to the insulating disc. The notched mounting bushing receives the matched insulating disc to prevent the rotation of the mounting bushing.

FRONT MOUNTING



max. panel
thickness 1 1/64"

(LH 89/1) 367-8430-09-503


- **Mounting Bushing:** Aluminum, black anodize finish.
- **Internal-tooth Lockwasher and Mounting Nut:** Steel, cadmium plated with yellow iridescent chromate finish.
- **Terminals:** Brass, hot tinned, with elongated slots.
- **Lens:** High impact plastic.



- **Mounting Bushing:** Brass, black nickel finish.
- **Mounting Nut:** Brass, white nickel finish.
- **Internal-tooth Lockwasher:** Phosphor bronze, white nickel finish.
- **Terminals:** Brass, hot tinned with elongated slots.

367 SERIES
368 SERIES
369 SERIES

BASE PART NUMBER



Part numbers shown in gray are normally in inventory at your Dialight Distributor.

Order complete with lamp to be assured of receiving the indicator light and correct lamp together for immediate use.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[368-8430-0111-203](#) [161-0111-203](#) [161-0114-203](#) [367-8430-09-503](#) [128-0933-003](#) [128-0931-003](#) [128-0932-003](#)
[161-0113-203](#) [128-0973-003](#) [160-0112-203](#) [128-0975-801](#) [368-8430-0111-805](#) [368-8430-0112-806](#) [160-0114-203](#)
[128-0934-003](#) [128-0975-003](#) [161-0112-203](#) [160-0111-203](#) [128-0972-003](#) [160-0117-203](#) [161-0117-203](#) [160-0113-](#)
[203](#) [128-0974-003](#) [128-0935-003](#) [367-8430-09-807](#)