

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

DIST

REVISIONS

ES

00

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

REVISED PER ECO-11-005033

29MAR11

RK

HMR

NOTES



MATERIAL & FINISH

CONTACT: COPPER ALLOY

Au PL. ON Pd-Ni PL. AT CONTACT AREA OVER Ni PL.

MATTE TIN PL. AT TINE AREA OVER Ni PL.

HOUSING: THERMO-PLASTICS, UL94V-0

SHELL : COPPER ALLOY, TIN PL.

2 GENERAL TOLERANCE

10 ≥ ±0.2

30 ≥ >10 ±0.25

100 ≥ >30 ±0.3

ANGLES ±5°






3. MATERIAL/PARTS WHICH ARE CONTAINED THE PROHIBITION

SUBSTANCE FOR ENVIRONMENTAL RELATED SUBSTANCE CONTROL

STANDARD EN-022 (ENVIRONMENT RELATED SUBSTANCE)


MUST NOT USE IN PRODUCT AND MANUFACTURING PROCESS

4. CADMIUM CONTENT: 5ppm UNDER

TAPE
1-5353583-1 ONLYREFERENCE DIMENSION OF
P.C.BOARD(MOUNTING SIDE)


SECTION A-A

5353583-1,2



WITH TAPE	BLACK	1-5353583-4
WITH OUT TAPE	BLACK	5353583-4
PRELIMINARY NOT FOR PRODUCTION	WHITE	5353583-3
PRELIMINARY NOT FOR PRODUCTION	BLACK	5353583-2
WITH TAPE	WHITE	1-5353583-1
WITH OUT TAPE	WHITE	5353583-1
REMARKS	HOUSING COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

DWN

J.JIANG

23MAR04

CHK

S.YAO

23MAR04

APVD

T.SASAKI

23MAR04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

RECEPTACLE ASS'Y R/A SMT
STANDARD TYPE USB CONNECTOR

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

SHEET

REV

A1

4:1

1 OF 2

A1

4






3

2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS					
ES		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



- △ MATERIAL & FINISH
CONTACT: COPPER ALLOY
Au PL. ON Pd-Ni PL. AT CONTACT AREA OVER Ni PL.
MATTE TIN PL. AT TINE AREA OVER Ni PL.
HOUSING: THERMO-PLASTICS, UL94V-0
SHELL : COPPER ALLOY, TIN PL.
- 2 GENERAL TOLERANCE
10 ≥ : ± 0.2
30 ≥ > 10 : ± 0.25
100 ≥ > 30 : ± 0.3
ANGLES : ± 5°
3. MATERIAL/PARTS WHICH ARE CONTAINED THE PROHIBITION
SUBSTANCE FOR ENVIRONMENTAL RELATED SUBSTANCE CONTROL
STANDARD EN-022 (ENVIRONMENT RELATED SUBSTANCE)
MUST NOT USE IN PRODUCT AND MANUFACTURING PROCESS
4. CADMIUM CONTENT: 5ppm UNDER



5353583-3,4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		STE TE Connectivity NAME RECEPTACLE ASS'Y R/A SMT STANDARD TYPE USB CONNECTOR SIZE CAGE CODE DRAWING NO RESTRICTED TO A3 00779 C-5353583 —			
DIMENSIONS: MM 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±						
MATERIAL 	FINISH 	CUSTOMER DRAWING		SCALE 4:1	SHEET 2 of 2	REV A1	