

DATE	REVISIONS	REV
1-5-98	E.C.N. #10BRDR./	A

DRAWING NUMBER	REV
OED-PT-23G	A

ELECTRO-OPTICAL CHARACTERISTICS $T_A = 25^\circ\text{C}$


PARAMETER	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
COLLECTOR DARK CURRENT	I_{ceo}	$V_{ce} = 10\text{V}$ $E_e = 0.5\text{mW/cm}^2$			1000	nA
COLLECTOR LIGHT CURRENT	I_c	$V_{ce} = 5\text{V}$ $E_e = 0.5\text{mW/cm}^2$	5.0			mA
COLLECTOR-EMITTER SATURATION VOLTAGE	$V_{ce(sat)}$	$I_c = 0.2\text{mA}$ $E_e = 0.5\text{mW/cm}^2$			1.4	V
SWITCHING SPEEDS:		$V_{cc} = 5\text{V}$				
RISING TIME	T_r	$I_c = 1\text{mA}$		85		μS
FALLING TIME	T_f	$R_I = 100\Omega$		75		μS
PEAK WAVELENGTH	λ_p			800		nm
ANGULAR RESPONSE	$\Delta\theta$			± 30		DEG
LENS COLOR:	CLEAR					

LIMITS OF SAFE OPERATION AT 25°C

PARAMETER	MAX	UNITS
COLLECTOR-EMITTER VOLTAGE (V_{ceo})	30	V
EMITTER-COLLECTOR VOLTAGE (V_{eco})	4	V
POWER DISSIPATION	150	mW
OPERATING TEMP.	-20 TO $+100$	$^\circ\text{C}$
STORAGE TEMP.	-20 TO $+100$	$^\circ\text{C}$
SOLDERING TEMP.	$+260$	$^\circ\text{C}$
2.0mm FROM BODY	3 SEC. MAX	

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



UNLESS OTHERWISE SPECIFIED TOLERANCE IS $\pm 0.25\text{mm}$ ($\pm 0.010"$)

au

LUMEX
INCORPORATED

290 E. HELLEN ROAD
PALATINE, ILLINOIS 60067
(847) 359-2790

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INCORPORATED. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INCORPORATED, THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE: 2-14-95	DWN:	CHK'D:	APPD:
SCALE: N/A			

HIGH OUTPUT, SIDE-EMITTING,
PHOTODARLINGTON, WATER CLEAR LENS.

PAGE 1 OF 1	DRAWING NUMBER OED-PT-23G	REV A
-------------	------------------------------	----------