

49 PCB Enclosed Relay

GENERAL SPECIFICATIONS



UL508
File No. E258297



- Small size
- Rated up to 10A
- TV3 rating
- 1/3 HP rating @ 120VAC for inductive switching
- Variety of footprint configurations for wide selection of applications




www.magnecraft.com
relays@magnecraft.com
847-441-2540

Contact Characteristics			49 PCB Relay 10A		49 PCB Relay 5A		49 PCB Relay 3 A	
Contact form			SPDT		SPDT		SPDT	
Contact materials			Silver Alloy		Silver Alloy		Fine Silver	
Thermal carrying current			15A (NO)	10A (NC)	5A (NO)	5A (NC)	15A (NO)	3 A (NC)
Maximum switching voltage		~	15A @ 277 VAC 50/60Hz	10A @ 277 VAC 50/60Hz	5A @ 120 VAC 50/60Hz		15A @ 150 VAC 50/60Hz	3 A @ 150 VAC 50/60Hz
		≡	15A @ 28 VDC	10A @ 28 VDC	5A @ 28 VDC		15A @ 28 VDC	3 A @ 28 VDC
Contact ratings			1/3 HP @ 120 VAC		1/3 HP @ 120 VAC		1/3 HP @ 120 VAC	1/3 HP @ 120 VAC
			1/3 HP @ 240 VAC		1/6 HP @ 240 VAC		1/3 HP @ 240 VAC	1/6 HP @ 240 VAC
			1/4 HP @ 277 VAC		1/8 HP @ 277 VAC		1/4 HP @ 277 VAC	1/8 HP @ 277 VAC
			B300 Pilot Duty (120/240 VAC)		B300 Pilot Duty (120/240 VAC)		B300 Pilot Duty (120/240 VAC)	
Minimum switching requirement			100 mA		100 mA		100 mA	
Coil Characteristics								
Voltage range		≡	3 to 24 VDC		3 to 24 VDC		3 to 24 VDC	5 to 24 VDC
Operating range		≡	75% to 110% of nominal		75% to 110% of nominal		75% to 110% of nominal	
Average power consumption		≡	0.11 W		0.11 W		0.11 W	
Drop-out voltage threshold		≡	10%		10%		10%	
Performance Characteristics								
Electrical life			100,000 operations @ rated current		100,000 operations @ rated current		100,000 operations @ rated current	
Mechanical life			10,000,000 operations unpowered		10,000,000 operations unpowered		10,000,000 operations unpowered	
Response time			25 ms		25 ms		25 ms	
Dielectric strength	Between coil and contact	~	1500 V(rms)		2500 V(rms)		2500 V(rms)	
	Between contacts	~	500 V(rms)		500 V(rms)		500 V(rms)	
Environment								
Storage temperature			-40...+85 °C		-40...+85 °C		-40...+85 °C	
Operating temperature			-40...+55 °C		-40...+55 °C		-40...+55 °C	
Operational vibration resistance			3 g-n, 10 - 55 Hz		3 g-n, 10 - 55 Hz		3 g-n, 10 - 55 Hz	
Shock resistance			10 g-n		10 g-n		10 g-n	
Weight			42 grams		42 grams		42 grams	
Available footprint styles			RE1C1		RE1C1 & RE1C2		RE1C1	


DIMENSIONS

shown in inches (millimeters)

STYLE RE1C1




STYLE RE1C2




WIRING DIAGRAMS

top view

RE1C1




RE1C2



CIRCUIT BOARD PIN SPACING

top view (from component side)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[W49RE1C2VF-12DC-SIL](#)