







DWG. NO. 0097-0610-02	
REVISIONS	
ECO-E4187 .2825 DIM WAS .312 UPDATED TO CURRENT FORMAT SDH 11/25/03 EWS 11/25/03	
	18

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO LAIRD TECHNOLOGIES.
IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN LAIRD TECHNOLOGIES
PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM LAIRD TECHNOLOGIES.

DWG. NO.
0097-0610-02

MATERIAL: .005±.0003 THICK BeCu ALLOY 25 1/4 HARD	TOLERANCES NOT SHOWN			DRAWN BY: JR		DATE: 02/27/89	
	DECIMAL 2 PL'S ±			CHECKED: BJ		DATE: 03/23/89	
	DECIMAL 3 PL'S ± .010			APPROVED: BJ		DATE: 03/23/89	
HEAT TREAT: TO DPH 373 MIN USING A 500 GRAM LOAD	ANGULAR ±			.187 PITCH CLIP-ON FINGER STOCK			
THICKNESS AFTER: CLEANING .0046 MIN	THIRD ANGLE PROJECTION 						
FINISH: AS REQUIRED	UNITS: INCH [MM]	SCALE: 3:1	REF. DWG NO. SK-072182-AE			REV	
			DWG. NO. 0097-0610-02			18	
CAD MAINTAINED DRAWING. MANUAL CHANGES UNAUTHORIZED. 			SHEET 1 OF 1				