



SK22A thru SK26A



Surface Mount Schottky Barrier Rectifiers
Reverse Voltage 20 to 60 Volts Forward Current 2.0 Amperes

Features

- ◆ For surface mounted applications
- ◆ Metal-Semiconductor junction with guarding
- ◆ Epitaxial construction
- ◆ Very low forward voltage drop
- ◆ High current capability
- ◆ Plastic material has UL flammability classification 94V-0
- ◆ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications



DO-214AC (SMA)



Dimensions in inches and (millimeters)

Mechanical Data

- ◆ Case : JEDEC DO-214AC(SMA) molded plastic
- ◆ Polarity : Indicated by cathode band
- ◆ Weight : 0.002 ounce, 0.064 gram

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Parameter	Symbols	SK22A	SK23A	SK24A	SK25A	SK26A	Units
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	Volts
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	Volts
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	Volts
Maximum average forward rectified current @T _L =100°C	I _(AV)	2.0					Amps
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	50.0					Amps
Maximum forward voltage at 2.0A DC	V _F	0.50			0.70		Volts
Maximum DC reverse current at rated DC blocking voltage @T _J = 25°C @T _J =100°C	I _R	0.5 20					mA
Typical junction capacitance (Note1)	C _J	200					pF
Typical thermal resistance (Note 2)	R _{θJL}	15					°C/W
Operating junction temperature range	T _J	-55 to +125					°C
Storage temperature range	T _{STG}	-55 to +150					°C

- Notes:**
1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
 2. Thermal Resistance Junction to Lead.

RATINGS AND CHARACTERISTIC CURVES

