

ARK-3202

Mobile Intel® ATOM N270 Fanless Solution with Dual Display and Multiple I/O

NEW



Features

- Fanless, Intel® ATOM Compact Embedded Box IPC
- Intel® ATOM N270 Processor at 1.6 GHz
- Dual display and support for wide screen with high resolution
- Supports 2 GbE, 5 USB 2.0 and max to 5 COMs ports
- Optional WLAN and HSDPA modules for advanced in-vehicle solution
- Optional GPS on-board for in-vehicle application
- IP40





Specifications


		ARK-3202L-S6A1E	ARK-3202F-S6A1E	ARK-3202V-S6A1E
Processor System	CPU	Intel® ATOM N270		
	Max. speed	1.6 GHz		
	System Chipset	Intel™ 945GSE + ICH7-M Chipset		
	Front Side Bus	400/533MHz		
	BIOS	AWAR 4 Mbit, SPI		
Memory	Technology	DDR2 400/533 MHz (945GSE)		
	Max. Capacity	2 GB		
	Socket	1 x 200-pin SODIMM		
Graphics	Chipset	Integrated graphics built in Intel® 945GSE		
	Interface	CRT Interface DVI Interface, compliant with DVI 1.0 36-bit LVDS interface(Optional)		
Ethernet	LAN 1	10/100/1000 Mbps Ethernet controller, support Wake On LAN		
	LAN 2	10/100/1000 Mbps Ethernet controller, support Wake On LAN		
Audio	Amplifier	2.2W amplifier		
	Interface	Spkr-out, Mic-in		
IO interface	Serial Interface	2 x RS-232 port	2 x RS-232 & 3 x RS-232/422/485 w/ Auto Flow Control	2 x RS-232 & 3 x RS-232/422/485 w/ Auto Flow Control
	USB Interface	5 x USB ports, Compliant with USB 2.0		
Others	Digital I/O	-		
	GPS	-		GPS on Board (optional)
	Thermal alarm	-		
	Watchdog timer	255 levels timer interval, setup by software		
Expansion	MiniPCle	-	2 x Mini CPlE	2 x Mini CPlE
Storage	HDD	1 x SATA 2.5" HDD	1x SATA 2.5" HDD	N/A
	SSD	Supports CompactFlash socket for type I/II CompactFlash disk		
Software support	Microsoft Windows	Vista, XP Professional, XP Embedded		
	Linux	Fedora 9.0		
Power requirement	Power Type	AT/ATX		
	Power Input Voltage	12 V _{DC} ~ 24 V _{DC}	12 V _{DC} ~ 24 V _{DC}	9 V _{DC} ~ 32 V _{DC} (for In Vehicle)
	Minimum Power Input	12V-24V, 3.0A-1.5A		
	Power Adapter	AC to DC, DC19V/3.42A, 65W (Optional)		
Power consumption	Typical	Typical 13.3W (CPU is Intel ATOM N270 1.6 GHz and w/o expansion)		
	Max.	Max. 17.1W (CPU is Intel ATOM N270 1.6 GHz and w/o expansion)		
Mechanical	Construction	Aluminum housing		
	Mounting	Desk/wall-mounting		
	Dimensions (W x H x D)	220 mm x 68 mm x 200 mm (8.66" x 2.67" x 7.87")		
	Weight	3 kg (6.6 lb)		
Environment	Operating Temperature	With Industrial Grade CompactFlash disk: -20 ~ 60° C (-4 ~ 140° F) With 2.5-inch extended temperature hard disk 0 to 45° C (32 ~ 112° F), with air flow		
	Storage Temperature	-40 ~ 85° C (-40 ~ 185° F)		
	Relative Humidity	95% @ 40° C (non-condensing)		
	Vibration Loading During Operation	With CompactFlash disk: 5 Grms, IEC 60068-2-64, random, 5 ~ 500 Hz, 1 Oct./min, 1 hr/axis. With 2.5-inch hard disk: 1 Grms, IEC 60068-2-64, random, 5 ~ 500 Hz, 1 Oct./min, 1 hr/axis.		
	Shock During Operation	With CompactFlash disk: 50 G, IEC 60068-2-27, half sine, 11 ms duration With hard disk: 20 G, IEC 60068-2-27, half sine, 11 ms duration		
	EMC	CE/FCC Class A, CCC, BSMI		
	Safety Certifications	UL, CCC, BSMI		

Dimensions


Unit: mm



Front Panel External I/O Mechanical Layout/Drawing



Rear Panel External I/O Mechanical Layout/Drawing



Packing List

Part Number	Description
-	1 x ARK-3202 Unit
1960014487T00C	2 x Desk/Wall mount plate
1700009001	1 x 2-pin Phoenix DC power connector
-	1 x User Manual (Simplified Chinese)
-	1 x Utility CD

Ordering Information

Part Number	Description
ARK-3202F-S6A1E	Intel ATOM N270 1.6GHz Compact Embedded Box IPC, w/ 2 x GbE, 5 x USB 2.0, 4 x COM, 2 x MiniPCle, GPS, VGA, DVI, Audio
ARK-3202L-S6A1E	Intel ATOM N270 1.6GHz Compact Embedded Box IPC, w/ 2 x GbE, 5 x USB 2.0, 2 x COM, VGA, DVI, Audio
ARK-3202V-S6A1E	Intel ATOM N270 1.6 GHz Compact Embedded Box IPC, w/ 2 x GbE, 5 x USB 2.0, 4 x COM, 2 x MiniPCle, GPS, VGA, DVI, Audio

Optional Items

Part Number	Description
1757000222	AC-to-DC Adapter, DC19 V/3.42A 65W, with Phoenix Power Plug, 0 ~ 40° C for Home and Office Use
1700001947	Power cable 2-pin 180 cm, USA for ARK-338X
1700001948	Power cable 2-pin 180 cm, Europe for ARK-338X
1700001949	Power cable 2-pin 180 cm, UK for ARK-338X
1700009398	LVDS power cable for ARK-3202