


## SEMITRANS® M Low Loss IGBT Modules

### SKM 300 GB 124 D



SEMITRANS 3



GB

#### Features

- MOS input (voltage controlled)
- N channel, homogeneous Silicon structure (NPT- Non punch-through IGBT)
- Low inductance case
- Very low tail current with low temperature dependence
- High short circuit capability, self limiting to  $6 \cdot I_{Cnom}$
- Latch-up free
- Fast & soft inverse CAL diodes<sup>8)</sup>
- Isolated copper baseplate using DCB Direct Copper Bonding Technology without hard mould
- Large clearance (12 mm) and creepage distances (20 mm)

#### Typical Applications

- Switching (not for linear use)
- AC inverter drives
- UPS

<sup>1)</sup>  $T_{case} = 25^\circ\text{C}$ , unless otherwise specified

<sup>2)</sup>  $I_F = -I_C$ ,  $V_R = 600\text{ V}$ ,  $-di_F/dt = 2000\text{ A}/\mu\text{s}$ ,  $V_{GE} = 0\text{ V}$

<sup>3)</sup> Use  $V_{GEoff} = -5 \dots -15\text{ V}$

<sup>8)</sup> CAL = Controlled Axial Lifetime Technology

Cases and mech. data → page 6  
SEMITRANS 3

| Absolute Maximum Ratings |                                                      | Values                 | Units                |
|--------------------------|------------------------------------------------------|------------------------|----------------------|
| Symbol                   | Conditions <sup>1)</sup>                             |                        |                      |
| $V_{CES}$                |                                                      | 1200                   | V                    |
| $V_{CGR}$                | $R_{GE} = 20\text{ k}\Omega$                         | 1200                   | V                    |
| $I_C$                    | $T_{case} = 25/65^\circ\text{C}$                     | 380 / 300              | A                    |
| $I_{CM}$                 | $T_{case} = 25/65^\circ\text{C}; t_p = 1\text{ ms}$  | 760 / 600              | A                    |
| $V_{GES}$                |                                                      | $\pm 20$               | V                    |
| $P_{tot}$                | per IGBT, $T_{case} = 25^\circ\text{C}$              | 1650                   | W                    |
| $T_j, (T_{stg})$         |                                                      | $-40 \dots +150 (125)$ | $^\circ\text{C}$     |
| $V_{isol}$               | AC, 1 min.                                           | 2500                   | V                    |
| humidity                 | DIN 40040                                            | Class F                |                      |
| climate                  | DIN IEC 68 T.1                                       | 40/125/56              |                      |
| Inverse Diode            |                                                      |                        |                      |
| $I_F = -I_C$             | $T_{case} = 25/80^\circ\text{C}$                     | 260 / 180              | A                    |
| $I_{FM} = -I_{CM}$       | $T_{case} = 25/80^\circ\text{C}; t_p = 1\text{ ms}$  | 760 / 600              | A                    |
| $I_{FSM}$                | $t_p = 10\text{ ms}; \sin.; T_j = 150^\circ\text{C}$ | 2 200                  | A                    |
| $I^2t$                   | $t_p = 10\text{ ms}; T_j = 150^\circ\text{C}$        | 24 200                 | $\text{A}^2\text{s}$ |

| Characteristics             |                                                                                                                              | min.           | typ.      | max.       | Units                     |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------|----------------|-----------|------------|---------------------------|
| Symbol                      | Conditions <sup>1)</sup>                                                                                                     |                |           |            |                           |
| $V_{(BR)CES}$               | $V_{GE} = 0, I_C = 4\text{ mA}$                                                                                              | $\geq V_{CES}$ | —         | —          | V                         |
| $V_{GE(th)}$                | $V_{GE} = V_{CE}, I_C = 8\text{ mA}$                                                                                         | 4,5            | 5,5       | 6,5        | V                         |
| $I_{CES}$                   | $V_{GE} = 0 \quad \left. \begin{matrix} T_j = 25^\circ\text{C} \\ T_j = 125^\circ\text{C} \end{matrix} \right\}$             | —              | —         | 10         | mA                        |
|                             | $V_{CE} = V_{CES}$                                                                                                           | —              | 15        | —          | mA                        |
| $I_{GES}$                   | $V_{GE} = 20\text{ V}, V_{CE} = 0$                                                                                           | —              | —         | 0,4        | $\mu\text{A}$             |
| $V_{CESat}$                 | $I_C = 200\text{ A} \quad \left. \begin{matrix} V_{GE} = 15\text{ V}; \\ T_j = 25 (125)^\circ\text{C} \end{matrix} \right\}$ | —              | 2,1(2,4)  | 2,45(2,85) | V                         |
| $V_{CESat}$                 | $I_C = 300\text{ A} \quad \left. \begin{matrix} V_{GE} = 15\text{ V}; \\ T_j = 25 (125)^\circ\text{C} \end{matrix} \right\}$ | —              | 2,6(3,1)  | —          | V                         |
| $g_{fs}$                    | $V_{CE} = 20\text{ V}, I_C = 200\text{ A}$                                                                                   | 110            | —         | —          | S                         |
| $C_{CHC}$                   | per IGBT                                                                                                                     | —              | —         | 700        | pF                        |
| $C_{ies}$                   | $V_{GE} = 0$                                                                                                                 | —              | 13        | —          | nF                        |
| $C_{oes}$                   | $V_{CE} = 25\text{ V}$                                                                                                       | —              | 2         | —          | nF                        |
| $C_{res}$                   | $f = 1\text{ MHz}$                                                                                                           | —              | 1,0       | 1,3        | nF                        |
| $L_{CE}$                    |                                                                                                                              | —              | —         | 20         | nH                        |
| $t_{d(on)}$                 | $V_{CC} = 600\text{ V}$                                                                                                      | —              | 90        | —          | ns                        |
| $t_r$                       | $V_{GE} = -15\text{ V} / +15\text{ V}^{3)}$                                                                                  | —              | 60        | —          | ns                        |
| $t_{d(off)}$                | $I_C = 200\text{ A, ind. load}$                                                                                              | —              | 600       | —          | ns                        |
| $t_f$                       | $R_{Gon} = R_{Goff} = 6\text{ }\Omega$                                                                                       | —              | 55        | —          | ns                        |
| $E_{on}$                    | $T_j = 125^\circ\text{C}$                                                                                                    | —              | 29        | —          | mWs                       |
| $E_{off}$                   |                                                                                                                              | —              | 28        | —          | mWs                       |
| Inverse Diode <sup>8)</sup> |                                                                                                                              |                |           |            |                           |
| $V_F = V_{EC}$              | $I_F = 200\text{ A} \quad \left. \begin{matrix} V_{GE} = 0\text{ V}; \\ T_j = 25 (125)^\circ\text{C} \end{matrix} \right\}$  | —              | 2,0(1,8)  | 2,5        | V                         |
| $V_F = V_{EC}$              | $I_F = 300\text{ A} \quad \left. \begin{matrix} V_{GE} = 0\text{ V}; \\ T_j = 25 (125)^\circ\text{C} \end{matrix} \right\}$  | —              | 2,25(2,1) | —          | V                         |
| $V_{TO}$                    | $T_j = 125^\circ\text{C}$                                                                                                    | —              | 1,1       | 1,2        | V                         |
| $r_t$                       | $T_j = 125^\circ\text{C}$                                                                                                    | —              | —         | 5,5        | $\text{m}\Omega$          |
| $I_{RRM}$                   | $I_F = 200\text{ A}; T_j = 125^\circ\text{C}^{2)}$                                                                           | —              | 120       | —          | A                         |
| $Q_{rr}$                    | $I_F = 200\text{ A}; T_j = 125^\circ\text{C}^{2)}$                                                                           | —              | 25        | —          | $\mu\text{C}$             |
| Thermal characteristics     |                                                                                                                              |                |           |            |                           |
| $R_{thjc}$                  | per IGBT                                                                                                                     | —              | —         | 0,075      | $^\circ\text{C}/\text{W}$ |
| $R_{thjc}$                  | per diode                                                                                                                    | —              | —         | 0,18       | $^\circ\text{C}/\text{W}$ |
| $R_{thch}$                  | per module                                                                                                                   | —              | —         | 0,038      | $^\circ\text{C}/\text{W}$ |




Fig. 1 Rated power dissipation  $P_{tot} = f(T_C)$




Fig. 2 Turn-on /off energy =  $f(I_C)$




Fig. 3 Turn-on /off energy =  $f(R_G)$




Fig. 4 Maximum safe operating area (SOA)  $I_C = f(V_{CE})$




Fig. 5 Turn-off safe operating area (RBSOA)




Fig. 6 Safe operating area at short circuit  $I_C = f(V_{CE})$




Fig. 8 Rated current vs. temperature  $I_C = f(T_C)$




Fig. 9 Typ. output characteristic,  $t_p = 80\text{ μs}$ ;  $25^\circ\text{C}$




Fig. 10 Typ. output characteristic,  $t_p = 80\text{ μs}$ ;  $125^\circ\text{C}$

$$P_{\text{cond}(t)} = V_{\text{CEsat}(t)} \cdot I_{\text{C}(t)}$$

$$V_{\text{CEsat}(t)} = V_{\text{CE(To)(Tj)}} + r_{\text{CE(Tj)}} \cdot I_{\text{C}(t)}$$

$$V_{\text{CE(To)(Tj)}} \leq 1,3 + 0,0005 (T_j - 25) [\text{V}]$$

$$\text{typ.: } r_{\text{CE(Tj)}} = 0,004 + 0,000013 (T_j - 25) [\Omega]$$

$$\text{max.: } r_{\text{CE(Tj)}} = 0,0058 + 0,000018 (T_j - 25) [\Omega]$$

$$\text{valid for } V_{\text{GE}} = +15 \frac{+2}{-1} [\text{V}]; I_C \geq 0,3 I_{\text{Cnom}}$$

Fig. 11 Saturation characteristic (IGBT)  
Calculation elements and equations




Fig. 12 Typ. transfer characteristic,  $t_p = 80\text{ μs}$ ;  $V_{CE} = 20\text{ V}$




Fig. 13 Typ. gate charge characteristic




Fig. 14 Typ. capacitances vs.  $V_{CE}$




Fig. 15 Typ. switching times vs.  $I_C$




Fig. 16 Typ. switching times vs. gate resistor  $R_G$




Fig. 17 Typ. CAL diode forward characteristic




Fig. 18 Diode turn-off energy dissipation per pulse




Fig. 19 Transient thermal impedance of IGBT  
 $Z_{thJC} = f(t_p)$ ;  $D = t_p / t_c = t_p \cdot f$




Fig. 20 Transient thermal impedance of inverse CAL diodes  
 $Z_{thJC} = f(t_p)$ ;  $D = t_p / t_c = t_p \cdot f$




Fig. 22 Typ. CAL diode peak reverse recovery current  $I_{RR} = f(I_F; R_G)$




Fig. 23 Typ. CAL diode peak reverse recovery current  $I_{RR} = f(di_F/dt; R_G)$





Fig. 24 Typ. CAL diode recovered charge  
 $Q_{RR} = f(di_F/dt; I_F; R_G)$



Case outline and circuit diagram

| Mechanical Data |                         |      |      |      |        | Units            |
|-----------------|-------------------------|------|------|------|--------|------------------|
| Symbol          | Conditions              |      | min. | typ. | max.   |                  |
| M <sub>1</sub>  | to heatsink, SI Units   | (M6) | 3    | —    | 5      | Nm               |
|                 | to heatsink, US Units   |      | 27   | —    | 44     | lb.in.           |
| M <sub>2</sub>  | for terminals, SI Units | (M6) | 2,5  | —    | 5      | Nm               |
|                 | for terminals, US Units |      | 22   | —    | 44     | lb.in.           |
| a               |                         |      | —    | —    | 5x9,81 | m/s <sup>2</sup> |
| w               |                         |      | —    | —    | 325    | g                |

This is an electrostatic discharge sensitive device (ESDS). Please observe the international standard IEC 747-1, Chapter IX.

Three devices are supplied in one SEMIBOX A without mounting hardware, which can be ordered separately under Ident No. 33321100 (for 10 SEMITRANS 3)

Larger packing units of 12 or 20 pieces are used if suitable

Accessories → page B 6 – 4

SEMIBOX → page C - 1.