

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
		REVISED PER ECO-13-001940		01OCT2013	KH	MB

NOTES:

MATERIAL:
TERMINAL BLOCK: POLYAMIDE 66, UL94V-0, BLACK.
TERMINAL: BRASS, TIN PLATED.
SCREW: M3 STEEL, NICKEL PLATED W/ WIRE CLAMP.



ELECTRICAL:
CURRENT RATING: 10A, 300V
INSULATION WITHSTANDS: 2000V, MIN
INSULATION RESISTANCE: >2000MEGA OHM, 500V

MECHANICAL:
WIRE RANGE: 16-30AWG
RECOMMENDED TORQUE: 10 IN-LB
OPERATION TEMP: -40°C TO 105°C

UL RECOGNIZED PER US & CANADIAN STANDARDS.

1

 PRELIMINARY NUMBER



RECOMMENDED PCB LAYOUT

1	.12	.54	.250	2	3-1546657-1
	.17	7.54	7.250	30	3-1546657-0
	.17	7.29	7.000	29	2-1546657-9
	.17	7.04	6.750	28	2-1546657-8
	.17	6.79	6.500	27	2-1546657-7
	.17	6.54	6.250	26	2-1546657-6
	.17	6.29	6.000	25	2-1546657-5
	.17	6.04	5.750	24	2-1546657-4
	.17	5.79	5.500	23	2-1546657-3
	.17	5.54	5.250	22	2-1546657-2
	.17	5.29	5.000	21	2-1546657-1
	.17	5.04	4.750	20	2-1546657-0
	.17	4.79	4.500	19	1-1546657-9
	.17	4.54	4.250	18	1-1546657-8
	.17	4.29	4.000	17	1-1546657-7
	.17	4.04	3.750	16	1-1546657-6
	.17	3.79	3.500	15	1-1546657-5
	.17	3.54	3.250	14	1-1546657-4
	.17	3.29	3.000	13	1-1546657-3
	.17	3.04	2.750	12	1-1546657-2
	.17	2.79	2.500	11	1-1546657-1
	.17	2.54	2.250	10	1-1546657-0
	.17	2.29	2.000	9	1546657-9
	.17	2.04	1.750	8	1546657-8
	.17	1.79	1.500	7	1546657-7
	.17	1.54	1.250	6	1546657-6
	.17	1.29	1.000	5	1546657-5
	.17	1.04	.750	4	1546657-4
	.17	.79	.500	3	1546657-3
	.17	.54	.250	2	1546657-2
DIM C	DIM B	DIM A	# POS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL

-

DWN S SCHLEGEL 30MAY03
CHK S YODER 5/30/03
APVD S YODER 5/30/03
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV B2

TE Connectivity

NAME
TERMINAL BLOCK, .250 PITCH, DUAL BARRIER
PCV STYLE -

SIZE A3
CAGE CODE 00779
DRAWING NO C-1546657
RESTRICTED TO -