SURFACE MOUNT .025" SQ POST HEADER



(2.54 mm) .100" PITCH • TSM SERIES

TSM
Board Mates:
SSW, SSQ, SSM, BSW, ESW, ESQ, BCS, SLW, CES, HLE
Cable Mates:
IDSS, IDSD

TSM	–	1	NO. PINS PER ROW	–	LEAD STYLE	–
			02 thru 36		Specify LEAD STYLE from chart	

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Au or Sn over
50 µ" (1.27 µm) Ni
Operating Temp Range:
-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold
Voltage Rating:
495 VAC/700 VDC -SV/-DV mated with the BCS
405 VAC/573 VDC -SV/-DV mated with the SSM
400 VAC/566 VDC mated with HLE

PROCESSING

Lead–Free Solderable:
Yes
-DH/-SH/-SV Lead Coplanarity:
(0.15 mm) .006" max (02-36)*
-DV Lead Coplanarity:
(0.10 mm) .004" max (02-05)
(0.13 mm) .005" max (06-10)*
(0.15 mm) .006" max (11-36)*
*(.004" stencil solution may be available; contact ipg@samtec.com)

MATES	CURRENT RATING (PER PIN)
TSM/SSW	4.7 A
TSM/SSM	5.6 A
TSM/HLE	4.1 A
TSM/BCS	5.0 A

2 POSITIONS POWERED



–SV Row Option

LEAD STYLE	POST HEIGHT	MATES WITH
–01	(5.84) .230	SSW, BCS, SSM, IDSS, IDSD
–02	(8.13) .320	SSM-DH
–03	(10.67) .420	Bottom Mount & Pass-Through
–04	(3.05) .120	SLW, CES, HLE



–SH Row Option



–DV Row Option

Notes:
Severe Environment Testing qualified; aligns with MIL-DTL-55302. Visit samtec.com/set

Some sizes, styles and options are non-standard, non-returnable.

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.



PLATING OPTION

–F
= Gold flash on post, Matte Tin on tail

–L
= 10 µ" (0.25 µm) Gold on post, Matte Tin on tail

–T
= Matte Tin

ROW OPTION

–SV
= Single Row Vertical Pin

–DV
= Double Row Vertical Pin

–SH
= Single Row Horizontal Pin

–DH
= Double Row Horizontal Pin

–TM
= Triple Row Vertical Mixed Technology
(Style –01 only)
(02 thru 30 positions only)

–MT
= Mixed Technology Pin
(Style –01, –02 or –03 only)

OTHER OPTIONS

–"XXX"
= Polarized Position

–A
= Alignment Pin
metal or plastic at Samtec discretion
(Not available with –TM or –MT)
(02 positions minimum)
(Not available with –LC)

–LC
= Locking Clip
(Not available with –TM)
(3 positions minimum)
(Not available with –A)
(Manual placement required)

–K
= (6.50 mm) .256" DIA
Polyimide Film Pick & Place Pad
(–SH: 4 positions minimum without –TR;
2 & 3 positions available with –TR)
(–DH: 4 positions minimum without –TR)

–P
= Plastic Pick & Place Pad
(–DV: 4 positions minimum without –TR;
2 & 3 positions available with –TR)
(–SH: 4 positions minimum without –TR;
2 & 3 positions available with –TR)
(–DH: 5 positions minimum without –TR)
(–SV: 4 positions minimum without –TR;
2 & 3 positions available with –TR)

–TR
= Tape & Reel
–SV: 02-22 positions, –DV: 02-28 positions,
–SH: 02-30 positions, –DH: 02-29 positions
(Not available with –MT or –TM)

–FR
= Full Reel Tape & Reel
(must order maximum quantity per reel;
contact Samtec for quantity breaks)
–SV: 02-22 positions, –DV: 02-28 positions,
–SH: 02-30 positions, –DH: 02-29 positions
(Not available with –MT or –TM)



–DH Row Option



–MT Row Option



–TM Row Option

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.