



CN-AA35-008

The drawing shows a mechanical part with the following dimensions and features:

- Top View (Cross-section):** A circular feature with a central hole of diameter $\varnothing 3.3 \pm 0.05$.
- Side View:**
 - Overall length: 38.8 ± 0.2
 - Left end radius: 6.5 ± 0.1
 - Outer diameter of the main body: $\varnothing 10 \pm 0.1$
 - Length of the main body: 16.5 ± 0.1
 - Length of the internal thread section: 14.3 ± 0.3
 - Length of the internal thread section (alternative measurement): 7.5 ± 0.1
 - Outer diameter of the internal thread section: $\varnothing 3.5 \pm 0.05$
 - Length of the internal thread section (alternative measurement): 5
 - Right end radius: 3 ± 0.05
 - Feature A: A specific section of the main body.
 - Feature B: A specific section of the internal thread.

○	Approved	
	Check	



CN-AA35-008

The drawing shows a mechanical part with the following dimensions and features:

- Top View (Cross-section):** A circular feature with a central hole of diameter $\phi 3.3 \pm 0.05$.
- Side View:**
 - Overall length: 38.8 ± 0.2
 - Left end radius: 6.5 ± 0.1
 - Outer diameter of the main body: $\phi 10 \pm 0.1$
 - Length of the main body: 16.5 ± 0.1
 - Length of the internal thread section: 14.3 ± 0.3
 - Length of the internal thread section (alternative measurement): 7.5 ± 0.1
 - Outer diameter of the internal thread section: $\phi 3.5 \pm 0.05$
 - Length of the internal thread section (alternative measurement): 5
 - Right end radius: 3 ± 0.05
 - Feature A: A small hole or feature on the main body.
 - Feature B: A small hole or feature on the internal thread section.

○	Approved	
	Check	