



Micro Commercial Components
21201 Itasca Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

2SC5200

Features


- Silicon NPN triple diffused type
- Complementary to 2SA1943
- Recommend for 100W fidelity audio frequency amplifier output stage

Maximum Ratings

Symbol	Rating	Rating	Unit
V_{CEO}	Collector-Emitter Voltage	230	V
V_{CBO}	Collector-Base Voltage	230	V
V_{EBO}	Emitter-Base Voltage	5.0	V
I_C	Collector Current	15	A
P_C	Collector power dissipation	150	W
T_J	Junction Temperature	-55 to +150	°C
T_{STG}	Storage Temperature	-55 to +150	°C

NPN Silicon Power Transistors

TO-3PL



Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
--------	-----------	-----	-----	-------

OFF CHARACTERISTICS

$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage ($I_C=50\text{mA}$, $I_B=0$)	230	---	Vdc
I_{CBO}	Collector-Base Cutoff Current ($V_{CB}=230\text{Vdc}$, $I_E=0$)	---	5.0	μAdc
I_{EBO}	Emitter-Base Cutoff Current ($V_{EB}=5.0\text{Vdc}$, $I_C=0$)	---	5.0	μAdc

ON CHARACTERISTICS

h_{FE-1}	Forward Current Transfer ratio ($I_C=1.0\text{Adc}$, $V_{CE}=5.0\text{Vdc}$)	55	160	---
h_{FE-2}	Forward Current Transfer ratio ($I_C=7.0\text{Adc}$, $V_{CE}=5.0\text{Vdc}$)	35	---	---
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ($I_C=8.0\text{Adc}$, $I_B=0.8\text{Adc}$)	---	3.0	Vdc
$V_{BE(sat)}$	Base-Emitter Saturation Voltage ($I_C=7.0\text{Adc}$, $V_{CE}=5.0\text{Vdc}$)	---	1.5	Vdc

DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	---	.007	---	20.50	
B	.098		2.50		
C	.098		2.50		
D	.118		3.00		
E	.039	.051	.75	1.30	
F	.209	.220	5.30	5.60	
G	.020	.033	.50	.85	
H	.209	.220	5.30	5.60	
I	.126	.142	3.20	3.60	Ø
J	.157		4.00		
K	.079		2.00		
L	.236		6.00		
M	.433		11.00		
N	.110		2.80		
O	1.004	1.043	25.50	26.50	
P	.764	.811	19.40	20.60	
Q	---	.205	---	5.20	