




PRODUCT NO.	NOTE
72325-001	5.0V
72325-001LF	5.0V
72325-101	3.3V
72325-101LF	3.3V



NOTES:




- 1 **HEADER ASSY**
 PLASTIC: HOUSING — HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK — ABOVE PCB
 PIN: PHOSPHOR BRONZE
GUIDE MECHANISM ASSY
 PLASTIC: GUIDE — HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
 COVER PLATE: STAINLESS STEEL
 EMI CONTACT: PHOSPHOR BRONZE
- 2 **FINISH — PIN**
 UNDER PLATING: 0.5um Ni
 CONTACT AREA: 0.076 μ m MIN. GOLD
 SOLDER TAIL(TIN LEAD OPTION): 2.5um Sn-Pb
 SOLDER TAIL(LEAD FREE OPTION): 2.5um PURE TIN
- ③ DIM "L"

4.25 $\pm$ 1	3.5 $\pm$ 1	5.0 $\pm$ 1
OTHERS	36,67	1,17,34,35,51,68
- 4 **RECOMMENDED HOLD DOWN — 2mm SCREWS**
 95121 AND 2mm NUTS 92869.
 SEE FOR CHARTED INFORMATION.
 RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).
- 5 SEE TA-1052 FOR PCB LAYOUT.
- 6 MATING CONNECTOR: 91931-31169. MUST BE PURCHASED SEPARATELY.
- 7 IF LEAD FREE P.N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- 8 IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 9 LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- 10 PRODUCT SPEC:110-263

mat'l. code				surface	tolerance	projection	product family
ISO1302				ISO1101	ISO406		MCS
l t r e c n n o d r				date		tolerances unless otherwise specified	title
F	V05-0302	WB	04/21/05	0.X $\pm$ 0.3		MM	EJECTOR HEADER ASSEMBLY
G	N05-0116	WB	04/27/05	0.XX $\pm$ 0.13		scale 1:1	68 POS. SMT TYPE 123
H	EX-N-011412	ZK	04/02/12	0.XXX $\pm$ 0.051			
				dr	R.GRAPE	8/16/96	dwg no
				engr	D.BRANN	8/16/96	sheet 1 of 5
				chr	D.BRANN	8/16/96	size
				appd	D.BRANN	8/16/96	A4
sheet				revision		type	
index	sheet	1	2	3	4	5	Product Customer Drawing





PRODUCT NO.	NOTE
72325-002	5.0V
72325-002LF	5.0V
72325-102	3.3V
72325-102LF	3.3V



mat'l. code		surface	tolerance	projection	product family
ISO1302		ISO1101	ISO406		MCS
tolerances unless otherwise specified		tolerances unless otherwise specified		tolerances unless otherwise specified	
H		angle	0.X±0.3	MM	EJECTOR HEADER ASSEMBLY
		0°±2'	0.XX±0.13	scale 1:1	68 POS. SMT TYPE 123
		dr	R.GRAPE	8/16/96	dwg no
		enr	D.BRANN	8/16/96	sheet 2 of 5
		chr	D.BRANN	8/16/96	size
		app	D.BRANN	8/16/96	A4
sheet index		revision			type Product Customer Drawing
sheet		sheet			


Printed: Sep 12, 2013

PRODUCT NO.	NOTE
72325-004	5.0V
72325-004LF	5.0V
72325-104	3.3V
72325-104LF	3.3V





NOTE:

TA-1052, PAGE 3, FOR PCB LAYOUT.




mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family MCS
ltr ecn nodr date	tolerances unless otherwise specified	angle 0°±2'	scale 1:1	EJECTOR HEADER ASSEMBLY 68 POS. SMT TYPE 123
H	0.X±0.3	0.XX±0.13	0.XXX±0.051	dwg no 72325
	dr R.GRAPE 8/16/96	engr D.BRANN 8/16/96	chr D.BRANN 8/16/96	appd D.BRANN 8/16/96
sheet index	revision sheet			type Product Customer Drawing

PRODUCT NO.	NOTE
72325-005	5.0V
72325-005LF	5.0V
72325-105	3.3V
72325-105LF	3.3V



NOTE:

TA-1052, PAGE 3, FOR PCB LAYOUT.



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family MCS
ltr ecn nodr date	tolerances unless otherwise specified	angle 0°±2'	scale 1:1	title EJECTOR HEADER ASSEMBLY 68 POS. SMT TYPE 123
H	0.X±0.3	dr R.GRAPE 8/16/96	FCI	dwg no 72325
	0.XX±0.13	engr D.BRANN 8/16/96		sheet 5 of 5
	0.XXX±0.051	chr D.BRANN 8/16/96		size A4
		appd D.BRANN 8/16/96		type Product Customer Drawing
sheet index	revision sheet			