




THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
GP	00	P	LTR	DESCRIPTION	DATE
		L		REVISED PER ECO-08-007327	13OCT08



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
- 3 MATERIAL:
HOUSING - THERMOPLASTIC (BLACK)
TERMINALS: - HIGH STRENGTH COPPER ALLOY PLATED WITH .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, .000030 MIN TOTAL ON MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. WIRE SIZE: 24 & 26 AWG SOLID & 24 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
- 5 CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH

3

DWN
B. MCMASTER

CHK
W. MILLHIMES

APVD
W. MILLHIMES

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

05OCT05

05OCT05

05OCT05

NAME

ASSY, RCPT, 14 POSN, B SLOT
CHAMP-LOK, W/ .187 DIA HOLES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

A2 00779

C=552271

SCALE
NTS

SHEET
1 of 1

REV
L

2-552271-1

PART
NUMBER