

# **Power PCB Relay RT1**

- 1 pole 12A/16A, 1 form C (CO) or 1 form A (NO) contact
- Sensitive coil 400mW
- 5kV/10mm coil-contact, reinforced insulation
- Ambient temperature 85°C





Typical applications

Boiler control, timers, garage door control, POS automation, interface modules

## Approvals


VDE REG.-Nr. 6106, UL E214025, cCSAus 14385


Technical data of approved types on request

Contact Data	12A	16A
Contact arrangement	1 form C (CO)	or 1 form A (NO)
Rated voltage	250VAC	
Max. switching voltage	400VAC	
Rated current	12A	16A
Limiting continuous current	12A	16A, UL: 20A
Limiting making current		
max. 4s, duty factor 10%	25A	30A
Breaking capacity max.	3000VA	4000VA
Contact Material AgNi 90/10		
Frequency of operation, with/without I	oad 360/7	72000h <sup>-1</sup>
Operate/release time max., DC coil	8/	/6ms
Bounce time max., DC coil, form A/for	rm B 4/	/6ms

**Contact ratings** 

oontaot rating	-		
Type	Contact	Load	Cycles
IEC 61810			
RT314 DC-coil	A (NO)	16A, 250VAC, cosφ=1, 85°C	30x10 <sup>3</sup>
RT314 DC-coil	C (CO)	16A, 250VAC, cosφ=1, 85°C	10x10 <sup>3</sup>
RT314 DC-coil	A (NO)	10A, 400VAC, cosφ=1, 85°C	150x10 <sup>3</sup>
RT114 DC-coil	A (NO)	12A, 250VAC, cosφ=1, 85°C	50x10 <sup>3</sup>
RT114 AC-coil	A (NO)	12A, 250VAC, cosφ=1, 70°C	100x10 <sup>3</sup>
UL 508			
RT314	A/B (NO/NC)	20A, 250VAC, general purpose, 85°	C 6x10 <sup>3</sup>
RT334	A (NO)	16A, 250VAC, gen. purpose, 85°C	50x10 <sup>3</sup>
RT314	A (NO)	1hp, 240VAC, 40°C	1x10 <sup>3</sup>
EN60947-5-1			
RT314 DC-coil	A/B (NO/NC)	2A, 24VDC, DC13	6.050
EN60730-1			
RT314 DC-coil	A (NO)	12(2)A, 250VAC, 85°C	100x10 <sup>3</sup>





# Contact Data (continued)

Contact ratings				
Type	Load	Cycles		
RT3, RTD	1 HP @ 480VAC* motor	6x10 <sup>3</sup>		
RT3, RTD	1 HP @ 240VAC* motor	6x10 <sup>3</sup>		
RT3, RTD	1/2 HP @ 120VAC* motor	6x10 <sup>3</sup>		
RT3, RTD	60 LRA/10 FLA @ 250VAC* motor	30x10 <sup>3</sup>		
RT3, RTD	TV-5 @ 120VAC* Tungsten	25x10 <sup>3</sup>		
RT3, RTD	A300, 720VA @ 240VAC* Pilot Duty	30x10 <sup>3</sup>		
RT3, RTD	B300, 360VA @ 240VAC** Pilot Duty	30x10 <sup>3</sup>		
*) form A (NO) c	ontact only, **) form B (NC) contact only			


Mechanical endurance >30x10<sup>6</sup> operations

Coil Data		
Coil voltage range	5 to 110VDC	
Operative range, IEC 61810	2	
Coil insulation system according UL	class F	

Coil versions, DC coil

Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
005	5	3.5	0.5	62	403
006	6	4.2	0.6	90	400
009	9	6.3	0.9	200	400
012	12	8.4	1.2	360	400
024	24	16.8	2.4	1440	400
048	48	33.6	4.8	5520	417

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.





## Power PCB Relay RT1 (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	$1000V_{rms}$
between contact and coil	5000V <sub>rms</sub>
Clearance/creepage	
between contact and coil	≥10/10mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI 250V

Other Data (contiinued)	
Terminal type	PCB-THT, plug-in
Weight	14g
Resistance to soldering heat	THT, IEC 60068-2-20
RTII	270°C/10s
RTIII	260°C/5s
Packaging/unit	tube/20 pcs., box/500 pcs.

### **Other Data**

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature -40 to 85°C

Category of environmental protection

IEC 61810 RTII - flux proof, RTIII - wash tight

Vibration resistance (functional)


form A/form B contact, 30 to 500Hz 20g/5g Shock resistance (destructive) 100g

### **Accessories**

For details see datasheet <u>Accessories Industrial Power Relay RT</u>

NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.


#### **Dimensions**



### PCB layout / terminal assignment


Bottom view on solder pins

\*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.




22,65±0,2

S0163-BG



22,65±0.2 22,65±0.2



1 form C (CO) contact


1 form A (NO) contact

A1


A2

S0163-BH

1 form C (CO) contact



1 form C (CO) contact



S0163-BF

S0163-BE

S0163-BC

S0163-BD



## Power PCB Relay RT1 (Continued)



Product code	Version	Contacts	Contact material	Coil	Part number
RT114012F	12A, pinning 3.5mm,	1 form C (CO)	AgNi 90/10	12VDC	1419108-2
RT114024F	flux proof	contact		24VDC	1419108-3
RT134012F		1 form A (NO)		12VDC	5-1415020-1
RT134024F		contact		24VDC	2-1393242-1
RT314005F	16A, pinning 5mm,	1 form C (CO)		5VDC	1419108-8
RT314012F	flux proof	contact		12VDC	2-1393237-2
RT314024F	·			24VDC	2-1393237-3
RT334012F		1 form A (NO)		12VDC	2-1393237-5
RT334024F		contact		24VDC	2-1393237-7
RTB14005F	12A, pinning 3.5mm,	1 form C (CO)		5VDC	2-1419108-4
RTB14012F	wash tight	contact		12VDC	2-1419108-5
RTB14024F				24VDC	2-1419108-6
RTB34012F		1 form A (NO)		12VDC	2-1419108-7
RTD14005F	16A, pinning 3.5mm,	1 form C (CO)		5VDC	2-1419108-8
RTD14012F	wash tight	contact		12VDC	2-1419108-9
RTD14024F				24VDC	3-1419108-1
RTD34012F		1 form A (NO)		12VDC	3-1419108-6
RTD34024F		contact		24VDC	3-1419108-9

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request

the 'Definitions' section, available at

http://relays.te.com/definitions