



**RELAYS, CONTACTORS & SWITCHES**

**TIME DELAY RELAYS**



✓ Active

**TE CONNECTIVITY (TE)**

**ETR14D3A004=RLY,NUC,ON,4P,125**

Agastat | ETR - Nuclear Qualified

**ETR14D3A004**

TE Internal Number: 1423177-3

**Not EU RoHS Compliant**

**Not EU ELV Compliant**

**Type of Control** Potentiometer Adjustable

**Input Voltage (VDC)** 125

**Timing Range (Off-Time) (seconds)** .15 – 3

**Mode of Operation** Delay on Energization

**Delay Time** .15 – 3 seconds

**DOCUMENTATION**

Catalog Pages/Data Sheets

**5-1773450-5\_sec12\_EGP\_EML\_ETR**

PDF

English

**FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

**Product Category** Electromechanical Relays

**Relay Type** Time Delay

**Product Type** Relay

## Configuration Features

**Multiple Timing Ranges** Without

---

## Electrical Characteristics

**Input Voltage (VDC)** 125

**Timing Range (Off-Time) (seconds)** .15 – 3

**Actuating System** DC

---

## Contact Features

**Type of Control** Potentiometer Adjustable

**Delay Time** .15 – 3 seconds

**Contact Arrangement** 4 Form C, 4PDT, 4 C/O

---

## Termination Features

**Termination Type** 16 Flat Base Pins

---

## Mechanical Attachment

**Mounting Type** Socket

---

## Usage Conditions

**Operating Temperature Range (°C)** 21 – 40

---

## Operation/Application

**Mode of Operation** Delay on Energization

---

## Other

**Repeatability (Max)** ±5%

---

## PRODUCT COMPLIANCE



### Statement of Compliance

#### **Statement of Compliance**

PDF

---