





PRODUCT NO.	DIM.M
61125-005CA/005CALF	10.0
61125-025CA/025CALF	6.55
61125-045CA/045CALF	6.55
61125-055CA/055CALF	6.55
61125-025CAC/025CACLf	6.55
61125-045CAC/045CACLf	6.55
61125-055CAC/055CACLf	6.55



ABOVE P.C.B.
RIGHT PUSH ROD
(CAN'T BE USED FOR SINGLE DECK)



PRODUCT NO.	DIM.M
61125-020CA/020CALF	-0.3
61125-220CA/220CALF	2.15
61125-040CA/040CALF	-0.3
61125-050CA/050CALF	-0.3
61125-050CAN/050CANLF	-0.3
61125-020CAC/020CACLf	-0.3
61125-040CAC/040CACLf	-0.3
61125-050CAC/050CACLf	-0.3





ABOVE P.C.B.
RIGHT PUSH ROD
(CAN BE USED FOR SINGLE DECK)

mat'l. code				surface		tolerance		projection		product family				
				ISO1302 ✓		ISO1101 ISO406				PCMCIA				
ltr	ecn	nodr	date	tolerances unless otherwise specified				title						
J	N05-0063	WB	03/04/05	angle	linear				MM	EJECTOR HEADER ASS'Y 3.3V, SMT TYPE 1/2/3				
K	N05-0140	WB	05/31/05			±0.30								
L	EX-N-011397	ZK	04/02/12			0°±2'								
								scale 1.2						
				dr	WENDY CHEN		07/11/95			dwg no		sheet 1 of 6		size
				engr	JOSEPH HSIA		07/11/95			61125		A4		
				chr	JOSEPH HSIA		07/11/95							
				appd	JENN TSAO		07/11/95							
sheet		revision		L	L	L	L	L		type Product Customer Drawing				
index		sheet		1	2	3	4	5	6					

PRODUCT NO.	DIM.M
61125-105CA/105CALF	10.0
61125-125CA/125CALF	6.55
61125-145CA/145CALF	6.55
61125-155CA/155CALF	6.55





PRODUCT NO.	DIM.M
61125-120CA/120CALF	-0.3
61125-140CA/140CALF	-0.3
61125-150CA/150CALF	-0.3






mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family PCMCIA
ltr ecn nodr	date	tolerances unless otherwise specified	scale 1.2	EJECTOR HEADER ASS'Y 3.3V, SMT TYPE 1/2/3
L		angle 0°±2'	MM	dwg no
		±0.30	scale 1.2	sheet 2 of 6
	dr	WENDY CHEN 07/11/95	FCI	size A4
	engr	JOSEPH HSIA 07/11/95		61125
	chr	JOSEPH HSIA 07/11/95		type
	appd	JENN TSAO 07/11/95		Product Customer Drawing
sheet index	revision sheet			

PRODUCT NO.	DIM.M
61125-605CA/650CALF	10.0
61125-625CA/625CALF	6.55
61125-645CA/645CALF	6.55
61125-655CA/655CALF	6.55





PRODUCT NO.	DIM.M
61125-620CA/620CALF	-0.3
61125-640CA/640CALF	-0.3
61125-650CA/650CALF	-0.3





BELOW P.C.B.
LEFT PUSH ROD
(CAN BE USED FOR SINGLE DECK)

mat'l. code	surface	tolerance	projection	product family
ISO1302	ISO1101	ISO406	MM	PCMCIA
l t r e c n n o d r	date	tolerances unless otherwise specified	title	
L		angle	scale 1.2	EJECTOR HEADER ASS'Y
		0°±2'		3.3V, SMT TYPE 1/2/3
	dr	WENDY CHEN	07/11/95	dwg no
	eng	JOSEPH HSIA	07/11/95	sheet 3 of 6
	chr	JOSEPH HSIA	07/11/95	size
	app	JENN TSAO	07/11/95	A4
sheet	revision			type
index	sheet			Product Customer Drawing

PRODUCT NO.	DIM.M
61125-505CA/505CALF	10.0
61125-525CA/525CALF	6.55
61125-545CA/545CALF	6.55
61125-555CA/555CALF	6.55



PRODUCT NO.	DIM.M	DIM.S
61125-520CA/520CALF	-0.3	13.0
61125-540CA/540CALF	-0.3	13.0
61125-550CA/550CALF	-0.3	15.6
61125-520DA/520DALF	-0.3	21.0
61125-520FA/520FALF	-0.3	21.0



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection ASME Y14.5	product family PCMCIA
ltr ecn nodr date	tolerances unless otherwise specified			title EJECTOR HEADER ASS'Y 3.3V, SMT TYPE 1/2/3
L	angle 0°±2'	±0.30	MM	scale 1.2
dr	WENDY CHEN	07/11/95	FCI	dwg no
eng	JOSEPH HSIA	07/11/95		sheet 4 of 6
chr	JOSEPH HSIA	07/11/95		size A4
app	JENN TSAO	07/11/95	type Product Customer Drawing	
sheet index	revision sheet			

NOTES:

- 8mm MIN. CARD EJECT.
- EJECT TRAVEL: 9.5mm
- PUSH ROD LOCATION AND P.C.B. SIDE ARE AS APPEARS INSTALLED.

4. MATERIAL

4.1 HEADER ASS'Y:

PLASTIC : HOUSING ...HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : PHOSPHOR BRONZE
PCB : FR4

4.2 EJECT MECHANISM ASS'Y:

PLASTIC : GUIDE: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
: BUTTON: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PLATE AND PUSH ROD : STAINLESS
EMI CONTACT: PHOSPHOR BRONZE

5. FINISH (PIN)

UNDER PLATING : 0.5μm MIN. Ni
CONTACT AREA : 0.076 μm MIN. GOLD

SOLDER TAIL (FOR TIN LEAD OPTION) : 2.5μm MIN. Sn-Pb
SOLDER TAIL (FOR LEAD FREE OPTION) : 2.5μm MIN. PURE TIN

6. DIM "X"

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,68

7. FOR P/N: 61125-050CAN AND 61125-050CANLF:

- TIGHTENING TORQUE OF SCREW: 1.5 ~ 2.0 Kgf-cm
- LUBRICANT SHOULD BE SPREAD TO MATING AREA OF PINS.

- IF LEAD FREE P.N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- IF LEAD FREE P/N. THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- PART NUMBER 61125-***CAC, -***CACLIF IS FOR CISCO
- PRODUCT SPEC: 110-263

ORDERING INFORMATION

NAME	PART NO.		Q'TY
Ⓐ EJECT HEADER ASS'Y	61125-*****	61125-*****LF	1
Ⓑ MATING RECEPTACLE	91931-31169	91931-31169LF	1

mat'l. code	surface	tolerance	projection	product family
ISO1302	ISO1101 ISO406			PCMCIA
l t r e c n n o d r	date	tolerances unless otherwise specified	title	
L		angle	MM	EJECTOR HEADER ASS'Y
		0°±2'	scale 1.2	3.3V, SMT TYPE 1/2/3
	dr WENDY CHEN	07/11/95	FCI	dwg no
	eng JOSEPH HSIA	07/11/95		sheet 5 of 6
	chr JOSEPH HSIA	07/11/95		size A4
	appd JENN TSAO	07/11/95		type Product Customer Drawing
sheet	revision			
index	sheet			


DESCRIPTION : ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEW BY USER.

LOWER DECK					Ⓑ MATING RECEPTACLE	MOUNT STYLE TO PCB AND PUSH ROD SIDE
Ⓐ PRODUCT NO.	STAND-OFF HIGH DIM. L	PUSH ROD LOCATION ⓐ	P.C.B. SIDE ⓐ	P.C.B LAYOUT RECOMMENDED		
61125-020CA/020CALF	2.2	RIGHT	ABOVE	P/N: TA-1056	↑ RECEPTACLE PART NUMBER: 91931-31169 91931-31169LF ↓	
61125-220CA/220CALF	2.2	RIGHT	ABOVE	SEE PAGE 6		
61125-040CA/040CALF	4.3	RIGHT	ABOVE	SEE DRAWING P/N: TA-1056		
61125-050CA/050CALF	5.0					
61125-050CAN/050CANLF	5.0					
61125-020CAC/020CACL	2.2					
61125-040CAC/040CACL	4.3					
61125-050CAC/050CACL	5.0					
61125-120CA/120CALF	2.2	LEFT	ABOVE	SEE DRAWING P/N: TA-1056		
61125-140CA/140CALF	4.3					
61125-150CA/150CALF	5.0					
61125-520CA/520CALF	2.2	RIGHT	BELOW	SEE DRAWING P/N: TA-1056		
61125-520FA/520FALF	2.2					
61125-520DA/520DALF	2.2					
61125-540CA/540CALF	4.3					
61125-550CA/550CALF	5.0					
61125-620CA/620CALF	2.2					
61125-640CA/640CALF	4.3	LEFT	BELOW	SEE DRAWING P/N: TA-1056		
61125-650CA/650CALF	5.0					
						
						

UPPER DECK					
Ⓐ PRODUCT NO.	JOINT WITH LOWER DECK STAND-OFF HIGH(DIM. L)	PUSH ROD LOCATION ③	P.C.B. SIDE ③	Ⓑ MATING RECEPTACLE	MOUNT STYLE TO PCB AND PUSH ROD SIDE
61125-005CA/005CALF	0.0	RIGHT	ABOVE		
61125-025CA/025CALF	2.2				
61125-045CA/045CALF	4.3				
61125-055CA/055CALF	5.0				
61125-025CAC/025CACLIF	2.2				
61125-045CAC/045CACLIF	4.3				
61125-055CAC/055CACLIF	5.0	LEFT		RECEPTACLE PART NUMBER: 91931-31169 91931-31169LF	
61125-105CA/105CALF	0.0				
61125-125CA/125CALF	2.2				
61125-145CA/145CALF	4.3				
61125-155CA/155CALF	5.0				
61125-505CA/505CALF	0.0				
61125-525CA/525CALF	2.2	RIGHT	BELOW		
61125-545CA/545CALF	4.3				
61125-555CA/555CALF	5.0				
61125-605CA/605CALF	0.0				
61125-625CA/625CALF	2.2	LEFT			
61125-645CA/645CALF	4.3				
61125-655CA/655CALF	5.0				

NOTES:

- IT CAN'T BE USED FOR SINGLE DECK.
- IT MUST BE ASSEMBLED BY USER FOR DOUBLE DECK APPLICATION.(PLEASE REFER TO P/N 61124)



mat'l. code		surface	tolerance	projection	product family
ISO1302		ISO1101	ISO406	MM	PCMCIA
l	tr	ec	n	o	d
date		tolerances unless otherwise specified		title	
angle		±0.30		EJECTOR HEADER ASS'Y	
0°±2'		scale 1.2		3.3V, SMT TYPE 1/2/3	
dr	WENDY CHEN	07/11/95		dwg no	sheet 6 of 6
eng	JOSEPH HSIA	07/11/95		61125	A4
chr	JOSEPH HSIA	07/11/95		type Product Customer Drawing	
app	JENN TSAO	07/11/95			
sheet	revision				
index	sheet				