

**9533 Non-Paired - EIA RS-232**



For more information please  
call

**1-800-Belden1**

See Put-ups and Colors

**Color Code Chart : No. 1.pdf**

**Description:**

24 AWG stranded conductors (7x32), tinned copper, conductors cabled, 24 AWG stranded tinned copper drain wire, S-R PVC insulated, Beldfoil® aluminum-polyester shield (100% shield coverage), PVC jacket.

**PHYSICAL CHARACTERISTICS:**

**CONDUCTOR:**

Number of Conductors	3
Total Number of Conductors	3
AWG	24
Stranding	7x32
Conductor Material	TC - Tinned Copper

**INSULATION:**

Insulation Material	PVC - Polyvinyl Chloride
Nom. Insulation Wall Thickness	.010 in.

**OVERALL CABLING:**

Overall Cabling Lay Length	1.50 in.
----------------------------	----------

Overall Cabling Color Code Chart :

Number	Color
1	Black
2	White
3	Red

**OUTER SHIELD:**

Outer Shield Trade Name	Beldfoil®
Outer Shield Material	Aluminum Foil-Polyester Tape
Outer Shield % Coverage	100 %

**OUTER SHIELD DRAIN WIRE :**

Outer Shield Drain Wire AWG	24
Outer Shield Drain Wire Stranding	7x32
Outer Shield Drain Wire Conductor Material	TC - Tinned Copper

**OUTER JACKET:**

**9533 Non-Paired - EIA RS-232**

Outer Jacket Material Trade Name	Beldfoil®
Outer Jacket Material	PVC - Polyvinyl Chloride
Outer Jacket Nominal Wall Thickness	.032 in.

**OVERALL NOMINAL DIAMETER:**

Overall Nominal Diameter	.162 in.
--------------------------	----------

**MECHANICAL CHARACTERISTICS:**

Operating Temperature Range	-30°C To +80°C
Bulk Cable Weight	16 lbs/1000 ft.
Max. Recommended Pulling Tension	16.5 lbs.
Min. Bend Radius (Install)	1.75 in.

**APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:**

**APPLICABLE STANDARDS:**

NEC/(UL) Specification	CMG
CEC/C(UL) Specification	CMG
AWM Specification	2464

**FLAME TEST:**

C(UL) Flame Test	FT4
------------------	-----

**PLENUM/NON-PLENUM:**

Plenum (Y/N)	N
--------------	---

**ELECTRICAL CHARACTERISTICS:**

Nom. Capacitance Conductor to Conductor @ 1 KHz	33 pF/ft
Nom. Cap. Cond. to Other Cond. & Shield @ 1 KHz	65 pF/ft
Nom. Conductor DC Resistance @ 20 Deg. C	25 Ohms/1000 ft
Nominal Outer Shield DC Resistance @ 20 Deg. C	18 Ohms/1000 ft
Max. Operating Voltage - UL	300 V RMS
Other Maximum Continuous Currents	1.75 Amps Per Conductor @ 25°C

**PUT-UPS AND COLORS:**

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
9533 060100	3 #24 PVC FS PVC	100	2.7	CHROME	
9533 0601000	3 #24 PVC FS PVC	1000	18	CHROME	
9533 060500	3 #24 PVC FS PVC	500	9	CHROME	
9533 060U1000	3 #24 PVC FS PVC	U1000	17	CHROME	
9533 060U500	3 #24 PVC FS PVC	U500	9	CHROME	

---

**9533 Non-Paired - EIA RS-232**

---

© 2003 Belden Wire & Cable Company  
All Rights Reserved.

Although Belden Electronics Division ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.