





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		D	REVISED PER ECO-08-008919	16APR08	HMR	DB
			D1	REVISED PER ECO-09-021510	15SEP09	KK	AEC

- 1 MATERIAL: CONNECTOR- NYLON UL94V-2 (WHITE).
CONTACTS- 0.30 [.012] THK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203 [.000080] MIN THK).
(MATTE TIN 0.00203 [.000080] MIN THK).
- 2 CONTACTS ACCEPT #24 AWG SOLID, FUSED STRANDED OR
STRANDED (7 STRANDS) WIRE WITH 2.41 [.095] MAX INSULATION DIA.
- 3 BOW, IN ANY DIRECTION, NOT TO EXCEED 0.15 [.006] PER IN.
- 4 HOUSING FEATURES: FEED-THRU.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- ⚠️ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION A-A

⚠️ OBSOLETE	TIN	91.14 [3.588]	95.20 [3.748]	99.06 [3.900]	24	5-641525-4
⚠️ OBSOLETE		55.47 [2.184]	59.54 [2.344]	63.40 [2.496]	15	4-641525-5
⚠️ OBSOLETE		43.59 [1.716]	47.65 [1.876]	51.51 [2.028]	12	4-641525-2
⚠️ OBSOLETE		31.70 [1.248]	35.76 [1.408]	39.62 [1.560]	9	3-641525-9
⚠️ OBSOLETE		19.81 [.780]	23.88 [.940]	27.74 [1.092]	6	3-641525-6
⚠️ OBSOLETE		11.89 [.468]	15.95 [.628]	19.81 [.780]	4	3-641525-4
⚠️ OBSOLETE	TIN-LEAD	7.92 [.312]	11.99 [.472]	15.85 [.624]	3	3-641525-3
⚠️ OBSOLETE		3.96 [.156]	8.03 [.316]	11.89 [.468]	2	3-641525-2
⚠️ OBSOLETE		91.14 [3.588]	95.20 [3.748]	99.06 [3.900]	24	2-641525-4
⚠️ OBSOLETE		55.47 [2.184]	59.54 [2.344]	63.40 [2.496]	15	1-641525-5
⚠️ OBSOLETE		43.59 [1.716]	47.65 [1.876]	51.51 [2.028]	12	1-641525-2
⚠️ OBSOLETE		31.70 [1.248]	35.76 [1.408]	39.62 [1.560]	9	641525-9
⚠️ OBSOLETE	SUPERSEDED	19.81 [.780]	23.88 [.940]	27.74 [1.092]	6	641525-6
⚠️ OBSOLETE		11.89 [.468]	15.95 [.628]	19.81 [.780]	4	641525-4
⚠️ OBSOLETE		7.92 [.312]	11.99 [.472]	15.85 [.624]	3	641525-3
⚠️ OBSOLETE		3.96 [.156]	8.03 [.316]	11.89 [.468]	2	641525-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
B. LEWIS
CHK
R. SWING
APVD

5-28-96
5-28-96

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL
SEE NOTE 1

FINISH
SEE NOTE 1

WEIGHT
-

CUSTOMER DRAWING

DWN
B. LEWIS
CHK
R. SWING
APVD

5-28-96
5-28-96

NAME
MTA-156
POSTED CONNECTOR ASSEMBLY,
24 AWG

SIZE
A1

CAGE CODE
00779

DRAWING NO
641525

RESTRICTED TO
-

SCALE
5:1

SHEET
1

OF
1

REV
D1

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

AMP 4805 REV 31MAR2000