

SmartRack 26U Wall-Mount Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: **SRW26US**



Description

The SRW26US 26U Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 26U of standard 19" rackmount equipment. Supports up to 250lbs of equipment. A sturdy hinge between the cabinet and the wall-mount bracket allows the cabinet to swing away from the wall for easy access to equipment and cabling. Top and bottom panels include convenient cutouts for cable routing. For additional versatility, an optional Rolling Caster Kit (Model SRCASTER) is available to convert the enclosure to a rollaway floor unit.

Features

- **Space-Saving Rackmount Solution:** The SRW26US features a sturdy bracket and heavy-duty steel frame that allows the enclosure to be wall mounted—an ideal rackmount solution for any venue where floor space is limited.
- **Easy Installation:** The SRW26US is compatible with all standard 19-inch rack equipment, and is designed to simplify equipment installation. It features front and rear pairs of vertical mounting rails that are adjustable in quarter-inch increments to accommodate equipment depths from 3 to 20.5 inches. Adjustment is quick and convenient—simply unscrew the rails, slide them to the desired depth and restore the screws. The rails feature square mounting holes and are capable of supporting up to 250 lbs. equipment with included installation hardware. Each rack space within the enclosure is numbered for easy reference.
- **Convenient Access to Equipment and Cabling:** The SRW26US's sturdy wall bracket features a sturdy hinge that allows the enclosure to swing away from the wall for convenient access to equipment and cabling. The swing direction can be reversed by rotating the enclosure 180 degrees before installation. The wall bracket locks to secure equipment in general-access areas. The lockable front door and lockable, removable side panels assure ease of installation and convenient service access to installed equipment. Both door and side panels are perforated to promote efficient airflow.
- **Vented Top and Bottom Panels with Cable Cutouts:** The top and bottom panels of the SRW26US are furnished with vents designed to help remove

Highlights

- 26U of rack space; 250-lb. load capacity
- Adjustable front and rear vertical rackmount rails
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Hinged cabinet swings away from wall bracket for easy equipment access (swing direction is reversible)
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

Package Includes

- SRW26US Wallmount Rack Enclosure
- (48) M6 screws
- (48) M6 cage nuts
- (48) M6 washers
- (2) Keys
- Owner's Manual

warm air from the enclosure and draw in cool air by convection. They also support installation of standard user-supplied case fans. The top and bottom panels are also provided with ports for cable routing through the movable portion of the enclosure or the fixed wall bracket. Removable covers block unused cable ports.

- **PCI DSS Compliance:** The SRW26US meets all requirements toward PCI DSS (Payment Card Industry Data Security Standard) compliance. A locking, reversible front door and locking, removable side panels restrict unwanted access to installed equipment while still allowing authorized personnel to perform inspections, maintenance and equipment replacement.
- **Optional Rollaway Floor Unit:** The SRW26US can also be configured as a freestanding, rollaway floor unit with Tripp Lite's optional Rolling Caster Kit (Model SRCASTER).

Specifications

SELECTOR	
Selector Type	RACK EQUIPMENT
General Info	
Product Group	RACKS
TAA Compliant	No
OVERVIEW	
Style	Wall Mounted
Rack Type	Wall-Mount
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	20.5
Installed Whole System Maximum Rack Depth (cm)	52.07
Installed Whole System Minimum Rack Depth (in.)	3
Installed Whole System Minimum Rack Depth (cm)	7.62
Rack Height (U Spaces)	26
Shipping Dimensions (hwd / in.)	55.4 x 25.6 x 23.6
Shipping Dimensions (hwd / cm)	140.71 x 65.02 x 60
Shipping Weight (lbs.)	140
Shipping Weight (kg)	63.5
Unit Dimensions (hwd / in.)	49.7 x 23.63 x 21.6
Unit Weight (lbs.)	125

Unit Weight (kg)	56.6
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 126 x 60 x 54.9 (HWD)
Color	Black
Weight Capacity - Stationary (lbs.)	250
Weight Capacity - Stationary (kg)	113.4
Factory Preset Rack Depth (in.)	11.42
Factory Preset Rack Depth (cm)	29.01
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Hinged (Swings Away from Wall Bracket)	Yes
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, IP20 Protection Rating, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.