



2SK4066

N-Channel Power MOSFET 60V, 100A, 4.7mΩ, TO-262-3L/TO-263-2L

ON Semiconductor®

<http://onsemi.com>

Features

- ON-resistance $R_{DS(on)} = 3.6\text{m}\Omega$ (typ.)
- Input capacitance $C_{iss} = 12500\text{pF}$ (typ.)
- 4V drive


Specifications

Absolute Maximum Ratings at $T_a = 25^\circ\text{C}$


Parameter	Symbol	Conditions	Ratings	Unit
Drain-to-Source Voltage	V_{DS}		60	V
Gate-to-Source Voltage	V_{GS}		± 20	V
Drain Current (DC)	I_D		100	A
Drain Current (Pulse)	I_{DP}	$PW \leq 10\mu\text{s}$, duty cycle $\leq 1\%$	400	A
Allowable Power Dissipation	P_D		1.65	W
		$T_c = 25^\circ\text{C}$	90	W

Continued on next page.

Package Dimensions unit : mm (typ)
7537-001




Package Dimensions unit : mm (typ)
7535-001



Product & Package Information


- Package : TO-262-3L
- JEITA, JEDEC : TO-262
- Minimum Packing Quantity : 50pcs./magazine

Marking




- Package : TO-263-2L
- JEITA, JEDEC : SC-83, TO-263
- Minimum Packing Quantity : 800pcs./reel

Packing Type : DL



Electrical Connection



Continued from preceding page.

Parameter	Symbol	Conditions	Ratings	Unit
Channel Temperature	Tch		150	°C
Storage Temperature	Tstg		-55 to +150	°C
Avalanche Energy (Single Pulse) *1	EAS		850	mJ
Avalanche Current *2	IAV		70	A

Note : *1 VDD=30V, L=200μH, IAV=70A (Fig.1)

*2 L≤200μH, single pulse

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Electrical Characteristics at Ta=25°C

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Drain-to-Source Breakdown Voltage	V(BR)DSS	ID=1mA, VGS=0V	60			V
Zero-Gate Voltage Drain Current	IDSS	VDS=60V, VGS=0V			1	μA
Gate-to-Source Leakage Current	IGSS	VGS=±16V, VDS=0V			±10	μA
Cutoff Voltage	VGS(off)	VDS=10V, ID=1mA	1.2		2.6	V
Forward Transfer Admittance	yfs	VDS=10V, ID=50A	51	85		S
Static Drain-to-Source On-State Resistance	RD(on)1	ID=50A, VGS=10V		3.6	4.7	mΩ
	RD(on)2	ID=50A, VGS=4V		4.7	6.6	mΩ
Input Capacitance	Ciss	VDS=20V, f=1MHz		12500		pF
Output Capacitance	Coss			1200		pF
Reverse Transfer Capacitance	Crss			950		pF
Turn-ON Delay Time	td(on)	See Fig.2		80		ns
Rise Time	tr			630		ns
Turn-OFF Delay Time	td(off)			860		ns
Fall Time	tf			750		ns
Total Gate Charge	Qg	VDS=30V, VGS=10V, ID=100A		220		nC
Gate-to-Source Charge	Qgs			31		nC
Gate-to-Drain "Miller" Charge	Qgd			55		nC
Diode Forward Voltage	VSD	IS=100A, VGS=0V		0.9	1.2	V

Fig.1 Avalanche Resistance Test Circuit


















Fig.2 Switching Time Test Circuit



Ordering Information

Device	Package	Shipping	memo
2SK4066-1E	TO-262-3L	50pcs./magazine	Pb Free
2SK4066-DL-1E	TO-263-2L	800pcs./reel	





Taping Specification

2SK4066-DL-1E

1. Packing Format


Package Name	Maximum Number of devices contained (pcs)			Packing format	
	Reel	Inner box	Outer box	Inner BOX	Outer BOX
TO-263-2L	800	1600	6400	SPD-0V0011 2 reel contained Dimensions:mm (external) 351×340×68	SPD-0V0009 4 inner boxes contained Dimensions:mm (external) 390×370×318

Reel label, Inner box label

Outer box label

(unit:mm)

Packing method





Reel label

Type No. →

LOT No. →

Quantity →

Origin →



It is a label at the time of factory shipments.
The form of a label may change in physical
distribution process.


NOTE (1)

The LEAD FREE * description shows that the surface
treatment of the terminal is lead free.


Label	JEITA Phase
LEAD FREE 3	JEITA Phase 3A

2. Taping configuration


2-1. Carrier tape size (unit:mm)




2-2. Device placement direction




Outline Drawing
2SK4066-DL-1E



Land Pattern Example



Outline Drawing
2SK4066-1E



Note on usage : Since the 2SK4066 is a MOSFET product, please avoid using this device in the vicinity of highly charged objects.

ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.