

DESCRIPTION: 0.085 RIBBON - DIP SOLDER

36 PIN
SHOWN


	014	024	036	050
A	1.728	2.154	2.667	3.272
	43.90	54.70	67.75	83.10
B	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85
C	1.004	1.429	1.929	2.538
	25.50	36.30	49.00	64.47
D	0.689	1.102	1.634	2.207
	17.50	28.00	41.50	56.05

MATERIAL:


INSULATION: PBT - UL 94V-0 RATED
CONTACTS: PHOSPHOR BRONZE
CONTACT PLATING: GOLD FLASH IN THE MATING AREA
BRIGHT TIN IN THE SOLDER AREA
SHELL: STEEL, NICKEL PLATED

ELECTRICAL:

CURRENT RATING: 1 AMPS
VOLTAGE RATING: 1,000V AC r.m.s.
INSULATION RESISTANCE: 1,000MegOhms Min. @ 500VDC
CONTACT RESISTANCE: 30Milliohms Max.
OPERATING TEMPERATURE: -55°C TO +125°C



RECOMMENDED PCB LAYOUT
SCALE = 2 : 1



111-YYY-1 1 3 L 00 1

SERIES
POSITIONS
014
024
036
050
GENDER
1 = MALE
TERMINATION
1 = DIP SOLDER
RoHS COMPLIANT
L = LOW TEMP. PROCESS
SHELL PLATING
3 = NICKEL
HARDWARE
00 = NO HARDWARE
PLATING
1 = GOLD FLASH

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

DATE:
09-21-98

CHECKED:

DATE:

SCALE:
1 : 1

SHEET
1 OF 2


REV
10

DWG NO. 111-YYY-113L001


RoHS COMPLIANT

NorComp


	014	024	036	050
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85




14 POSITION



36 POSITION



24 POSITION



50 POSITION

NOTEDIMENSION "C" =
CENTER TO CENTER OF MOUNTING HOLES
CENTER OF RADI
OVERALL LENGTH OF CUTOUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: M. SIGMON		DATE: 01-14-11	
			CHECKED:		DATE:	
	NorComp		SCALE: NONE	SHEET 2 OF 2		REV 10
DWG NO. 111-YYY-113L001						