

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

BD

0

[illegible]

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


L

REVISÉD PER ECO-08-029128

	22NOV08
--	---------

8	HMR
---	-----

R	MS
---	----



(2) #5-20 SELF-TAPPING SCREWS,
 SOLID OR SLOTTED SHANK.
 MATERIAL: 
 LENGTH: .50⁺⁰⁰_{-.05}

$$-1.000 \pm .010$$

CLAMPING AREA SHADED 2 3

1 PARTS PACKAGED UNASSEMBLED.

2 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN
BY REVERSING CLAMPING INSERTS.
(2 INSERTS SUPPLIED, -1 AND -2 ONLY)


 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN
BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -3 ONLY)

4 .453 MAXIMUM CABLE OUTSIDE DIAMETER.

 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 200 ONLY.

6 STEEL, ZINC PLATE WITH NON-HEXAVALENT CHROMATE.

		 BULK	206358-5
		INDIVIDUAL	206358-4
OBSOLETE		 BULK	206358-3
		 BULK	206358-2
		INDIVIDUAL	206358-1
		PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN A GRAFF		4/23/91		 Tyco Electronics Corporation Harrisburg, PA 17105-3608								
DIMENSIONS: INCHES			TOLERANCES UNLESS OTHERWISE SPECIFIED:			CHK W.G.LENKER		7-23-92							
						APVD —		NAME							
			0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			PRODUCT SPEC		CABLE CLAMP KIT, LARGE, SHELL SIZE 11, CPC							
						108-10024									
						APPLICATION SPEC									
						—									
MATERIAL THERMOPLASTIC			FINISH —			WEIGHT —		SIZE A3		CAGE CODE 00779		DRAWING NO C-206358		RESTRICTED TO —	
CUSTOMER DRAWING										SCALE NTS		SHEET 1 OF 1		REV	